

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930001

Luminaire Tested: DFN2DS-4P4F0-060DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-060DS950-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.3 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 62
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930001

CATALOG NUMBER: DFN2DS-4P4F0-060DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930001

CATALOG NUMBER: DFN2DS-4P4F0-060DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1431	1431	1431
5°	1437	1416	1424
10°	1428	1402	1409
15°	1411	1383	1382
20°	1385	1356	1355
25°	1361	1323	1323
30°	1329	1292	1281
35°	1299	1255	1236
40°	1261	1218	1195
45°	1224	1181	1152
50°	1184	1143	1103
55°	1142	1099	1058
60°	1095	1046	1007
65°	1046	993	948
70°	982	929	885
75°	893	856	835
80°	793	768	729
85°	646	616	553

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1224 cd/sqm

TEST NUMBER: P930001

CATALOG NUMBER: DFN2DS-4P4F0-060DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	3.7
10°-20°	584.3	10.4
20°-30°	858.6	15.3
30°-40°	997.2	17.8
40°-50°	996.0	17.7
50°-60°	868.5	15.5
60°-70°	642.0	11.4
70°-80°	363.2	6.5
80°-90°	95.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1650.5	29.4
0°-40°	2647.7	47.2
0°-60°	4512.2	80.4
0°-90°	5613.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5613.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2206	2206	2206	2206	2206	
5°	2206	2198	2174	2191	2187	209
15°	2100	2088	2060	2068	2058	592
25°	1901	1884	1848	1852	1848	875
35°	1640	1619	1585	1572	1561	1024
45°	1334	1320	1288	1264	1256	1030
55°	1010	997	972	946	936	903
65°	681	668	647	628	617	673
75°	356	352	341	329	333	380
85°	87	85	83	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930001

CATALOG NUMBER: DFN2DS-4P4F0-060DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2206.2	2206.2	2206.2	2206.2	2206.2
2.5°	2219.0	2208.5	2185.0	2206.2	2202.1
5°	2206.2	2197.9	2174.4	2191.4	2187.3
7.5°	2191.4	2178.8	2155.4	2172.5	2168.2
10°	2168.2	2153.4	2127.9	2144.8	2138.4
12.5°	2136.3	2123.6	2098.2	2108.8	2104.5
15°	2100.2	2087.6	2059.9	2068.5	2057.9
17.5°	2055.7	2043.1	2015.4	2025.9	2015.4
20°	2006.8	1994.2	1964.5	1970.8	1962.5
22.5°	1958.2	1939.0	1911.4	1911.4	1907.1
25°	1900.8	1884.0	1847.9	1851.9	1847.9
27.5°	1837.1	1822.2	1794.7	1788.5	1777.9
30°	1773.7	1756.5	1724.8	1718.5	1709.9
32.5°	1705.6	1693.1	1659.0	1646.2	1637.7
35°	1640.0	1618.8	1584.8	1571.9	1561.3
37.5°	1565.7	1546.5	1512.6	1497.6	1487.1
40°	1489.3	1472.2	1438.3	1419.4	1410.8
42.5°	1415.0	1397.9	1364.2	1342.8	1330.2
45°	1334.5	1319.6	1287.7	1264.5	1255.9
47.5°	1255.9	1241.1	1207.1	1183.7	1171.0
50°	1173.1	1162.5	1132.9	1103.1	1092.5
52.5°	1092.5	1077.7	1050.2	1026.8	1012.0
55°	1009.9	997.1	971.6	946.2	935.6
57.5°	927.1	916.6	888.9	863.4	854.8
60°	844.3	835.9	806.3	782.8	776.5
62.5°	763.7	748.8	727.6	706.5	698.0
65°	681.1	668.3	647.1	628.0	617.4
67.5°	596.2	585.4	566.5	551.7	543.1
70°	517.7	509.2	490.0	475.1	466.8
72.5°	437.1	428.6	418.0	403.1	396.8
75°	356.3	352.3	341.4	328.9	333.1
77.5°	284.3	275.8	271.4	265.2	258.8
80°	212.2	210.0	205.7	199.4	195.1
82.5°	144.3	144.3	142.2	133.7	133.7
85°	86.8	84.9	82.8	76.3	74.3
87.5°	38.3	34.0	29.7	23.4	21.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930001

CATALOG NUMBER: DFN2DS-4P4F0-060DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.53	14.14	12.89	14.45	14.77	12.08	13.69	12.45	14.01	14.32
	3H	14.28	15.73	14.66	16.06	16.42	13.79	15.24	14.16	15.57	15.93
	4H	14.92	16.29	15.32	16.64	17.02	14.43	15.80	14.83	16.15	16.52
	6H	15.39	16.66	15.81	17.03	17.42	14.89	16.16	15.30	16.53	16.92
	8H	15.54	16.75	15.96	17.14	17.54	15.03	16.24	15.46	16.63	17.03
	12H	15.63	16.79	16.06	17.17	17.60	15.11	16.27	15.54	16.66	17.09
4H	2H	13.09	14.46	13.49	14.81	15.18	12.74	14.10	13.13	14.45	14.83
	3H	15.06	16.21	15.47	16.61	17.01	14.66	15.80	15.07	16.20	16.60
	4H	15.84	16.88	16.27	17.29	17.73	15.42	16.45	15.85	16.87	17.30
	6H	16.44	17.34	16.89	17.78	18.24	16.00	16.91	16.46	17.35	17.81
	8H	16.63	17.47	17.09	17.92	18.38	16.19	17.03	16.65	17.48	17.94
	12H	16.76	17.52	17.24	17.99	18.46	16.31	17.07	16.79	17.54	18.01
8H	4H	16.11	16.96	16.57	17.40	17.87	15.74	16.59	16.20	17.03	17.49
	6H	16.83	17.53	17.32	18.02	18.50	16.45	17.15	16.94	17.64	18.11
	8H	17.09	17.72	17.60	18.23	18.71	16.70	17.33	17.21	17.83	18.32
	12H	17.29	17.85	17.79	18.34	18.90	16.87	17.43	17.38	17.92	18.48
12H	4H	16.14	16.90	16.62	17.38	17.85	15.78	16.53	16.26	17.01	17.48
	6H	16.87	17.51	17.38	18.01	18.50	16.50	17.14	17.01	17.64	18.13
	8H	17.19	17.75	17.69	18.24	18.80	16.81	17.37	17.32	17.86	18.42