

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930019

Luminaire Tested: DFN2DS-4P4F0-070DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-070DS950-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6548.9 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 74.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930019

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930019

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1670	1670	1670
5°	1676	1652	1662
10°	1666	1635	1644
15°	1646	1614	1613
20°	1616	1582	1581
25°	1587	1543	1543
30°	1550	1507	1494
35°	1515	1464	1443
40°	1472	1421	1394
45°	1428	1378	1344
50°	1381	1334	1286
55°	1333	1282	1235
60°	1278	1221	1176
65°	1220	1159	1106
70°	1145	1084	1033
75°	1042	998	974
80°	925	897	851
85°	755	720	645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1428 cd/sqm

TEST NUMBER: P930019

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.3	3.7
10°-20°	681.6	10.4
20°-30°	1001.7	15.3
30°-40°	1163.4	17.8
40°-50°	1162.0	17.7
50°-60°	1013.2	15.5
60°-70°	749.0	11.4
70°-80°	423.8	6.5
80°-90°	111.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1925.6	29.4
0°-40°	3089.0	47.2
0°-60°	5264.2	80.4
0°-90°	6548.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6548.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2574	2574	2574	2574	2574	
5°	2574	2564	2537	2557	2552	244
15°	2450	2436	2403	2413	2401	690
25°	2218	2198	2156	2161	2156	1020
35°	1913	1889	1849	1834	1822	1195
45°	1557	1540	1502	1475	1465	1202
55°	1178	1163	1134	1104	1092	1053
65°	795	780	755	733	720	786
75°	416	411	398	384	389	444
85°	101	99	97	89	87	119
90°	0	0	0	0	0	

TEST NUMBER: P930019

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2573.9	2573.9	2573.9	2573.9	2573.9
2.5°	2588.9	2576.5	2549.2	2573.9	2569.2
5°	2573.9	2564.3	2536.9	2556.6	2551.9
7.5°	2556.6	2541.9	2514.6	2534.6	2529.6
10°	2529.6	2512.2	2482.5	2502.3	2494.9
12.5°	2492.2	2477.6	2447.9	2460.2	2455.2
15°	2450.3	2435.5	2403.2	2413.2	2400.9
17.5°	2398.2	2383.6	2351.3	2363.6	2351.3
20°	2341.2	2326.6	2291.9	2299.3	2289.5
22.5°	2284.5	2262.2	2229.9	2229.9	2224.9
25°	2217.6	2197.9	2155.9	2160.6	2155.9
27.5°	2143.3	2126.0	2093.9	2086.6	2074.2
30°	2069.3	2049.2	2012.3	2004.9	1994.9
32.5°	1989.9	1975.2	1935.5	1920.6	1910.6
35°	1913.2	1888.6	1848.9	1834.0	1821.6
37.5°	1826.6	1804.3	1764.6	1747.3	1734.9
40°	1737.6	1717.6	1677.9	1655.9	1645.9
42.5°	1650.9	1631.0	1591.6	1566.6	1551.9
45°	1556.9	1539.6	1502.3	1475.2	1465.2
47.5°	1465.2	1447.9	1408.2	1380.9	1366.3
50°	1368.6	1356.3	1321.6	1287.0	1274.6
52.5°	1274.6	1257.3	1225.3	1198.0	1180.6
55°	1178.2	1163.3	1133.6	1103.9	1091.6
57.5°	1081.6	1069.3	1036.9	1007.3	997.4
60°	985.0	975.2	940.7	913.3	906.0
62.5°	890.9	873.7	849.0	824.3	814.3
65°	794.7	779.6	755.0	732.7	720.3
67.5°	695.6	683.0	660.9	643.6	633.6
70°	603.9	594.0	571.6	554.3	544.6
72.5°	509.9	500.0	487.6	470.3	463.0
75°	415.7	411.0	398.3	383.7	388.7
77.5°	331.7	321.7	316.7	309.3	302.0
80°	247.6	245.0	240.0	232.7	227.7
82.5°	168.3	168.3	165.9	156.0	156.0
85°	101.4	99.0	96.7	89.0	86.7
87.5°	44.6	39.7	34.7	27.3	24.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930019

CATALOG NUMBER: DFN2DS-4P4F0-070DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.06	14.67	13.43	14.99	15.30	12.62	14.23	12.98	14.54	14.86
	3H	14.81	16.27	15.19	16.60	16.96	14.32	15.78	14.70	16.10	16.46
	4H	15.46	16.83	15.86	17.18	17.55	14.97	16.33	15.36	16.68	17.06
	6H	15.93	17.20	16.34	17.56	17.95	15.43	16.70	15.84	17.06	17.45
	8H	16.07	17.28	16.50	17.67	18.07	15.57	16.78	15.99	17.17	17.57
	12H	16.16	17.32	16.59	17.70	18.13	15.65	16.81	16.08	17.19	17.62
4H	2H	13.62	14.99	14.02	15.34	15.72	13.27	14.64	13.67	14.99	15.36
	3H	15.60	16.75	16.01	17.14	17.54	15.19	16.34	15.60	16.74	17.14
	4H	16.38	17.41	16.81	17.83	18.26	15.95	16.99	16.38	17.40	17.84
	6H	16.97	17.88	17.43	18.32	18.77	16.54	17.44	16.99	17.89	18.34
	8H	17.16	18.01	17.62	18.45	18.92	16.72	17.57	17.18	18.01	18.48
	12H	17.29	18.05	17.77	18.53	19.00	16.84	17.60	17.32	18.08	18.55
8H	4H	16.65	17.50	17.11	17.94	18.40	16.28	17.12	16.74	17.56	18.03
	6H	17.36	18.07	17.86	18.56	19.03	16.98	17.69	17.48	18.17	18.65
	8H	17.62	18.25	18.13	18.76	19.25	17.23	17.86	17.74	18.37	18.85
	12H	17.82	18.38	18.33	18.87	19.43	17.41	17.97	17.92	18.46	19.02
12H	4H	16.68	17.44	17.16	17.91	18.38	16.31	17.07	16.79	17.55	18.02
	6H	17.41	18.04	17.92	18.55	19.03	17.04	17.67	17.55	18.18	18.67
	8H	17.72	18.28	18.23	18.77	19.33	17.35	17.90	17.85	18.39	18.95