

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930508

Luminaire Tested: DFN2DS-PN3F0-030DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-030DS830-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2402.1 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 28.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930508

CATALOG NUMBER: DFN2DS-PN3F0-030DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930508

CATALOG NUMBER: DFN2DS-PN3F0-030DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1365	1365	1365
5°	1371	1348	1356
10°	1360	1326	1315
15°	1344	1287	1250
20°	1323	1231	1169
25°	1301	1167	1091
30°	1270	1101	990
35°	1240	1030	902
40°	1210	956	800
45°	1174	874	708
50°	1138	790	617
55°	1101	700	530
60°	1057	606	440
65°	1009	509	401
70°	950	419	368
75°	878	382	344
80°	776	341	313
85°	609	270	270

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1174 cd/sqm

TEST NUMBER: P930508

CATALOG NUMBER: DFN2DS-PN3F0-030DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	4.6
10°-20°	300.5	12.5
20°-30°	421.9	17.6
30°-40°	459.9	19.1
40°-50°	422.7	17.6
50°-60°	332.0	13.8
60°-70°	216.1	9.0
70°-80°	111.2	4.6
80°-90°	28.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.9	34.6
0°-40°	1291.8	53.8
0°-60°	2046.4	85.2
0°-90°	2402.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2402.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1168	1168	1168	1168	1168	
5°	1168	1163	1149	1158	1155	111
15°	1111	1099	1063	1043	1033	313
25°	1008	974	905	862	846	464
35°	869	815	722	655	632	544
45°	710	639	529	453	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	120	85	77	76	206
85°	45	23	20	20	20	54
90°	0	0	0	0	0	

TEST NUMBER: P930508

CATALOG NUMBER: DFN2DS-PN3F0-030DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.0	1168.0	1168.0	1168.0	1168.0
2.5°	1173.3	1168.0	1156.3	1166.9	1164.9
5°	1168.0	1162.7	1149.0	1158.5	1155.3
7.5°	1158.5	1152.2	1137.4	1141.5	1136.2
10°	1145.8	1138.4	1117.3	1114.0	1107.8
12.5°	1129.9	1120.4	1091.9	1085.6	1073.9
15°	1110.9	1099.2	1063.3	1043.3	1032.7
17.5°	1088.7	1071.8	1027.3	1004.2	987.2
20°	1063.3	1042.1	989.3	963.0	939.6
22.5°	1035.9	1011.5	950.2	914.3	898.5
25°	1008.4	974.5	904.8	861.5	845.5
27.5°	975.6	939.6	862.5	812.9	788.5
30°	940.8	900.6	816.0	762.2	733.5
32.5°	906.9	858.3	771.7	708.2	681.7
35°	868.9	814.9	721.9	655.3	632.1
37.5°	831.9	773.7	675.4	602.4	576.1
40°	792.8	729.4	626.8	551.7	524.3
42.5°	752.6	685.0	578.2	499.9	473.5
45°	710.4	639.4	528.6	453.4	428.0
47.5°	670.1	595.2	481.0	405.8	382.6
50°	625.8	550.7	434.5	361.4	339.3
52.5°	582.3	503.1	390.1	320.3	300.2
55°	540.0	457.6	343.5	280.2	260.1
57.5°	496.8	412.2	302.4	243.1	226.2
60°	452.3	367.9	259.0	205.1	188.2
62.5°	409.1	324.5	221.9	171.3	162.9
65°	364.6	279.0	183.9	148.0	144.8
67.5°	322.4	236.7	148.0	130.0	126.8
70°	278.0	195.6	122.6	112.0	107.8
72.5°	235.7	157.4	102.5	94.1	91.9
75°	194.4	120.5	84.6	77.1	76.1
77.5°	153.3	85.5	66.6	62.4	60.2
80°	115.2	61.3	50.7	46.5	46.5
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930508

CATALOG NUMBER: DFN2DS-PN3F0-030DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.32	13.84	12.68	14.15	14.47	8.28	9.80	8.64	10.11	10.43
	3H	14.08	15.45	14.46	15.77	16.14	9.54	10.91	9.92	11.23	11.60
	4H	14.75	16.03	15.15	16.38	16.76	10.04	11.32	10.44	11.67	12.05
	6H	15.24	16.42	15.65	16.79	17.18	10.42	11.61	10.84	11.97	12.37
	8H	15.40	16.53	15.83	16.92	17.32	10.55	11.68	10.98	12.06	12.47
	12H	15.51	16.58	15.94	16.97	17.39	10.63	11.71	11.06	12.09	12.52
4H	2H	12.42	13.70	12.82	14.05	14.43	8.97	10.25	9.37	10.60	10.98
	3H	14.35	15.42	14.76	15.82	16.22	10.42	11.48	10.83	11.88	12.28
	4H	15.10	16.06	15.54	16.48	16.91	11.01	11.97	11.45	12.39	12.82
	6H	15.69	16.53	16.15	16.97	17.43	11.50	12.33	11.96	12.78	13.24
	8H	15.91	16.69	16.37	17.13	17.60	11.66	12.44	12.13	12.89	13.35
	12H	16.06	16.76	16.54	17.24	17.71	11.78	12.48	12.26	12.96	13.43
8H	4H	15.13	15.90	15.59	16.35	16.82	11.37	12.15	11.83	12.59	13.06
	6H	15.76	16.41	16.26	16.90	17.38	11.95	12.60	12.45	13.09	13.57
	8H	16.02	16.59	16.53	17.10	17.59	12.18	12.75	12.69	13.26	13.75
	12H	16.22	16.73	16.73	17.22	17.79	12.36	12.87	12.87	13.36	13.92
12H	4H	15.11	15.81	15.59	16.28	16.76	11.41	12.11	11.89	12.58	13.06
	6H	15.75	16.32	16.26	16.83	17.32	12.02	12.60	12.53	13.11	13.59
	8H	16.03	16.54	16.54	17.03	17.60	12.29	12.80	12.80	13.29	13.86