

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930526

Luminaire Tested: DFN2DS-PN3F0-040DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-040DS830-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3202.8 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930526

CATALOG NUMBER: DFN2DS-PN3F0-040DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930526

CATALOG NUMBER: DFN2DS-PN3F0-040DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1820	1820	1820
5°	1827	1798	1808
10°	1813	1768	1753
15°	1793	1716	1666
20°	1764	1641	1559
25°	1734	1556	1454
30°	1693	1468	1320
35°	1653	1374	1203
40°	1613	1275	1067
45°	1566	1165	944
50°	1517	1053	823
55°	1468	933	707
60°	1410	807	587
65°	1345	678	534
70°	1267	558	491
75°	1171	509	458
80°	1033	454	418
85°	813	359	359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1566 cd/sqm

TEST NUMBER: P930526

CATALOG NUMBER: DFN2DS-PN3F0-040DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	4.6
10°-20°	400.7	12.5
20°-30°	562.5	17.6
30°-40°	613.2	19.1
40°-50°	563.6	17.6
50°-60°	442.6	13.8
60°-70°	288.1	9.0
70°-80°	148.3	4.6
80°-90°	37.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.1	34.6
0°-40°	1722.3	53.8
0°-60°	2728.5	85.2
0°-90°	3202.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3202.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1557	1557	1557	1557	1557	
5°	1557	1550	1532	1545	1540	148
15°	1481	1466	1418	1391	1377	417
25°	1344	1299	1206	1149	1127	618
35°	1159	1087	963	874	843	725
45°	947	853	705	605	571	731
55°	720	610	458	374	347	644
65°	486	372	245	197	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	73
90°	0	0	0	0	0	

TEST NUMBER: P930526

CATALOG NUMBER: DFN2DS-PN3F0-040DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1557.3	1557.3	1557.3	1557.3	1557.3
2.5°	1564.4	1557.3	1541.8	1556.0	1553.1
5°	1557.3	1550.2	1531.9	1544.6	1540.5
7.5°	1544.6	1536.2	1516.5	1522.0	1515.0
10°	1527.7	1517.8	1489.7	1485.3	1477.1
12.5°	1506.6	1493.9	1455.8	1447.4	1431.8
15°	1481.2	1465.7	1417.8	1391.1	1377.0
17.5°	1451.6	1429.0	1369.8	1338.9	1316.3
20°	1417.8	1389.5	1319.1	1283.9	1252.9
22.5°	1381.2	1348.8	1266.9	1219.0	1198.0
25°	1344.5	1299.4	1206.3	1148.7	1127.4
27.5°	1300.9	1252.9	1150.0	1083.8	1051.3
30°	1254.4	1200.7	1087.9	1016.1	978.1
32.5°	1209.2	1144.3	1028.9	944.3	908.9
35°	1158.6	1086.6	962.6	873.8	842.7
37.5°	1109.2	1031.6	900.6	803.2	768.1
40°	1057.0	972.5	835.7	735.7	699.1
42.5°	1003.4	913.3	770.9	666.6	631.4
45°	947.1	852.6	704.7	604.6	570.8
47.5°	893.6	793.5	641.3	541.2	510.2
50°	834.3	734.3	579.2	481.9	452.4
52.5°	776.5	670.8	520.1	427.0	400.3
55°	720.2	610.2	458.0	373.5	346.8
57.5°	662.4	549.7	403.1	324.1	301.6
60°	603.2	490.4	345.2	273.5	250.9
62.5°	545.5	432.8	295.9	228.3	217.1
65°	486.3	372.0	245.2	197.3	193.0
67.5°	429.9	315.7	197.3	173.3	169.1
70°	370.7	260.7	163.4	149.4	143.7
72.5°	314.3	210.0	136.7	125.5	122.6
75°	259.2	160.6	112.8	102.9	101.5
77.5°	204.4	114.1	88.8	83.2	80.3
80°	153.5	81.8	67.5	62.1	62.1
82.5°	107.1	55.0	46.5	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930526

CATALOG NUMBER: DFN2DS-PN3F0-040DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.32	14.84	13.68	15.15	15.47	9.28	10.80	9.64	11.11	11.43
	3H	15.08	16.45	15.46	16.77	17.14	10.54	11.91	10.92	12.23	12.60
	4H	15.75	17.03	16.15	17.38	17.76	11.04	12.32	11.44	12.67	13.05
	6H	16.24	17.42	16.65	17.79	18.18	11.42	12.61	11.84	12.97	13.37
	8H	16.40	17.53	16.83	17.92	18.32	11.55	12.68	11.98	13.06	13.47
	12H	16.51	17.58	16.94	17.97	18.39	11.63	12.71	12.06	13.09	13.52
4H	2H	13.42	14.70	13.82	15.05	15.43	9.97	11.25	10.37	11.60	11.98
	3H	15.35	16.42	15.76	16.82	17.22	11.41	12.48	11.83	12.88	13.28
	4H	16.10	17.06	16.54	17.48	17.91	12.01	12.97	12.45	13.39	13.83
	6H	16.69	17.53	17.15	17.97	18.43	12.50	13.34	12.96	13.78	14.24
	8H	16.91	17.69	17.37	18.13	18.60	12.66	13.44	13.13	13.89	14.35
	12H	17.06	17.76	17.54	18.24	18.71	12.78	13.48	13.26	13.96	14.43
8H	4H	16.13	16.90	16.59	17.35	17.82	12.37	13.15	12.83	13.59	14.06
	6H	16.76	17.41	17.26	17.90	18.38	12.96	13.60	13.45	14.09	14.57
	8H	17.01	17.59	17.53	18.10	18.59	13.18	13.75	13.69	14.26	14.75
	12H	17.22	17.73	17.73	18.22	18.79	13.36	13.87	13.87	14.36	14.92
12H	4H	16.11	16.81	16.59	17.28	17.76	12.41	13.11	12.89	13.58	14.06
	6H	16.75	17.32	17.26	17.83	18.32	13.02	13.60	13.53	14.11	14.59
	8H	17.03	17.54	17.54	18.03	18.60	13.29	13.80	13.80	14.29	14.86

END OF REPORT