

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930062

Luminaire Tested: DFN2DS-HX2F0-030DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-030DS840-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2552.5 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930062

CATALOG NUMBER: DFN2DS-HX2F0-030DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930062

CATALOG NUMBER: DFN2DS-HX2F0-030DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2924	2924	2924
5°	2935	2888	2903
10°	2913	2841	2816
15°	2880	2756	2677
20°	2833	2636	2504
25°	2786	2500	2336
30°	2720	2359	2121
35°	2656	2207	1932
40°	2591	2049	1714
45°	2515	1872	1516
50°	2438	1692	1322
55°	2357	1499	1135
60°	2265	1297	942
65°	2160	1089	858
70°	2035	897	789
75°	1881	818	736
80°	1661	731	670
85°	1303	576	576

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2515 cd/sqm

TEST NUMBER: P930062

CATALOG NUMBER: DFN2DS-HX2F0-030DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	4.6
10°-20°	319.3	12.5
20°-30°	448.3	17.6
30°-40°	488.7	19.1
40°-50°	449.2	17.6
50°-60°	352.7	13.8
60°-70°	229.6	9.0
70°-80°	118.2	4.6
80°-90°	30.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	884.0	34.6
0°-40°	1372.7	53.8
0°-60°	2174.6	85.2
0°-90°	2552.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1241	1241	1241	1241	1241	
5°	1241	1236	1221	1231	1228	118
15°	1180	1168	1130	1109	1097	333
25°	1072	1036	962	915	898	493
35°	923	866	767	696	672	578
45°	755	680	562	482	455	583
55°	574	486	365	298	276	513
65°	388	296	195	157	154	384
75°	207	128	90	82	81	219
85°	48	25	21	21	21	58
90°	0	0	0	0	0	

TEST NUMBER: P930062

CATALOG NUMBER: DFN2DS-HX2F0-030DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1241.1	1241.1	1241.1	1241.1	1241.1
2.5°	1246.7	1241.1	1228.7	1240.0	1237.8
5°	1241.1	1235.5	1220.9	1231.0	1227.6
7.5°	1231.0	1224.3	1208.6	1213.0	1207.4
10°	1217.5	1209.7	1187.3	1183.8	1177.2
12.5°	1200.7	1190.6	1160.3	1153.6	1141.1
15°	1180.5	1168.1	1129.9	1108.6	1097.4
17.5°	1156.9	1138.9	1091.7	1067.1	1049.0
20°	1129.9	1107.4	1051.3	1023.3	998.5
22.5°	1100.8	1074.9	1009.7	971.6	954.8
25°	1071.6	1035.5	961.5	915.4	898.5
27.5°	1036.7	998.5	916.5	863.8	837.8
30°	999.7	957.0	867.1	809.9	779.5
32.5°	963.7	912.0	820.0	752.6	724.4
35°	923.3	866.0	767.2	696.4	671.7
37.5°	884.0	822.1	717.7	640.1	612.2
40°	842.4	775.1	666.1	586.3	557.2
42.5°	799.7	727.9	614.4	531.2	503.2
45°	754.9	679.5	561.7	481.8	454.9
47.5°	712.1	632.4	511.1	431.2	406.6
50°	665.0	585.2	461.7	384.1	360.6
52.5°	618.8	534.6	414.5	340.3	319.0
55°	573.9	486.3	365.0	297.7	276.4
57.5°	527.9	438.0	321.3	258.4	240.3
60°	480.7	390.9	275.2	217.9	200.0
62.5°	434.7	344.8	235.8	182.0	173.1
65°	387.5	296.5	195.4	157.3	153.9
67.5°	342.6	251.6	157.3	138.1	134.7
70°	295.4	207.8	130.2	119.0	114.5
72.5°	250.5	167.3	108.9	100.0	97.7
75°	206.6	128.0	89.9	82.0	80.9
77.5°	162.9	90.9	70.8	66.3	64.0
80°	122.4	65.2	53.9	49.4	49.4
82.5°	85.3	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930062

CATALOG NUMBER: DFN2DS-HX2F0-030DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.96	16.48	15.33	16.80	17.11	10.92	12.45	11.29	12.76	13.07
	3H	16.73	18.09	17.11	18.42	18.78	12.19	13.55	12.57	13.88	14.24
	4H	17.39	18.67	17.79	19.02	19.40	12.69	13.97	13.09	14.32	14.70
	6H	17.88	19.07	18.30	19.43	19.82	13.07	14.25	13.48	14.62	15.01
	8H	18.05	19.17	18.47	19.56	19.97	13.20	14.32	13.62	14.71	15.11
	12H	18.15	19.23	18.58	19.61	20.04	13.28	14.35	13.71	14.74	15.17
4H	2H	15.07	16.35	15.47	16.70	17.07	11.62	12.90	12.02	13.25	13.63
	3H	17.00	18.06	17.41	18.46	18.86	13.06	14.12	13.47	14.52	14.93
	4H	17.75	18.71	18.18	19.12	19.56	13.66	14.62	14.09	15.03	15.47
	6H	18.34	19.17	18.80	19.62	20.08	14.15	14.98	14.61	15.42	15.88
	8H	18.56	19.33	19.02	19.78	20.24	14.31	15.09	14.77	15.53	16.00
	12H	18.71	19.40	19.19	19.88	20.35	14.43	15.12	14.91	15.60	16.07
8H	4H	17.77	18.55	18.24	18.99	19.46	14.01	14.79	14.48	15.24	15.70
	6H	18.41	19.05	18.91	19.54	20.02	14.60	15.24	15.10	15.74	16.21
	8H	18.66	19.24	19.18	19.75	20.24	14.82	15.40	15.34	15.91	16.40
	12H	18.86	19.37	19.37	19.87	20.43	15.00	15.51	15.51	16.00	16.57
12H	4H	17.76	18.45	18.24	18.93	19.40	14.06	14.75	14.54	15.23	15.70
	6H	18.39	18.97	18.91	19.48	19.97	14.66	15.24	15.18	15.75	16.24
	8H	18.68	19.19	19.19	19.68	20.24	14.94	15.45	15.45	15.94	16.50