

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930064

Luminaire Tested: DFN2DS-HX2F0-030DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930064
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-030DS850-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2827.9 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 27.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930064

CATALOG NUMBER: DFN2DS-HX2F0-030DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930064

CATALOG NUMBER: DFN2DS-HX2F0-030DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3240	3240	3240
5°	3252	3199	3217
10°	3227	3147	3120
15°	3190	3053	2966
20°	3139	2920	2774
25°	3086	2769	2588
30°	3013	2613	2350
35°	2942	2445	2140
40°	2871	2270	1899
45°	2787	2074	1679
50°	2700	1875	1464
55°	2612	1661	1258
60°	2509	1437	1044
65°	2393	1207	951
70°	2255	994	874
75°	2084	907	816
80°	1840	810	744
85°	1446	638	638

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2787 cd/sqm

TEST NUMBER: P930064

CATALOG NUMBER: DFN2DS-HX2F0-030DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	4.6
10°-20°	353.8	12.5
20°-30°	496.7	17.6
30°-40°	541.4	19.1
40°-50°	497.6	17.6
50°-60°	390.8	13.8
60°-70°	254.4	9.0
70°-80°	130.9	4.6
80°-90°	33.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.3	34.6
0°-40°	1520.7	53.8
0°-60°	2409.2	85.2
0°-90°	2827.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2827.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	64
90°	0	0	0	0	0	

TEST NUMBER: P930064

CATALOG NUMBER: DFN2DS-HX2F0-030DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930064

CATALOG NUMBER: DFN2DS-HX2F0-030DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.32	16.84	15.68	17.15	17.47	11.28	12.80	11.64	13.11	13.43
	3H	17.08	18.45	17.46	18.78	19.14	12.54	13.91	12.92	14.24	14.60
	4H	17.75	19.03	18.15	19.38	19.76	13.05	14.33	13.45	14.67	15.05
	6H	18.24	19.42	18.65	19.79	20.18	13.43	14.61	13.84	14.98	15.37
	8H	18.40	19.53	18.83	19.92	20.32	13.55	14.68	13.98	15.07	15.47
	12H	18.51	19.59	18.94	19.97	20.40	13.63	14.71	14.06	15.09	15.52
4H	2H	15.42	16.70	15.82	17.05	17.43	11.97	13.25	12.37	13.60	13.98
	3H	17.36	18.42	17.77	18.82	19.22	13.42	14.48	13.83	14.88	15.28
	4H	18.11	19.06	18.54	19.48	19.92	14.02	14.97	14.45	15.39	15.83
	6H	18.70	19.53	19.15	19.97	20.43	14.51	15.34	14.96	15.78	16.24
	8H	18.91	19.69	19.37	20.13	20.60	14.67	15.44	15.13	15.89	16.36
	12H	19.06	19.76	19.55	20.24	20.71	14.78	15.48	15.27	15.96	16.43
8H	4H	18.13	18.91	18.59	19.35	19.82	14.37	15.15	14.83	15.59	16.06
	6H	18.77	19.41	19.26	19.90	20.38	14.96	15.60	15.45	16.09	16.57
	8H	19.02	19.59	19.53	20.10	20.59	15.18	15.76	15.69	16.27	16.75
	12H	19.22	19.73	19.73	20.22	20.79	15.36	15.87	15.87	16.36	16.92
12H	4H	18.11	18.81	18.60	19.29	19.76	14.41	15.11	14.90	15.59	16.06
	6H	18.75	19.33	19.26	19.83	20.32	15.02	15.60	15.53	16.11	16.60
	8H	19.03	19.54	19.54	20.03	20.60	15.29	15.80	15.80	16.30	16.86

END OF REPORT