

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930118

Luminaire Tested: DFN2DS-HX2F0-060DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS850-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5655.9 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930118

CATALOG NUMBER: DFN2DS-HX2F0-060DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930118

CATALOG NUMBER: DFN2DS-HX2F0-060DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6480	6480	6480
5°	6504	6398	6434
10°	6454	6294	6240
15°	6380	6107	5931
20°	6278	5841	5548
25°	6173	5538	5176
30°	6026	5227	4699
35°	5885	4890	4281
40°	5741	4539	3797
45°	5573	4147	3358
50°	5401	3749	2929
55°	5224	3322	2515
60°	5020	2873	2088
65°	4787	2415	1901
70°	4509	1988	1748
75°	4168	1812	1632
80°	3680	1619	1487
85°	2890	1276	1276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5573 cd/sqm

TEST NUMBER: P930118

CATALOG NUMBER: DFN2DS-HX2F0-060DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	4.6
10°-20°	707.6	12.5
20°-30°	993.4	17.6
30°-40°	1082.8	19.1
40°-50°	995.2	17.6
50°-60°	781.6	13.8
60°-70°	508.8	9.0
70°-80°	261.9	4.6
80°-90°	66.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1958.7	34.6
0°-40°	3041.5	53.8
0°-60°	4818.4	85.2
0°-90°	5655.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5655.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	128
90°	0	0	0	0	0	

TEST NUMBER: P930118

CATALOG NUMBER: DFN2DS-HX2F0-060DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930118

CATALOG NUMBER: DFN2DS-HX2F0-060DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.73	19.25	18.09	19.56	19.88	13.69	15.21	14.05	15.52	15.84
	3H	19.49	20.86	19.87	21.19	21.55	14.95	16.32	15.33	16.65	17.01
	4H	20.16	21.44	20.56	21.79	22.17	15.45	16.74	15.85	17.08	17.46
	6H	20.65	21.83	21.06	22.20	22.59	15.84	17.02	16.25	17.39	17.78
	8H	20.81	21.94	21.24	22.33	22.73	15.96	17.09	16.39	17.48	17.88
	12H	20.92	21.99	21.35	22.38	22.81	16.04	17.12	16.47	17.50	17.93
4H	2H	17.83	19.11	18.23	19.46	19.84	14.38	15.66	14.78	16.01	16.39
	3H	19.76	20.83	20.17	21.23	21.63	15.83	16.89	16.24	17.29	17.69
	4H	20.51	21.47	20.95	21.89	22.32	16.43	17.38	16.86	17.80	18.24
	6H	21.11	21.94	21.56	22.38	22.84	16.91	17.75	17.37	18.19	18.65
	8H	21.32	22.10	21.78	22.54	23.01	17.08	17.85	17.54	18.30	18.77
	12H	21.47	22.17	21.96	22.65	23.12	17.19	17.89	17.68	18.37	18.84
8H	4H	20.54	21.32	21.00	21.76	22.23	16.78	17.56	17.24	18.00	18.47
	6H	21.18	21.82	21.67	22.31	22.79	17.37	18.01	17.86	18.50	18.98
	8H	21.43	22.00	21.94	22.51	23.00	17.59	18.16	18.10	18.67	19.16
	12H	21.63	22.14	22.14	22.63	23.20	17.77	18.28	18.28	18.77	19.33
12H	4H	20.52	21.22	21.00	21.70	22.17	16.82	17.52	17.31	18.00	18.47
	6H	21.16	21.73	21.67	22.24	22.73	17.43	18.01	17.94	18.52	19.01
	8H	21.44	21.95	21.95	22.44	23.01	17.70	18.21	18.21	18.70	19.27