

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930564

Luminaire Tested: DFN2DS-PN3F0-060DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-060DS835-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5100.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 61.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930564
CATALOG NUMBER: DFN2DS-PN3F0-060DS835-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P930564

CATALOG NUMBER: DFN2DS-PN3F0-060DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2899	2899	2899
5°	2910	2862	2878
10°	2888	2816	2792
15°	2854	2732	2654
20°	2808	2613	2482
25°	2762	2478	2316
30°	2696	2338	2102
35°	2633	2188	1915
40°	2568	2031	1699
45°	2493	1855	1502
50°	2416	1677	1310
55°	2337	1486	1125
60°	2246	1285	934
65°	2142	1080	850
70°	2017	889	782
75°	1865	811	730
80°	1646	724	665
85°	1293	571	571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2493 cd/sqm



TEST NUMBER: P930564
 CATALOG NUMBER: DFN2DS-PN3F0-060DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	4.6
10°-20°	638.0	12.5
20°-30°	895.7	17.6
30°-40°	976.4	19.1
40°-50°	897.4	17.6
50°-60°	704.8	13.8
60°-70°	458.8	9.0
70°-80°	236.1	4.6
80°-90°	60.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1766.2	34.6
0°-40°	2742.6	53.8
0°-60°	4344.8	85.2
0°-90°	5100.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5100.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2480	2480	2480	2480	2480	
5°	2480	2469	2439	2460	2453	235
15°	2359	2334	2258	2215	2193	665
25°	2141	2069	1921	1829	1795	985
35°	1845	1730	1533	1391	1342	1155
45°	1508	1358	1122	963	909	1165
55°	1147	972	729	595	552	1025
65°	774	592	390	314	307	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	116
90°	0	0	0	0	0	



TEST NUMBER: P930564

CATALOG NUMBER: DFN2DS-PN3F0-060DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.8	2479.8	2479.8	2479.8	2479.8
2.5°	2491.0	2479.8	2455.0	2477.6	2473.1
5°	2479.8	2468.6	2439.3	2459.6	2452.9
7.5°	2459.6	2446.2	2414.8	2423.6	2412.4
10°	2432.6	2416.9	2372.2	2365.3	2351.9
12.5°	2399.1	2378.8	2318.1	2304.8	2280.0
15°	2358.6	2333.8	2257.6	2215.0	2192.6
17.5°	2311.5	2275.5	2181.2	2131.9	2096.0
20°	2257.6	2212.6	2100.5	2044.5	1995.0
22.5°	2199.3	2147.6	2017.4	1941.2	1907.6
25°	2141.0	2069.1	1921.0	1829.1	1795.3
27.5°	2071.5	1995.0	1831.2	1725.7	1674.1
30°	1997.4	1911.9	1732.4	1618.1	1557.4
32.5°	1925.5	1822.2	1638.4	1503.6	1447.4
35°	1844.8	1730.3	1532.9	1391.4	1341.9
37.5°	1766.2	1642.6	1434.1	1279.1	1223.1
40°	1683.1	1548.6	1330.7	1171.4	1113.1
42.5°	1597.9	1454.3	1227.6	1061.4	1005.5
45°	1508.1	1357.6	1122.2	962.6	908.8
47.5°	1422.9	1263.6	1021.2	861.7	812.4
50°	1328.6	1169.3	922.4	767.4	720.5
52.5°	1236.4	1068.1	828.1	680.0	637.4
55°	1146.7	971.7	729.3	594.8	552.1
57.5°	1054.8	875.2	641.9	516.2	480.2
60°	960.5	781.0	549.8	435.5	399.5
62.5°	868.6	689.1	471.2	363.6	345.7
65°	774.3	592.4	390.5	314.3	307.4
67.5°	684.5	502.6	314.3	276.0	269.3
70°	590.2	415.2	260.2	237.9	228.8
72.5°	500.5	334.3	217.6	199.8	195.2
75°	412.9	255.7	179.5	163.8	161.7
77.5°	325.5	181.7	141.4	132.4	127.9
80°	244.5	130.2	107.6	98.8	98.8
82.5°	170.5	87.6	74.0	69.5	69.5
85°	96.4	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930564
 CATALOG NUMBER: DFN2DS-PN3F0-060DS835-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.93	16.45	15.30	16.77	17.08	10.89	12.41	11.26	12.73	13.04
	3H	16.70	18.06	17.08	18.39	18.75	12.16	13.52	12.54	13.85	14.21
	4H	17.36	18.64	17.76	18.99	19.37	12.66	13.94	13.06	14.29	14.67
	6H	17.85	19.04	18.27	19.40	19.79	13.04	14.22	13.45	14.59	14.98
	8H	18.02	19.14	18.44	19.53	19.94	13.17	14.29	13.59	14.68	15.08
	12H	18.12	19.20	18.55	19.58	20.01	13.25	14.32	13.68	14.71	15.14
4H	2H	15.04	16.32	15.44	16.67	17.04	11.59	12.87	11.99	13.22	13.60
	3H	16.97	18.03	17.38	18.43	18.83	13.03	14.09	13.44	14.49	14.90
	4H	17.72	18.68	18.15	19.09	19.53	13.63	14.59	14.06	15.00	15.44
	6H	18.31	19.14	18.77	19.59	20.05	14.12	14.95	14.58	15.39	15.85
	8H	18.53	19.30	18.99	19.75	20.21	14.28	15.06	14.74	15.50	15.97
	12H	18.68	19.37	19.16	19.85	20.32	14.40	15.09	14.88	15.57	16.04
8H	4H	17.74	18.52	18.21	18.96	19.43	13.98	14.76	14.45	15.21	15.67
	6H	18.38	19.02	18.88	19.51	19.99	14.57	15.21	15.07	15.71	16.18
	8H	18.63	19.21	19.14	19.72	20.21	14.79	15.37	15.31	15.88	16.37
	12H	18.84	19.34	19.34	19.84	20.40	14.97	15.48	15.48	15.97	16.54
12H	4H	17.73	18.42	18.21	18.90	19.37	14.03	14.72	14.51	15.20	15.67
	6H	18.36	18.94	18.88	19.45	19.94	14.63	15.21	15.15	15.72	16.21
	8H	18.65	19.16	19.16	19.65	20.21	14.91	15.42	15.42	15.91	16.47