

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930620

Luminaire Tested: DFN2DS-PN3F0-090DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930620
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-090DS840-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7657.7 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 97.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930620

CATALOG NUMBER: DFN2DS-PN3F0-090DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930620

CATALOG NUMBER: DFN2DS-PN3F0-090DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4353	4353	4353
5°	4369	4298	4322
10°	4336	4228	4192
15°	4286	4103	3984
20°	4217	3923	3726
25°	4146	3720	3477
30°	4048	3511	3156
35°	3953	3285	2875
40°	3857	3049	2551
45°	3744	2785	2256
50°	3628	2519	1967
55°	3509	2232	1690
60°	3372	1930	1403
65°	3216	1622	1277
70°	3029	1336	1174
75°	2800	1218	1096
80°	2472	1088	998
85°	1941	858	858

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3744 cd/sqm

TEST NUMBER: P930620

CATALOG NUMBER: DFN2DS-PN3F0-090DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.0	4.6
10°-20°	958.0	12.5
20°-30°	1345.0	17.6
30°-40°	1466.1	19.1
40°-50°	1347.5	17.6
50°-60°	1058.3	13.8
60°-70°	688.8	9.0
70°-80°	354.6	4.6
80°-90°	90.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2651.9	34.6
0°-40°	4118.0	53.8
0°-60°	6523.8	85.2
0°-90°	7657.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7657.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3723	3723	3723	3723	3723	
5°	3723	3707	3663	3693	3683	353
15°	3541	3504	3390	3326	3292	998
25°	3215	3107	2884	2746	2696	1478
35°	2770	2598	2302	2089	2015	1734
45°	2264	2038	1685	1445	1365	1749
55°	1722	1459	1095	893	829	1539
65°	1163	890	586	472	462	1153
75°	620	384	270	246	243	656
85°	145	74	64	64	64	174
90°	0	0	0	0	0	

TEST NUMBER: P930620

CATALOG NUMBER: DFN2DS-PN3F0-090DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3723.4	3723.4	3723.4	3723.4	3723.4
2.5°	3740.2	3723.4	3686.2	3720.2	3713.4
5°	3723.4	3706.6	3662.7	3693.0	3683.0
7.5°	3693.0	3673.0	3625.8	3639.0	3622.2
10°	3652.6	3629.0	3561.9	3551.4	3531.4
12.5°	3602.2	3571.9	3480.7	3460.7	3423.4
15°	3541.4	3504.3	3389.9	3325.8	3292.3
17.5°	3470.7	3416.7	3275.1	3201.1	3147.1
20°	3389.9	3322.3	3153.9	3069.9	2995.5
22.5°	3302.3	3224.7	3029.1	2914.7	2864.4
25°	3214.7	3106.7	2884.4	2746.3	2695.6
27.5°	3110.3	2995.5	2749.5	2591.2	2513.6
30°	2999.1	2870.8	2601.2	2429.6	2338.4
32.5°	2891.1	2735.9	2460.0	2257.7	2173.3
35°	2770.0	2598.0	2301.6	2089.3	2014.9
37.5°	2651.9	2466.5	2153.3	1920.5	1836.5
40°	2527.2	2325.2	1998.1	1759.0	1671.4
42.5°	2399.2	2183.7	1843.2	1593.8	1509.7
45°	2264.5	2038.5	1684.9	1445.3	1364.6
47.5°	2136.4	1897.3	1533.3	1293.8	1219.8
50°	1994.9	1755.7	1385.0	1152.3	1081.8
52.5°	1856.6	1603.8	1243.4	1021.0	957.1
55°	1721.7	1459.0	1095.0	893.1	829.0
57.5°	1583.8	1314.2	963.9	775.1	721.1
60°	1442.1	1172.6	825.5	653.9	599.9
62.5°	1304.2	1034.6	707.5	545.9	519.1
65°	1162.6	889.5	586.3	471.9	461.6
67.5°	1027.8	754.7	471.9	414.3	404.3
70°	886.3	623.5	390.8	357.2	343.5
72.5°	751.5	501.9	326.7	299.9	293.2
75°	619.9	384.0	269.6	245.9	242.7
77.5°	488.7	272.8	212.3	198.8	192.0
80°	367.2	195.6	161.6	148.3	148.3
82.5°	256.0	131.5	111.2	104.4	104.4
85°	144.7	74.0	64.0	64.0	64.0
87.5°	54.0	26.8	26.8	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930620

CATALOG NUMBER: DFN2DS-PN3F0-090DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.34	17.87	16.71	18.18	18.49	12.31	13.83	12.67	14.14	14.46
	3H	18.11	19.48	18.49	19.80	20.16	13.57	14.94	13.95	15.26	15.63
	4H	18.78	20.06	19.18	20.41	20.78	14.07	15.35	14.47	15.70	16.08
	6H	19.27	20.45	19.68	20.81	21.21	14.45	15.64	14.87	16.00	16.39
	8H	19.43	20.56	19.86	20.95	21.35	14.58	15.70	15.00	16.09	16.49
	12H	19.53	20.61	19.96	20.99	21.42	14.66	15.74	15.09	16.12	16.55
4H	2H	16.45	17.73	16.85	18.08	18.46	13.00	14.28	13.40	14.63	15.01
	3H	18.38	19.44	18.79	19.84	20.25	14.44	15.51	14.85	15.91	16.31
	4H	19.13	20.09	19.56	20.50	20.94	15.04	16.00	15.48	16.42	16.85
	6H	19.72	20.56	20.18	21.00	21.46	15.53	16.36	15.99	16.81	17.27
	8H	19.94	20.72	20.40	21.16	21.63	15.69	16.47	16.16	16.91	17.38
	12H	20.09	20.79	20.57	21.26	21.74	15.81	16.50	16.29	16.98	17.45
8H	4H	19.16	19.93	19.62	20.38	20.84	15.40	16.17	15.86	16.62	17.09
	6H	19.79	20.44	20.29	20.93	21.40	15.98	16.63	16.48	17.12	17.59
	8H	20.04	20.62	20.56	21.13	21.62	16.20	16.78	16.72	17.29	17.78
	12H	20.25	20.76	20.76	21.25	21.81	16.38	16.89	16.89	17.39	17.95
12H	4H	19.14	19.83	19.62	20.31	20.78	15.44	16.13	15.92	16.61	17.08
	6H	19.77	20.35	20.29	20.86	21.35	16.05	16.62	16.56	17.13	17.62
	8H	20.06	20.57	20.57	21.06	21.63	16.32	16.83	16.83	17.32	17.89