

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930531

Luminaire Tested: DFN2DS-PN3F0-040DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-040DS850-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4391.7 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930531

CATALOG NUMBER: DFN2DS-PN3F0-040DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930531

CATALOG NUMBER: DFN2DS-PN3F0-040DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2018	2018	2018
5°	2025	1996	2008
10°	2014	1976	1986
15°	1989	1950	1948
20°	1953	1912	1910
25°	1918	1865	1865
30°	1873	1821	1806
35°	1831	1769	1743
40°	1778	1717	1684
45°	1726	1665	1624
50°	1669	1612	1554
55°	1610	1549	1492
60°	1544	1475	1420
65°	1474	1400	1336
70°	1384	1310	1248
75°	1259	1207	1177
80°	1117	1083	1028
85°	912	869	779

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1726 cd/sqm

TEST NUMBER: P930531

CATALOG NUMBER: DFN2DS-PN3F0-040DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	3.7
10°-20°	457.1	10.4
20°-30°	671.7	15.3
30°-40°	780.2	17.8
40°-50°	779.2	17.7
50°-60°	679.5	15.5
60°-70°	502.3	11.4
70°-80°	284.2	6.5
80°-90°	75.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.3	29.4
0°-40°	2071.5	47.2
0°-60°	3530.2	80.4
0°-90°	4391.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4391.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930531

CATALOG NUMBER: DFN2DS-PN3F0-040DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930531

CATALOG NUMBER: DFN2DS-PN3F0-040DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.72	15.33	14.09	15.65	15.96	13.28	14.89	13.64	15.20	15.52
	3H	15.47	16.93	15.85	17.25	17.61	14.98	16.44	15.36	16.76	17.12
	4H	16.12	17.49	16.52	17.83	18.21	15.62	16.99	16.02	17.34	17.72
	6H	16.59	17.86	17.00	18.22	18.61	16.09	17.35	16.50	17.72	18.11
	8H	16.73	17.94	17.15	18.33	18.73	16.23	17.44	16.65	17.83	18.23
	12H	16.82	17.98	17.25	18.36	18.79	16.31	17.47	16.74	17.85	18.28
4H	2H	14.28	15.65	14.68	16.00	16.38	13.93	15.30	14.33	15.65	16.02
	3H	16.26	17.40	16.67	17.80	18.20	15.85	17.00	16.26	17.39	17.79
	4H	17.03	18.07	17.47	18.48	18.92	16.61	17.65	17.04	18.06	18.50
	6H	17.63	18.53	18.08	18.98	19.43	17.20	18.10	17.65	18.54	19.00
	8H	17.82	18.67	18.28	19.11	19.57	17.38	18.23	17.84	18.67	19.14
	12H	17.95	18.71	18.43	19.19	19.66	17.50	18.26	17.98	18.74	19.20
8H	4H	17.31	18.15	17.77	18.60	19.06	16.93	17.78	17.39	18.22	18.69
	6H	18.02	18.72	18.51	19.21	19.69	17.64	18.34	18.13	18.83	19.31
	8H	18.28	18.91	18.79	19.42	19.90	17.89	18.52	18.40	19.03	19.51
	12H	18.48	19.04	18.99	19.53	20.09	18.07	18.62	18.57	19.12	19.68
12H	4H	17.33	18.09	17.81	18.57	19.04	16.97	17.73	17.45	18.20	18.67
	6H	18.07	18.70	18.58	19.21	19.69	17.70	18.33	18.21	18.84	19.32
	8H	18.38	18.94	18.89	19.43	19.99	18.00	18.56	18.51	19.05	19.61