

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930121

Luminaire Tested: DFN2DS-HX2F0-060DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS930-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4841.1 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930121

CATALOG NUMBER: DFN2DS-HX2F0-060DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930121

CATALOG NUMBER: DFN2DS-HX2F0-060DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4483	4483	4483
5°	4500	4435	4462
10°	4474	4390	4412
15°	4418	4333	4329
20°	4339	4248	4244
25°	4262	4143	4143
30°	4162	4047	4012
35°	4068	3931	3873
40°	3950	3815	3742
45°	3835	3700	3609
50°	3708	3581	3454
55°	3578	3442	3315
60°	3431	3277	3156
65°	3275	3111	2968
70°	3076	2911	2773
75°	2797	2681	2615
80°	2483	2407	2284
85°	2025	1930	1733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3835 cd/sqm

TEST NUMBER: P930121

CATALOG NUMBER: DFN2DS-HX2F0-060DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	3.7
10°-20°	503.9	10.4
20°-30°	740.5	15.3
30°-40°	860.0	17.8
40°-50°	859.0	17.7
50°-60°	749.0	15.5
60°-70°	553.7	11.4
70°-80°	313.3	6.5
80°-90°	82.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.5	29.4
0°-40°	2283.5	47.2
0°-60°	3891.5	80.4
0°-90°	4841.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4841.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	88
90°	0	0	0	0	0	

TEST NUMBER: P930121

CATALOG NUMBER: DFN2DS-HX2F0-060DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930121

CATALOG NUMBER: DFN2DS-HX2F0-060DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.50	18.11	16.86	18.42	18.73	16.05	17.66	16.42	17.98	18.29
	3H	18.25	19.70	18.62	20.03	20.39	17.75	19.21	18.13	19.54	19.90
	4H	18.89	20.26	19.29	20.61	20.98	18.40	19.77	18.80	20.11	20.49
	6H	19.36	20.63	19.77	20.99	21.38	18.86	20.13	19.27	20.49	20.88
	8H	19.50	20.71	19.93	21.10	21.50	19.00	20.21	19.43	20.60	21.00
	12H	19.59	20.75	20.02	21.14	21.56	19.08	20.24	19.51	20.62	21.05
4H	2H	17.06	18.43	17.45	18.77	19.15	16.70	18.07	17.10	18.42	18.80
	3H	19.03	20.18	19.44	20.58	20.98	18.62	19.77	19.03	20.17	20.57
	4H	19.81	20.84	20.24	21.26	21.69	19.38	20.42	19.81	20.83	21.27
	6H	20.40	21.31	20.86	21.75	22.21	19.97	20.88	20.43	21.32	21.77
	8H	20.59	21.44	21.05	21.88	22.35	20.16	21.00	20.62	21.44	21.91
	12H	20.73	21.49	21.21	21.96	22.43	20.27	21.03	20.75	21.51	21.98
8H	4H	20.08	20.93	20.54	21.37	21.84	19.71	20.55	20.17	21.00	21.46
	6H	20.80	21.50	21.29	21.99	22.46	20.41	21.12	20.91	21.60	22.08
	8H	21.05	21.69	21.56	22.19	22.68	20.66	21.29	21.17	21.80	22.29
	12H	21.25	21.81	21.76	22.30	22.86	20.84	21.40	21.35	21.89	22.45
12H	4H	20.11	20.87	20.59	21.34	21.81	19.74	20.50	20.22	20.98	21.45
	6H	20.84	21.47	21.35	21.98	22.47	20.47	21.10	20.98	21.61	22.10
	8H	21.15	21.71	21.66	22.20	22.76	20.78	21.33	21.28	21.82	22.39