

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930570

Luminaire Tested: DFN2DS-PN3F0-060DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-060DS927-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4039.2 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 61.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930570

CATALOG NUMBER: DFN2DS-PN3F0-060DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930570

CATALOG NUMBER: DFN2DS-PN3F0-060DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2296	2296	2296
5°	2305	2267	2280
10°	2287	2230	2211
15°	2261	2164	2102
20°	2224	2070	1966
25°	2187	1962	1834
30°	2135	1852	1665
35°	2085	1733	1517
40°	2034	1608	1345
45°	1975	1469	1190
50°	1914	1328	1038
55°	1851	1177	891
60°	1778	1018	740
65°	1696	856	674
70°	1598	704	619
75°	1477	642	579
80°	1303	574	526
85°	1023	452	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1975 cd/sqm

TEST NUMBER: P930570

CATALOG NUMBER: DFN2DS-PN3F0-060DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	4.6
10°-20°	505.3	12.5
20°-30°	709.4	17.6
30°-40°	773.3	19.1
40°-50°	710.8	17.6
50°-60°	558.2	13.8
60°-70°	363.3	9.0
70°-80°	187.0	4.6
80°-90°	47.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1398.8	34.6
0°-40°	2172.1	53.8
0°-60°	3441.1	85.2
0°-90°	4039.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4039.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1955	1932	1948	1943	186
15°	1868	1848	1788	1754	1736	526
25°	1696	1639	1521	1449	1422	780
35°	1461	1370	1214	1102	1063	914
45°	1194	1075	889	762	720	922
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	202	142	130	128	346
85°	76	39	34	34	34	92
90°	0	0	0	0	0	

TEST NUMBER: P930570

CATALOG NUMBER: DFN2DS-PN3F0-060DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.0	1964.0	1964.0	1964.0	1964.0
2.5°	1972.9	1964.0	1944.4	1962.3	1958.7
5°	1964.0	1955.1	1931.9	1948.0	1942.7
7.5°	1948.0	1937.4	1912.5	1919.5	1910.6
10°	1926.6	1914.2	1878.8	1873.3	1862.7
12.5°	1900.1	1884.0	1835.9	1825.4	1805.8
15°	1868.0	1848.4	1788.0	1754.3	1736.5
17.5°	1830.7	1802.2	1727.5	1688.5	1660.0
20°	1788.0	1752.4	1663.6	1619.2	1580.0
22.5°	1741.8	1700.9	1597.8	1537.4	1510.8
25°	1695.7	1638.7	1521.4	1448.6	1421.9
27.5°	1640.6	1580.0	1450.3	1366.8	1325.9
30°	1581.9	1514.2	1372.1	1281.5	1233.5
32.5°	1525.0	1443.2	1297.6	1190.9	1146.3
35°	1461.1	1370.4	1214.1	1102.0	1062.8
37.5°	1398.8	1300.9	1135.8	1013.0	968.7
40°	1333.0	1226.5	1053.9	927.7	881.6
42.5°	1265.5	1151.8	972.3	840.6	796.4
45°	1194.4	1075.2	888.8	762.4	719.8
47.5°	1126.9	1000.8	808.8	682.5	643.4
50°	1052.3	926.1	730.5	607.8	570.6
52.5°	979.2	845.9	655.9	538.6	504.8
55°	908.2	769.6	577.6	471.1	437.3
57.5°	835.4	693.2	508.4	408.8	380.3
60°	760.7	618.6	435.4	344.9	316.4
62.5°	687.9	545.8	373.2	288.0	273.8
65°	613.2	469.2	309.3	248.9	243.5
67.5°	542.1	398.1	248.9	218.6	213.3
70°	467.4	328.8	206.1	188.4	181.2
72.5°	396.4	264.8	172.3	158.2	154.6
75°	327.0	202.5	142.2	129.7	128.1
77.5°	257.8	143.9	112.0	104.9	101.3
80°	193.6	103.1	85.2	78.2	78.2
82.5°	135.0	69.4	58.6	55.0	55.0
85°	76.3	39.0	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930570

CATALOG NUMBER: DFN2DS-PN3F0-060DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.12	15.64	14.49	15.96	16.27	10.08	11.60	10.45	11.92	12.23
	3H	15.89	17.25	16.27	17.58	17.94	11.35	12.71	11.73	13.04	13.40
	4H	16.55	17.83	16.95	18.18	18.56	11.85	13.13	12.25	13.48	13.86
	6H	17.04	18.23	17.45	18.59	18.98	12.23	13.41	12.64	13.78	14.17
	8H	17.21	18.33	17.63	18.72	19.13	12.35	13.48	12.78	13.87	14.27
	12H	17.31	18.39	17.74	18.77	19.20	12.44	13.51	12.87	13.90	14.33
4H	2H	14.23	15.51	14.63	15.86	16.23	10.78	12.06	11.18	12.41	12.79
	3H	16.16	17.22	16.57	17.62	18.02	12.22	13.28	12.63	13.68	14.09
	4H	16.91	17.87	17.34	18.28	18.72	12.82	13.78	13.25	14.19	14.63
	6H	17.50	18.33	17.96	18.78	19.23	13.31	14.14	13.77	14.58	15.04
	8H	17.71	18.49	18.18	18.94	19.40	13.47	14.25	13.93	14.69	15.16
	12H	17.87	18.56	18.35	19.04	19.51	13.59	14.28	14.07	14.76	15.23
8H	4H	16.93	17.71	17.40	18.15	18.62	13.17	13.95	13.64	14.40	14.86
	6H	17.57	18.21	18.07	18.70	19.18	13.76	14.40	14.26	14.89	15.37
	8H	17.82	18.40	18.33	18.91	19.40	13.98	14.56	14.50	15.07	15.56
	12H	18.02	18.53	18.53	19.03	19.59	14.16	14.67	14.67	15.16	15.73
12H	4H	16.92	17.61	17.40	18.09	18.56	13.22	13.91	13.70	14.39	14.86
	6H	17.55	18.13	18.06	18.64	19.13	13.82	14.40	14.34	14.91	15.40
	8H	17.84	18.35	18.35	18.84	19.40	14.10	14.61	14.61	15.10	15.66

END OF REPORT