

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930089

Luminaire Tested: DFN2DS-HX2F0-040DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-040DS940-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3532.3 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930089

CATALOG NUMBER: DFN2DS-HX2F0-040DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930089

CATALOG NUMBER: DFN2DS-HX2F0-040DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3271	3271	3271
5°	3284	3236	3255
10°	3264	3204	3220
15°	3224	3162	3159
20°	3166	3100	3097
25°	3110	3023	3023
30°	3037	2953	2927
35°	2968	2869	2826
40°	2883	2784	2731
45°	2798	2700	2633
50°	2706	2613	2520
55°	2611	2512	2419
60°	2504	2391	2302
65°	2389	2270	2166
70°	2244	2125	2023
75°	2041	1956	1908
80°	1811	1756	1666
85°	1479	1408	1262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2798 cd/sqm

TEST NUMBER: P930089

CATALOG NUMBER: DFN2DS-HX2F0-040DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	3.7
10°-20°	367.6	10.4
20°-30°	540.3	15.3
30°-40°	627.5	17.8
40°-50°	626.8	17.7
50°-60°	546.5	15.5
60°-70°	404.0	11.4
70°-80°	228.6	6.5
80°-90°	60.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.6	29.4
0°-40°	1666.2	47.2
0°-60°	2839.4	80.4
0°-90°	3532.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3532.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	64
90°	0	0	0	0	0	

TEST NUMBER: P930089

CATALOG NUMBER: DFN2DS-HX2F0-040DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930089

CATALOG NUMBER: DFN2DS-HX2F0-040DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.40	17.01	15.77	17.33	17.64	14.96	16.57	15.32	16.88	17.19
	3H	17.15	18.61	17.53	18.93	19.29	16.66	18.11	17.04	18.44	18.80
	4H	17.80	19.17	18.20	19.51	19.89	17.30	18.67	17.70	19.02	19.39
	6H	18.27	19.53	18.68	19.90	20.29	17.76	19.03	18.18	19.40	19.79
	8H	18.41	19.62	18.83	20.01	20.41	17.91	19.12	18.33	19.51	19.90
	12H	18.50	19.66	18.93	20.04	20.47	17.99	19.15	18.42	19.53	19.96
4H	2H	15.96	17.33	16.36	17.68	18.05	15.61	16.98	16.01	17.32	17.70
	3H	17.94	19.08	18.35	19.48	19.88	17.53	18.68	17.94	19.07	19.47
	4H	18.71	19.75	19.14	20.16	20.60	18.29	19.32	18.72	19.74	20.17
	6H	19.31	20.21	19.76	20.65	21.11	18.88	19.78	19.33	20.22	20.68
	8H	19.50	20.34	19.96	20.79	21.25	19.06	19.91	19.52	20.35	20.81
	12H	19.63	20.39	20.11	20.87	21.34	19.18	19.94	19.66	20.41	20.88
8H	4H	18.99	19.83	19.45	20.27	20.74	18.61	19.46	19.07	19.90	20.37
	6H	19.70	20.40	20.19	20.89	21.37	19.32	20.02	19.81	20.51	20.98
	8H	19.96	20.59	20.47	21.10	21.58	19.57	20.20	20.08	20.70	21.19
	12H	20.16	20.72	20.67	21.21	21.77	19.75	20.30	20.25	20.79	21.35
12H	4H	19.01	19.77	19.49	20.25	20.72	18.65	19.41	19.13	19.88	20.35
	6H	19.74	20.38	20.25	20.88	21.37	19.38	20.01	19.89	20.52	21.00
	8H	20.06	20.62	20.57	21.11	21.67	19.68	20.24	20.19	20.73	21.29