

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930128

Luminaire Tested: DFN2DS-HX2F0-060DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS950-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4819.5 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930128

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930128

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5521	5521	5521
5°	5542	5452	5482
10°	5500	5363	5317
15°	5437	5204	5054
20°	5349	4977	4727
25°	5260	4719	4411
30°	5135	4454	4004
35°	5014	4167	3647
40°	4892	3868	3235
45°	4749	3534	2862
50°	4602	3195	2496
55°	4451	2831	2143
60°	4277	2449	1779
65°	4079	2057	1620
70°	3842	1694	1489
75°	3552	1544	1391
80°	3136	1380	1267
85°	2463	1089	1089

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4749 cd/sqm

TEST NUMBER: P930128

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.6	4.6
10°-20°	602.9	12.5
20°-30°	846.5	17.6
30°-40°	922.7	19.1
40°-50°	848.1	17.6
50°-60°	666.0	13.8
60°-70°	433.5	9.0
70°-80°	223.2	4.6
80°-90°	57.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1669.0	34.6
0°-40°	2591.7	53.8
0°-60°	4105.8	85.2
0°-90°	4819.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4819.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2343	2343	2343	2343	2343	
5°	2343	2333	2305	2324	2318	222
15°	2229	2205	2133	2093	2072	628
25°	2023	1955	1815	1728	1697	930
35°	1743	1635	1449	1315	1268	1091
45°	1425	1283	1060	910	859	1101
55°	1084	918	689	562	522	968
65°	732	560	369	297	290	725
75°	390	242	170	155	153	413
85°	91	47	40	40	40	109
90°	0	0	0	0	0	

TEST NUMBER: P930128

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2343.4	2343.4	2343.4	2343.4	2343.4
2.5°	2354.0	2343.4	2320.0	2341.3	2337.1
5°	2343.4	2332.8	2305.1	2324.3	2318.0
7.5°	2324.3	2311.7	2282.0	2290.3	2279.7
10°	2298.8	2284.0	2241.7	2235.2	2222.5
12.5°	2267.1	2248.0	2190.6	2178.0	2154.6
15°	2228.9	2205.4	2133.4	2093.2	2072.0
17.5°	2184.4	2150.3	2061.2	2014.6	1980.7
20°	2133.4	2090.9	1985.0	1932.1	1885.3
22.5°	2078.3	2029.5	1906.4	1834.4	1802.7
25°	2023.2	1955.3	1815.3	1728.5	1696.6
27.5°	1957.6	1885.3	1730.5	1630.8	1582.0
30°	1887.5	1806.7	1637.1	1529.1	1471.7
32.5°	1819.6	1722.0	1548.3	1420.9	1367.8
35°	1743.3	1635.1	1448.6	1314.9	1268.1
37.5°	1669.1	1552.3	1355.2	1208.7	1155.8
40°	1590.5	1463.4	1257.5	1107.0	1051.9
42.5°	1510.0	1374.3	1160.1	1003.0	950.2
45°	1425.2	1282.9	1060.5	909.7	858.8
47.5°	1344.6	1194.1	965.0	814.3	767.7
50°	1255.5	1105.0	871.7	725.2	680.9
52.5°	1168.4	1009.4	782.6	642.6	602.3
55°	1083.6	918.3	689.2	562.1	521.7
57.5°	996.8	827.1	606.6	487.8	453.8
60°	907.7	738.0	519.6	411.5	377.5
62.5°	820.8	651.2	445.3	343.6	326.7
65°	731.7	559.8	369.0	297.0	290.5
67.5°	646.9	475.0	297.0	260.8	254.5
70°	557.7	392.4	245.9	224.8	216.2
72.5°	473.0	315.9	205.6	188.8	184.5
75°	390.2	241.6	169.6	154.8	152.8
77.5°	307.6	171.7	133.6	125.1	120.9
80°	231.1	123.0	101.7	93.4	93.4
82.5°	161.1	82.8	69.9	65.7	65.7
85°	91.1	46.6	40.3	40.3	40.3
87.5°	34.0	16.9	16.9	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930128

CATALOG NUMBER: DFN2DS-HX2F0-060DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.17	18.69	17.54	19.01	19.32	13.13	14.65	13.50	14.97	15.28
	3H	18.94	20.30	19.31	20.63	20.99	14.40	15.76	14.77	16.09	16.45
	4H	19.60	20.88	20.00	21.23	21.61	14.90	16.18	15.30	16.53	16.91
	6H	20.09	21.27	20.50	21.64	22.03	15.28	16.46	15.69	16.83	17.22
	8H	20.26	21.38	20.68	21.77	22.17	15.40	16.53	15.83	16.92	17.32
	12H	20.36	21.44	20.79	21.82	22.25	15.49	16.56	15.92	16.95	17.38
4H	2H	17.28	18.56	17.67	18.90	19.28	13.83	15.11	14.23	15.46	15.83
	3H	19.21	20.27	19.62	20.67	21.07	15.27	16.33	15.68	16.73	17.13
	4H	19.96	20.91	20.39	21.33	21.77	15.87	16.83	16.30	17.24	17.68
	6H	20.55	21.38	21.01	21.82	22.28	16.36	17.19	16.82	17.63	18.09
	8H	20.76	21.54	21.23	21.99	22.45	16.52	17.30	16.98	17.74	18.21
	12H	20.92	21.61	21.40	22.09	22.56	16.64	17.33	17.12	17.81	18.28
8H	4H	19.98	20.76	20.45	21.20	21.67	16.22	17.00	16.69	17.44	17.91
	6H	20.62	21.26	21.12	21.75	22.23	16.81	17.45	17.31	17.94	18.42
	8H	20.87	21.45	21.38	21.96	22.44	17.03	17.61	17.55	18.12	18.61
	12H	21.07	21.58	21.58	22.08	22.64	17.21	17.72	17.72	18.21	18.78
12H	4H	19.97	20.66	20.45	21.14	21.61	16.27	16.96	16.75	17.44	17.91
	6H	20.60	21.18	21.11	21.69	22.18	16.87	17.45	17.39	17.96	18.45
	8H	20.88	21.39	21.39	21.89	22.45	17.15	17.66	17.66	18.15	18.71