

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930625

Luminaire Tested: DFN2DS-PN3F0-090DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-090DS930-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7261.7 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 97.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930625

CATALOG NUMBER: DFN2DS-PN3F0-090DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930625

CATALOG NUMBER: DFN2DS-PN3F0-090DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3336	3336	3336
5°	3349	3301	3320
10°	3329	3267	3284
15°	3288	3225	3222
20°	3230	3161	3158
25°	3172	3083	3083
30°	3097	3012	2986
35°	3028	2926	2883
40°	2940	2839	2785
45°	2854	2754	2686
50°	2760	2665	2570
55°	2663	2562	2467
60°	2554	2438	2349
65°	2437	2315	2209
70°	2289	2167	2064
75°	2082	1995	1947
80°	1849	1791	1700
85°	1508	1438	1289

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2854 cd/sqm

TEST NUMBER: P930625

CATALOG NUMBER: DFN2DS-PN3F0-090DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	3.7
10°-20°	755.8	10.4
20°-30°	1110.7	15.3
30°-40°	1290.1	17.8
40°-50°	1288.5	17.7
50°-60°	1123.5	15.5
60°-70°	830.5	11.4
70°-80°	469.9	6.5
80°-90°	124.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2135.2	29.4
0°-40°	3425.3	47.2
0°-60°	5837.3	80.4
0°-90°	7261.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7261.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2854	2854	2854	2854	2854	
5°	2854	2843	2813	2835	2830	271
15°	2717	2701	2665	2676	2662	765
25°	2459	2437	2391	2396	2391	1131
35°	2122	2094	2050	2034	2020	1325
45°	1726	1707	1666	1636	1625	1332
55°	1306	1290	1257	1224	1210	1168
65°	881	864	837	812	799	871
75°	461	456	442	425	431	492
85°	112	110	107	99	96	132
90°	0	0	0	0	0	

TEST NUMBER: P930625

CATALOG NUMBER: DFN2DS-PN3F0-090DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2854.0	2854.0	2854.0	2854.0	2854.0
2.5°	2870.7	2857.0	2826.7	2854.0	2848.8
5°	2854.0	2843.3	2813.1	2834.9	2829.6
7.5°	2834.9	2818.6	2788.3	2810.4	2804.9
10°	2804.9	2785.7	2752.7	2774.6	2766.4
12.5°	2763.5	2747.2	2714.4	2728.0	2722.5
15°	2717.0	2700.7	2664.8	2675.9	2662.2
17.5°	2659.3	2643.0	2607.2	2620.9	2607.2
20°	2596.1	2579.8	2541.3	2549.5	2538.7
22.5°	2533.2	2508.5	2472.6	2472.6	2467.1
25°	2458.9	2437.1	2390.6	2395.8	2390.6
27.5°	2376.5	2357.3	2321.9	2313.7	2300.0
30°	2294.5	2272.3	2231.2	2223.1	2212.1
32.5°	2206.5	2190.2	2146.2	2129.7	2118.6
35°	2121.5	2094.1	2050.1	2033.6	2019.9
37.5°	2025.4	2000.7	1956.7	1937.5	1923.8
40°	1926.7	1904.6	1860.6	1836.1	1825.1
42.5°	1830.6	1808.5	1764.8	1737.2	1720.9
45°	1726.3	1707.2	1665.8	1635.8	1624.8
47.5°	1624.8	1605.6	1561.5	1531.3	1515.0
50°	1517.6	1503.9	1465.5	1427.1	1413.4
52.5°	1413.4	1394.1	1358.6	1328.4	1309.1
55°	1306.5	1289.9	1257.0	1224.1	1210.4
57.5°	1199.4	1185.7	1149.9	1117.0	1105.9
60°	1092.2	1081.4	1043.0	1012.7	1004.6
62.5°	987.9	968.7	941.3	914.0	902.9
65°	881.1	864.5	837.1	812.4	798.7
67.5°	771.3	757.4	732.8	713.7	702.6
70°	669.7	658.6	633.9	614.7	603.9
72.5°	565.4	554.4	540.7	521.5	513.4
75°	461.0	455.7	441.7	425.4	431.0
77.5°	367.7	356.7	351.2	343.0	334.9
80°	274.6	271.6	266.1	257.9	252.5
82.5°	186.6	186.6	184.0	172.9	172.9
85°	112.4	109.8	107.2	98.7	96.1
87.5°	49.5	43.9	38.5	30.3	27.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930625

CATALOG NUMBER: DFN2DS-PN3F0-090DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	17.08	15.83	17.39	17.71	15.02	16.64	15.39	16.95	17.26
	3H	17.22	18.67	17.60	19.00	19.36	16.73	18.18	17.10	18.51	18.87
	4H	17.87	19.23	18.26	19.58	19.96	17.37	18.74	17.77	19.09	19.46
	6H	18.33	19.60	18.75	19.97	20.36	17.83	19.10	18.24	19.47	19.86
	8H	18.48	19.69	18.90	20.08	20.48	17.97	19.19	18.40	19.57	19.97
	12H	18.57	19.73	19.00	20.11	20.54	18.06	19.22	18.49	19.60	20.03
4H	2H	16.03	17.40	16.43	17.75	18.12	15.68	17.05	16.07	17.39	17.77
	3H	18.00	19.15	18.41	19.55	19.95	17.60	18.74	18.01	19.14	19.54
	4H	18.78	19.82	19.21	20.23	20.67	18.36	19.39	18.79	19.81	20.24
	6H	19.38	20.28	19.83	20.72	21.18	18.95	19.85	19.40	20.29	20.75
	8H	19.57	20.41	20.03	20.86	21.32	19.13	19.98	19.59	20.42	20.88
	12H	19.70	20.46	20.18	20.93	21.40	19.25	20.01	19.73	20.48	20.95
8H	4H	19.05	19.90	19.51	20.34	20.81	18.68	19.53	19.14	19.97	20.43
	6H	19.77	20.47	20.26	20.96	21.44	19.39	20.09	19.88	20.58	21.05
	8H	20.03	20.66	20.54	21.17	21.65	19.64	20.27	20.15	20.77	21.26
	12H	20.23	20.79	20.73	21.28	21.84	19.81	20.37	20.32	20.86	21.42
12H	4H	19.08	19.84	19.56	20.32	20.79	18.72	19.48	19.20	19.95	20.42
	6H	19.81	20.45	20.32	20.95	21.44	19.45	20.08	19.95	20.58	21.07
	8H	20.13	20.69	20.63	21.18	21.74	19.75	20.31	20.26	20.80	21.36