

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930555

Luminaire Tested: DFN2DS-PN3F0-050DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS935-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930555

CATALOG NUMBER: DFN2DS-PN3F0-050DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930555

CATALOG NUMBER: DFN2DS-PN3F0-050DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1956	1956	1956
5°	1963	1935	1947
10°	1952	1916	1925
15°	1928	1891	1889
20°	1893	1853	1851
25°	1859	1808	1808
30°	1816	1766	1750
35°	1775	1715	1690
40°	1724	1664	1633
45°	1673	1614	1574
50°	1618	1562	1507
55°	1561	1502	1446
60°	1497	1430	1377
65°	1429	1357	1295
70°	1342	1270	1210
75°	1220	1169	1141
80°	1084	1050	996
85°	884	842	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1673 cd/sqm

TEST NUMBER: P930555

CATALOG NUMBER: DFN2DS-PN3F0-050DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.7
10°-20°	443.1	10.4
20°-30°	651.1	15.3
30°-40°	756.3	17.8
40°-50°	755.3	17.7
50°-60°	658.6	15.5
60°-70°	486.9	11.4
70°-80°	275.5	6.5
80°-90°	72.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1251.7	29.4
0°-40°	2008.0	47.2
0°-60°	3421.9	80.4
0°-90°	4257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1673	1673	1673	1673	1673	
5°	1673	1667	1649	1662	1659	159
15°	1593	1583	1562	1569	1561	449
25°	1442	1429	1401	1404	1401	663
35°	1244	1228	1202	1192	1184	777
45°	1012	1001	976	959	952	781
55°	766	756	737	718	710	685
65°	516	507	491	476	468	511
75°	270	267	259	249	253	288
85°	66	64	63	58	56	77
90°	0	0	0	0	0	

TEST NUMBER: P930555

CATALOG NUMBER: DFN2DS-PN3F0-050DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1673.1	1673.1	1673.1	1673.1	1673.1
2.5°	1682.8	1674.8	1657.1	1673.1	1670.1
5°	1673.1	1666.9	1649.0	1661.9	1658.9
7.5°	1661.9	1652.3	1634.6	1647.6	1644.3
10°	1644.3	1633.1	1613.8	1626.5	1621.8
12.5°	1620.1	1610.5	1591.3	1599.3	1596.0
15°	1592.7	1583.2	1562.2	1568.7	1560.6
17.5°	1558.9	1549.4	1528.4	1536.4	1528.4
20°	1521.9	1512.4	1489.9	1494.6	1488.3
22.5°	1485.0	1470.5	1449.5	1449.5	1446.3
25°	1441.5	1428.7	1401.4	1404.5	1401.4
27.5°	1393.2	1381.9	1361.1	1356.3	1348.3
30°	1345.0	1332.1	1308.1	1303.2	1296.8
32.5°	1293.5	1284.0	1258.2	1248.5	1242.0
35°	1243.6	1227.6	1201.8	1192.1	1184.1
37.5°	1187.3	1172.9	1147.1	1135.8	1127.8
40°	1129.5	1116.5	1090.7	1076.4	1069.9
42.5°	1073.2	1060.2	1034.6	1018.3	1008.8
45°	1012.0	1000.8	976.5	959.0	952.4
47.5°	952.4	941.2	915.5	897.7	888.1
50°	889.7	881.7	859.1	836.6	828.5
52.5°	828.5	817.3	796.4	778.7	767.5
55°	765.9	756.2	736.8	717.6	709.6
57.5°	703.0	695.1	674.1	654.8	648.3
60°	640.3	634.0	611.5	593.7	588.9
62.5°	579.2	567.9	551.9	535.8	529.3
65°	516.5	506.8	490.7	476.3	468.2
67.5°	452.2	444.0	429.7	418.4	411.9
70°	392.6	386.1	371.6	360.3	354.1
72.5°	331.5	325.0	317.0	305.7	300.9
75°	270.2	267.1	258.9	249.4	252.7
77.5°	215.6	209.1	205.9	201.1	196.3
80°	161.0	159.3	156.0	151.3	148.0
82.5°	109.4	109.4	107.8	101.4	101.4
85°	65.9	64.3	62.8	57.9	56.3
87.5°	29.0	25.8	22.5	17.7	16.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930555

CATALOG NUMBER: DFN2DS-PN3F0-050DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.61	15.22	13.98	15.54	15.85	13.17	14.78	13.53	15.09	15.41
	3H	15.36	16.82	15.74	17.14	17.51	14.87	16.33	15.25	16.65	17.01
	4H	16.01	17.38	16.41	17.73	18.10	15.52	16.88	15.91	17.23	17.61
	6H	16.48	17.75	16.89	18.11	18.50	15.98	17.25	16.39	17.61	18.00
	8H	16.62	17.83	17.05	18.22	18.62	16.12	17.33	16.54	17.72	18.12
	12H	16.71	17.87	17.14	18.25	18.68	16.20	17.36	16.63	17.74	18.17
4H	2H	14.17	15.54	14.57	15.89	16.27	13.82	15.19	14.22	15.54	15.91
	3H	16.15	17.30	16.56	17.69	18.09	15.74	16.89	16.15	17.29	17.69
	4H	16.93	17.96	17.36	18.37	18.81	16.50	17.54	16.93	17.95	18.39
	6H	17.52	18.43	17.98	18.87	19.32	17.09	17.99	17.54	18.44	18.89
	8H	17.71	18.56	18.17	19.00	19.47	17.27	18.12	17.73	18.56	19.03
	12H	17.84	18.60	18.32	19.08	19.55	17.39	18.15	17.87	18.63	19.10
8H	4H	17.20	18.05	17.66	18.49	18.95	16.82	17.67	17.29	18.11	18.58
	6H	17.91	18.62	18.41	19.10	19.58	17.53	18.23	18.03	18.72	19.20
	8H	18.17	18.80	18.68	19.31	19.80	17.78	18.41	18.29	18.92	19.40
	12H	18.37	18.93	18.88	19.42	19.98	17.96	18.52	18.47	19.01	19.57
12H	4H	17.22	17.98	17.70	18.46	18.93	16.86	17.62	17.34	18.10	18.57
	6H	17.96	18.59	18.47	19.10	19.58	17.59	18.22	18.10	18.73	19.21
	8H	18.27	18.83	18.78	19.32	19.88	17.89	18.45	18.40	18.94	19.50

END OF REPORT