

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930147

Luminaire Tested: DFN2DS-HX3F0-040DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-040DS830-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3730.3 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930147

CATALOG NUMBER: DFN2DS-HX3F0-040DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930147

CATALOG NUMBER: DFN2DS-HX3F0-040DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1698	1698	1698
5°	1705	1680	1690
10°	1695	1663	1672
15°	1674	1642	1640
20°	1644	1609	1608
25°	1614	1570	1570
30°	1576	1533	1520
35°	1541	1489	1467
40°	1497	1445	1418
45°	1453	1402	1367
50°	1405	1357	1308
55°	1356	1304	1256
60°	1300	1241	1195
65°	1241	1179	1125
70°	1165	1103	1051
75°	1060	1015	991
80°	941	912	865
85°	767	731	657

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1453 cd/sqm

TEST NUMBER: P930147

CATALOG NUMBER: DFN2DS-HX3F0-040DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	3.7
10°-20°	388.3	10.4
20°-30°	570.6	15.3
30°-40°	662.7	17.8
40°-50°	661.9	17.7
50°-60°	577.1	15.5
60°-70°	426.6	11.4
70°-80°	241.4	6.5
80°-90°	63.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.8	29.4
0°-40°	1759.5	47.2
0°-60°	2998.6	80.4
0°-90°	3730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3730.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1461	1445	1456	1454	139
15°	1396	1387	1369	1375	1368	393
25°	1263	1252	1228	1231	1228	581
35°	1090	1076	1053	1045	1038	681
45°	887	877	856	840	835	684
55°	671	663	646	629	622	600
65°	453	444	430	417	410	447
75°	237	234	227	218	221	253
85°	58	56	55	51	49	68
90°	0	0	0	0	0	

TEST NUMBER: P930147

CATALOG NUMBER: DFN2DS-HX3F0-040DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.1	1466.1	1466.1	1466.1	1466.1
2.5°	1474.7	1467.6	1452.1	1466.1	1463.5
5°	1466.1	1460.6	1445.0	1456.2	1453.6
7.5°	1456.2	1447.9	1432.3	1443.7	1440.9
10°	1440.9	1431.0	1414.1	1425.3	1421.1
12.5°	1419.6	1411.2	1394.3	1401.4	1398.5
15°	1395.7	1387.3	1368.9	1374.6	1367.6
17.5°	1366.1	1357.7	1339.3	1346.3	1339.3
20°	1333.6	1325.2	1305.5	1309.7	1304.2
22.5°	1301.3	1288.6	1270.2	1270.2	1267.4
25°	1263.1	1251.9	1228.0	1230.7	1228.0
27.5°	1220.8	1210.9	1192.8	1188.5	1181.6
30°	1178.6	1167.3	1146.2	1142.0	1136.3
32.5°	1133.5	1125.1	1102.5	1094.0	1088.3
35°	1089.8	1075.8	1053.2	1044.7	1037.6
37.5°	1040.4	1027.7	1005.1	995.3	988.3
40°	989.8	978.4	955.8	943.2	937.6
42.5°	940.4	929.0	906.6	892.4	884.0
45°	886.8	877.0	855.7	840.4	834.6
47.5°	834.6	824.7	802.2	786.7	778.3
50°	779.6	772.5	752.8	733.1	726.0
52.5°	726.0	716.2	697.9	682.4	672.5
55°	671.2	662.6	645.7	628.8	621.8
57.5°	616.1	609.1	590.6	573.8	568.1
60°	561.1	555.5	535.8	520.3	516.0
62.5°	507.5	497.7	483.6	469.5	463.8
65°	452.6	444.1	430.0	417.3	410.3
67.5°	396.2	389.0	376.5	366.6	361.0
70°	344.0	338.4	325.6	315.8	310.2
72.5°	290.5	284.8	277.8	267.9	263.7
75°	236.8	234.1	226.9	218.5	221.4
77.5°	188.9	183.2	180.4	176.2	172.0
80°	141.0	139.5	136.7	132.5	129.7
82.5°	95.9	95.9	94.6	88.8	88.8
85°	57.7	56.4	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.5	14.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930147

CATALOG NUMBER: DFN2DS-HX3F0-040DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.12	14.73	13.49	15.05	15.36	12.68	14.29	13.04	14.60	14.92
	3H	14.87	16.33	15.25	16.65	17.01	14.38	15.84	14.76	16.16	16.52
	4H	15.52	16.89	15.92	17.24	17.61	15.02	16.39	15.42	16.74	17.12
	6H	15.99	17.26	16.40	17.62	18.01	15.49	16.76	15.90	17.12	17.51
	8H	16.13	17.34	16.56	17.73	18.13	15.63	16.84	16.05	17.23	17.63
	12H	16.22	17.38	16.65	17.76	18.19	15.71	16.87	16.14	17.25	17.68
4H	2H	13.68	15.05	14.08	15.40	15.78	13.33	14.70	13.73	15.05	15.42
	3H	15.66	16.80	16.07	17.20	17.60	15.25	16.40	15.66	16.80	17.20
	4H	16.43	17.47	16.87	17.88	18.32	16.01	17.05	16.44	17.46	17.90
	6H	17.03	17.94	17.49	18.38	18.83	16.60	17.50	17.05	17.94	18.40
	8H	17.22	18.07	17.68	18.51	18.97	16.78	17.63	17.24	18.07	18.54
	12H	17.35	18.11	17.83	18.59	19.06	16.90	17.66	17.38	18.14	18.61
8H	4H	16.71	17.55	17.17	18.00	18.46	16.33	17.18	16.79	17.62	18.09
	6H	17.42	18.13	17.92	18.61	19.09	17.04	17.74	17.53	18.23	18.71
	8H	17.68	18.31	18.19	18.82	19.31	17.29	17.92	17.80	18.43	18.91
	12H	17.88	18.44	18.39	18.93	19.49	17.47	18.03	17.98	18.52	19.08
12H	4H	16.73	17.49	17.21	17.97	18.44	16.37	17.13	16.85	17.61	18.07
	6H	17.47	18.10	17.98	18.61	19.09	17.10	17.73	17.61	18.24	18.72
	8H	17.78	18.34	18.29	18.83	19.39	17.40	17.96	17.91	18.45	19.01