

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930574

Luminaire Tested: DFN2DS-PN3F0-060DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-060DS935-RLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4386.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 61.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930574

CATALOG NUMBER: DFN2DS-PN3F0-060DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930574

CATALOG NUMBER: DFN2DS-PN3F0-060DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2493	2493	2493
5°	2502	2462	2475
10°	2483	2422	2401
15°	2455	2350	2282
20°	2415	2247	2134
25°	2375	2131	1991
30°	2319	2011	1808
35°	2264	1881	1647
40°	2209	1746	1461
45°	2144	1595	1292
50°	2078	1443	1127
55°	2010	1278	968
60°	1931	1105	803
65°	1842	929	731
70°	1735	765	673
75°	1604	697	628
80°	1416	623	572
85°	1112	491	491

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2144 cd/sqm

TEST NUMBER: P930574

CATALOG NUMBER: DFN2DS-PN3F0-060DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	4.6
10°-20°	548.7	12.5
20°-30°	770.3	17.6
30°-40°	839.7	19.1
40°-50°	771.8	17.6
50°-60°	606.1	13.8
60°-70°	394.5	9.0
70°-80°	203.1	4.6
80°-90°	51.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.9	34.6
0°-40°	2358.6	53.8
0°-60°	3736.5	85.2
0°-90°	4386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2133	2133	2133	2133	2133	
5°	2133	2123	2098	2115	2110	202
15°	2028	2007	1942	1905	1886	572
25°	1841	1779	1652	1573	1544	847
35°	1586	1488	1318	1197	1154	993
45°	1297	1168	965	828	782	1002
55°	986	836	627	512	475	881
65°	666	510	336	270	264	660
75°	355	220	154	141	139	376
85°	83	42	37	37	37	99
90°	0	0	0	0	0	

TEST NUMBER: P930574

CATALOG NUMBER: DFN2DS-PN3F0-060DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2132.6	2132.6	2132.6	2132.6	2132.6
2.5°	2142.3	2132.6	2111.3	2130.7	2126.9
5°	2132.6	2123.0	2097.8	2115.3	2109.5
7.5°	2115.3	2103.7	2076.7	2084.3	2074.7
10°	2092.0	2078.5	2040.1	2034.2	2022.6
12.5°	2063.2	2045.8	1993.6	1982.1	1960.8
15°	2028.4	2007.1	1941.5	1904.9	1885.6
17.5°	1987.9	1956.9	1875.8	1833.4	1802.6
20°	1941.5	1902.8	1806.4	1758.3	1715.7
22.5°	1891.4	1846.9	1735.0	1669.4	1640.5
25°	1841.3	1779.4	1652.1	1573.0	1544.0
27.5°	1781.5	1715.7	1574.8	1484.1	1439.7
30°	1717.8	1644.2	1489.9	1391.6	1339.4
32.5°	1655.9	1567.1	1409.0	1293.1	1244.8
35°	1586.5	1488.1	1318.3	1196.6	1154.0
37.5°	1518.9	1412.6	1233.3	1100.0	1051.9
40°	1447.5	1331.8	1144.4	1007.4	957.3
42.5°	1374.2	1250.7	1055.7	912.8	864.7
45°	1297.0	1167.5	965.1	827.8	781.6
47.5°	1223.7	1086.7	878.2	741.1	698.7
50°	1142.6	1005.6	793.3	660.0	619.6
52.5°	1063.3	918.6	712.2	584.8	548.2
55°	986.2	835.7	627.2	511.5	474.8
57.5°	907.1	752.7	552.0	443.9	413.0
60°	826.0	671.7	472.8	374.5	343.6
62.5°	747.0	592.6	405.2	312.7	297.3
65°	665.9	509.5	335.8	270.3	264.4
67.5°	588.7	432.2	270.3	237.4	231.6
70°	507.6	357.1	223.8	204.6	196.8
72.5°	430.4	287.5	187.1	171.8	167.9
75°	355.1	219.9	154.4	140.9	139.1
77.5°	279.9	156.3	121.6	113.9	110.0
80°	210.3	112.0	92.5	85.0	85.0
82.5°	146.6	75.3	63.6	59.8	59.8
85°	82.9	42.4	36.6	36.6	36.6
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930574

CATALOG NUMBER: DFN2DS-PN3F0-060DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.41	15.93	14.77	16.24	16.56	10.37	11.89	10.73	12.20	12.52
	3H	16.17	17.54	16.55	17.87	18.23	11.63	13.00	12.01	13.33	13.69
	4H	16.84	18.12	17.24	18.47	18.85	12.14	13.42	12.54	13.77	14.14
	6H	17.33	18.51	17.74	18.88	19.27	12.52	13.70	12.93	14.07	14.46
	8H	17.49	18.62	17.92	19.01	19.41	12.64	13.77	13.07	14.16	14.56
	12H	17.60	18.68	18.03	19.06	19.49	12.72	13.80	13.15	14.18	14.61
4H	2H	14.51	15.79	14.91	16.14	16.52	11.06	12.34	11.46	12.69	13.07
	3H	16.45	17.51	16.86	17.91	18.31	12.51	13.57	12.92	13.97	14.37
	4H	17.20	18.15	17.63	18.57	19.01	13.11	14.06	13.54	14.48	14.92
	6H	17.79	18.62	18.24	19.06	19.52	13.60	14.43	14.05	14.87	15.33
	8H	18.00	18.78	18.46	19.22	19.69	13.76	14.54	14.22	14.98	15.45
	12H	18.15	18.85	18.64	19.33	19.80	13.87	14.57	14.36	15.05	15.52
8H	4H	17.22	18.00	17.68	18.44	18.91	13.46	14.24	13.92	14.68	15.15
	6H	17.86	18.50	18.35	18.99	19.47	14.05	14.69	14.54	15.18	15.66
	8H	18.11	18.68	18.62	19.19	19.68	14.27	14.85	14.78	15.36	15.84
	12H	18.31	18.82	18.82	19.31	19.88	14.45	14.96	14.96	15.45	16.01
12H	4H	17.20	17.90	17.69	18.38	18.85	13.50	14.20	13.99	14.68	15.15
	6H	17.84	18.42	18.35	18.92	19.41	14.11	14.69	14.62	15.20	15.69
	8H	18.12	18.63	18.63	19.12	19.69	14.38	14.89	14.89	15.39	15.95

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7