

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930575

Luminaire Tested: DFN2DS-PN3F0-060DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-060DS940-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5298.4 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 61.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930575

CATALOG NUMBER: DFN2DS-PN3F0-060DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930575

CATALOG NUMBER: DFN2DS-PN3F0-060DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2434	2434	2434
5°	2444	2409	2423
10°	2429	2384	2396
15°	2399	2353	2351
20°	2357	2307	2304
25°	2314	2250	2250
30°	2260	2198	2179
35°	2209	2135	2103
40°	2145	2072	2032
45°	2083	2009	1960
50°	2014	1945	1875
55°	1943	1869	1800
60°	1863	1779	1714
65°	1778	1690	1612
70°	1670	1581	1506
75°	1519	1456	1420
80°	1348	1307	1240
85°	1100	1048	940

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2083 cd/sqm

TEST NUMBER: P930575

CATALOG NUMBER: DFN2DS-PN3F0-060DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	3.7
10°-20°	551.5	10.4
20°-30°	810.5	15.3
30°-40°	941.3	17.8
40°-50°	940.1	17.7
50°-60°	819.8	15.5
60°-70°	606.0	11.4
70°-80°	342.9	6.5
80°-90°	90.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1558.0	29.4
0°-40°	2499.3	47.2
0°-60°	4259.1	80.4
0°-90°	5298.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5298.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2075	2052	2068	2065	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	826
35°	1548	1528	1496	1484	1474	967
45°	1260	1246	1215	1194	1186	972
55°	953	941	917	893	883	852
65°	643	631	611	593	583	636
75°	336	332	322	310	314	359
85°	82	80	78	72	70	96
90°	0	0	0	0	0	

TEST NUMBER: P930575

CATALOG NUMBER: DFN2DS-PN3F0-060DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2082.5	2082.5	2082.5	2082.5	2082.5
2.5°	2094.6	2084.6	2062.5	2082.5	2078.6
5°	2082.5	2074.6	2052.5	2068.5	2064.6
7.5°	2068.5	2056.6	2034.5	2050.6	2046.6
10°	2046.6	2032.6	2008.5	2024.5	2018.5
12.5°	2016.5	2004.5	1980.5	1990.5	1986.5
15°	1982.4	1970.5	1944.4	1952.5	1942.5
17.5°	1940.4	1928.5	1902.4	1912.3	1902.4
20°	1894.3	1882.4	1854.3	1860.3	1852.4
22.5°	1848.4	1830.3	1804.2	1804.2	1800.1
25°	1794.2	1778.3	1744.2	1748.1	1744.2
27.5°	1734.0	1720.0	1694.1	1688.2	1678.2
30°	1674.2	1658.0	1628.1	1622.1	1614.0
32.5°	1610.0	1598.1	1566.0	1553.9	1545.8
35°	1548.0	1528.0	1495.9	1483.8	1473.8
37.5°	1477.9	1459.8	1427.7	1413.6	1403.7
40°	1405.8	1389.6	1357.6	1339.8	1331.7
42.5°	1335.7	1319.5	1287.7	1267.5	1255.6
45°	1259.7	1245.6	1215.4	1193.6	1185.5
47.5°	1185.5	1171.5	1139.4	1117.3	1105.4
50°	1107.3	1097.3	1069.3	1041.2	1031.2
52.5°	1031.2	1017.2	991.3	969.2	955.2
55°	953.3	941.1	917.2	893.2	883.2
57.5°	875.1	865.2	839.0	815.0	806.9
60°	796.9	789.1	761.1	738.9	733.0
62.5°	720.8	706.8	686.8	666.9	658.8
65°	642.9	630.8	610.8	592.7	582.7
67.5°	562.8	552.6	534.8	520.7	512.6
70°	488.6	480.6	462.5	448.5	440.6
72.5°	412.6	404.5	394.5	380.5	374.6
75°	336.3	332.5	322.3	310.4	314.4
77.5°	268.3	260.3	256.2	250.3	244.3
80°	200.3	198.2	194.2	188.2	184.2
82.5°	136.2	136.2	134.2	126.2	126.2
85°	82.0	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930575

CATALOG NUMBER: DFN2DS-PN3F0-060DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.37	15.98	14.74	16.30	16.61	13.93	15.54	14.29	15.85	16.17
	3H	16.12	17.58	16.50	17.91	18.27	15.63	17.09	16.01	17.41	17.77
	4H	16.77	18.14	17.17	18.49	18.86	16.28	17.64	16.67	17.99	18.37
	6H	17.24	18.51	17.65	18.87	19.26	16.74	18.01	17.15	18.37	18.76
	8H	17.38	18.59	17.81	18.98	19.38	16.88	18.09	17.30	18.48	18.88
	12H	17.47	18.63	17.90	19.01	19.44	16.96	18.12	17.39	18.50	18.93
4H	2H	14.93	16.30	15.33	16.65	17.03	14.58	15.95	14.98	16.30	16.67
	3H	16.91	18.06	17.32	18.45	18.85	16.50	17.65	16.91	18.05	18.45
	4H	17.69	18.72	18.12	19.14	19.57	17.26	18.30	17.69	18.71	19.15
	6H	18.28	19.19	18.74	19.63	20.08	17.85	18.75	18.30	19.20	19.65
	8H	18.47	19.32	18.93	19.76	20.23	18.03	18.88	18.49	19.32	19.79
	12H	18.60	19.36	19.08	19.84	20.31	18.15	18.91	18.63	19.39	19.86
8H	4H	17.96	18.81	18.42	19.25	19.71	17.58	18.43	18.05	18.87	19.34
	6H	18.67	19.38	19.17	19.86	20.34	18.29	18.99	18.79	19.48	19.96
	8H	18.93	19.56	19.44	20.07	20.56	18.54	19.17	19.05	19.68	20.16
	12H	19.13	19.69	19.64	20.18	20.74	18.72	19.28	19.23	19.77	20.33
12H	4H	17.99	18.75	18.47	19.22	19.69	17.62	18.38	18.10	18.86	19.33
	6H	18.72	19.35	19.23	19.86	20.34	18.35	18.98	18.86	19.49	19.97
	8H	19.03	19.59	19.54	20.08	20.64	18.65	19.21	19.16	19.70	20.26