

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930611

Luminaire Tested: DFN2DS-PN3F0-080DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-080DS940-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7064.6 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 84.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930611

CATALOG NUMBER: DFN2DS-PN3F0-080DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930611

CATALOG NUMBER: DFN2DS-PN3F0-080DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3246	3246	3246
5°	3258	3211	3230
10°	3239	3179	3195
15°	3199	3137	3134
20°	3142	3076	3073
25°	3086	3000	3000
30°	3013	2930	2905
35°	2945	2846	2804
40°	2860	2762	2709
45°	2777	2679	2613
50°	2685	2593	2501
55°	2590	2492	2400
60°	2484	2372	2285
65°	2371	2253	2149
70°	2227	2108	2008
75°	2025	1941	1893
80°	1799	1743	1653
85°	1467	1399	1254

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2777 cd/sqm

TEST NUMBER: P930611

CATALOG NUMBER: DFN2DS-PN3F0-080DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	3.7
10°-20°	735.3	10.4
20°-30°	1080.6	15.3
30°-40°	1255.1	17.8
40°-50°	1253.5	17.7
50°-60°	1093.0	15.5
60°-70°	808.0	11.4
70°-80°	457.1	6.5
80°-90°	120.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.3	29.4
0°-40°	3332.3	47.2
0°-60°	5678.8	80.4
0°-90°	7064.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7064.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2777	2777	2777	2777	2777	
5°	2777	2766	2737	2758	2753	264
15°	2643	2627	2592	2603	2590	744
25°	2392	2371	2326	2331	2326	1101
35°	2064	2037	1994	1978	1965	1289
45°	1680	1661	1621	1591	1581	1296
55°	1271	1255	1223	1191	1178	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	129
90°	0	0	0	0	0	

TEST NUMBER: P930611

CATALOG NUMBER: DFN2DS-PN3F0-080DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2776.6	2776.6	2776.6	2776.6	2776.6
2.5°	2792.8	2779.5	2750.0	2776.6	2771.5
5°	2776.6	2766.2	2736.7	2758.0	2752.9
7.5°	2758.0	2742.1	2712.7	2734.2	2728.8
10°	2728.8	2710.1	2678.1	2699.3	2691.4
12.5°	2688.6	2672.7	2640.7	2654.0	2648.6
15°	2643.3	2627.4	2592.5	2603.3	2590.0
17.5°	2587.2	2571.3	2536.4	2549.8	2536.4
20°	2525.7	2509.8	2472.4	2480.4	2469.9
22.5°	2464.5	2440.4	2405.5	2405.5	2400.2
25°	2392.3	2371.0	2325.7	2330.8	2325.7
27.5°	2312.1	2293.4	2258.8	2250.9	2237.6
30°	2232.2	2210.6	2170.8	2162.8	2152.0
32.5°	2146.7	2130.8	2088.0	2071.8	2061.1
35°	2063.9	2037.3	1994.5	1978.4	1965.1
37.5°	1970.4	1946.3	1903.6	1884.9	1871.6
40°	1874.4	1852.9	1810.1	1786.3	1775.5
42.5°	1781.0	1759.4	1716.9	1690.0	1674.2
45°	1679.5	1660.8	1620.6	1591.4	1580.7
47.5°	1580.7	1562.0	1519.2	1489.7	1473.9
50°	1476.4	1463.1	1425.7	1388.3	1375.0
52.5°	1375.0	1356.3	1321.8	1292.3	1273.6
55°	1271.0	1254.9	1222.9	1190.9	1177.5
57.5°	1166.8	1153.5	1118.7	1086.6	1075.8
60°	1062.6	1052.1	1014.6	985.2	977.3
62.5°	961.1	942.5	915.8	889.2	878.4
65°	857.2	841.1	814.4	790.3	777.0
67.5°	750.4	736.8	713.0	694.3	683.5
70°	651.5	640.7	616.7	598.0	587.5
72.5°	550.1	539.4	526.0	507.4	499.4
75°	448.4	443.3	429.8	413.9	419.2
77.5°	357.8	347.0	341.6	333.7	325.8
80°	267.2	264.3	258.9	251.0	245.6
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.4	106.8	104.3	96.1	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930611

CATALOG NUMBER: DFN2DS-PN3F0-080DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.37	16.98	15.74	17.30	17.61	14.93	16.54	15.29	16.85	17.17
	3H	17.12	18.58	17.50	18.90	19.26	16.63	18.09	17.01	18.41	18.77
	4H	17.77	19.14	18.17	19.49	19.86	17.27	18.64	17.67	18.99	19.37
	6H	18.24	19.51	18.65	19.87	20.26	17.74	19.01	18.15	19.37	19.76
	8H	18.38	19.59	18.81	19.98	20.38	17.88	19.09	18.30	19.48	19.88
	12H	18.47	19.63	18.90	20.01	20.44	17.96	19.12	18.39	19.50	19.93
4H	2H	15.93	17.30	16.33	17.65	18.03	15.58	16.95	15.98	17.30	17.67
	3H	17.91	19.05	18.32	19.45	19.85	17.50	18.65	17.91	19.05	19.45
	4H	18.69	19.72	19.12	20.13	20.57	18.26	19.30	18.69	19.71	20.15
	6H	19.28	20.19	19.74	20.63	21.08	18.85	19.75	19.30	20.19	20.65
	8H	19.47	20.32	19.93	20.76	21.23	19.03	19.88	19.49	20.32	20.79
	12H	19.60	20.36	20.08	20.84	21.31	19.15	19.91	19.63	20.39	20.86
8H	4H	18.96	19.81	19.42	20.25	20.71	18.58	19.43	19.04	19.87	20.34
	6H	19.67	20.38	20.17	20.86	21.34	19.29	19.99	19.79	20.48	20.96
	8H	19.93	20.56	20.44	21.07	21.56	19.54	20.17	20.05	20.68	21.16
	12H	20.13	20.69	20.64	21.18	21.74	19.72	20.28	20.23	20.77	21.33
12H	4H	18.98	19.74	19.46	20.22	20.69	18.62	19.38	19.10	19.86	20.33
	6H	19.72	20.35	20.23	20.86	21.34	19.35	19.98	19.86	20.49	20.97
	8H	20.03	20.59	20.54	21.08	21.64	19.65	20.21	20.16	20.70	21.26