

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930168

Luminaire Tested: DFN2DS-HX3F0-050DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-050DS835-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4250.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930168

CATALOG NUMBER: DFN2DS-HX3F0-050DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930168

CATALOG NUMBER: DFN2DS-HX3F0-050DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2394	2394	2394
5°	2403	2364	2377
10°	2384	2325	2305
15°	2357	2256	2191
20°	2319	2158	2049
25°	2280	2046	1912
30°	2226	1931	1736
35°	2174	1806	1581
40°	2121	1677	1403
45°	2059	1532	1241
50°	1995	1385	1082
55°	1930	1227	929
60°	1854	1061	771
65°	1768	892	702
70°	1666	735	646
75°	1540	670	603
80°	1359	598	549
85°	1069	472	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2059 cd/sqm

TEST NUMBER: P930168

CATALOG NUMBER: DFN2DS-HX3F0-050DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	4.6
10°-20°	531.7	12.5
20°-30°	746.5	17.6
30°-40°	813.7	19.1
40°-50°	747.9	17.6
50°-60°	587.3	13.8
60°-70°	382.3	9.0
70°-80°	196.8	4.6
80°-90°	50.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.8	34.6
0°-40°	2285.5	53.8
0°-60°	3620.7	85.2
0°-90°	4250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4250.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	96
90°	0	0	0	0	0	

TEST NUMBER: P930168

CATALOG NUMBER: DFN2DS-HX3F0-050DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930168

CATALOG NUMBER: DFN2DS-HX3F0-050DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.27	15.79	14.63	16.10	16.42	10.23	11.75	10.59	12.06	12.38
	3H	16.03	17.40	16.41	17.73	18.09	11.49	12.86	11.87	13.19	13.55
	4H	16.70	17.98	17.10	18.33	18.71	11.99	13.28	12.39	13.62	14.00
	6H	17.19	18.37	17.60	18.74	19.13	12.38	13.56	12.79	13.92	14.32
	8H	17.35	18.48	17.78	18.87	19.27	12.50	13.63	12.93	14.02	14.42
	12H	17.46	18.53	17.89	18.92	19.35	12.58	13.66	13.01	14.04	14.47
4H	2H	14.37	15.65	14.77	16.00	16.38	10.92	12.20	11.32	12.55	12.93
	3H	16.30	17.37	16.72	17.77	18.17	12.37	13.43	12.78	13.83	14.23
	4H	17.05	18.01	17.49	18.43	18.86	12.97	13.92	13.40	14.34	14.78
	6H	17.65	18.48	18.10	18.92	19.38	13.45	14.29	13.91	14.73	15.19
	8H	17.86	18.64	18.32	19.08	19.55	13.62	14.39	14.08	14.84	15.30
	12H	18.01	18.71	18.50	19.19	19.66	13.73	14.43	14.21	14.91	15.38
8H	4H	17.08	17.86	17.54	18.30	18.77	13.32	14.10	13.78	14.54	15.01
	6H	17.72	18.36	18.21	18.85	19.33	13.91	14.55	14.40	15.04	15.52
	8H	17.97	18.54	18.48	19.05	19.54	14.13	14.70	14.64	15.21	15.70
	12H	18.17	18.68	18.68	19.17	19.74	14.31	14.82	14.82	15.31	15.87
12H	4H	17.06	17.76	17.55	18.24	18.71	13.36	14.06	13.85	14.54	15.01
	6H	17.70	18.27	18.21	18.78	19.27	13.97	14.55	14.48	15.06	15.54
	8H	17.98	18.49	18.49	18.98	19.55	14.24	14.75	14.75	15.24	15.81