

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930204

Luminaire Tested: DFN2DS-HX3F0-070DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS835-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5950.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930204

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930204

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3351	3351	3351
5°	3364	3309	3328
10°	3338	3255	3227
15°	3300	3159	3068
20°	3247	3021	2869
25°	3192	2864	2677
30°	3117	2703	2430
35°	3043	2529	2214
40°	2969	2348	1964
45°	2882	2145	1737
50°	2793	1939	1515
55°	2702	1718	1301
60°	2596	1486	1080
65°	2476	1249	983
70°	2332	1028	904
75°	2156	937	844
80°	1903	838	769
85°	1495	661	661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2882 cd/sqm

TEST NUMBER: P930204

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	4.6
10°-20°	744.3	12.5
20°-30°	1045.0	17.6
30°-40°	1139.2	19.1
40°-50°	1047.0	17.6
50°-60°	822.3	13.8
60°-70°	535.2	9.0
70°-80°	275.5	4.6
80°-90°	70.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2060.5	34.6
0°-40°	3199.7	53.8
0°-60°	5068.9	85.2
0°-90°	5950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	135
90°	0	0	0	0	0	

TEST NUMBER: P930204

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930204

CATALOG NUMBER: DFN2DS-HX3F0-070DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.44	16.96	15.80	17.27	17.59	11.40	12.92	11.76	13.23	13.55
	3H	17.20	18.57	17.58	18.89	19.26	12.66	14.03	13.04	14.35	14.72
	4H	17.87	19.15	18.27	19.50	19.88	13.16	14.44	13.56	14.79	15.17
	6H	18.36	19.54	18.77	19.91	20.30	13.54	14.73	13.96	15.09	15.49
	8H	18.52	19.65	18.95	20.04	20.44	13.67	14.80	14.10	15.19	15.59
	12H	18.63	19.70	19.06	20.09	20.51	13.75	14.83	14.18	15.21	15.64
4H	2H	15.54	16.82	15.94	17.17	17.55	12.09	13.37	12.49	13.72	14.10
	3H	17.47	18.54	17.88	18.94	19.34	13.54	14.60	13.95	15.00	15.40
	4H	18.22	19.18	18.66	19.60	20.03	14.13	15.09	14.57	15.51	15.95
	6H	18.81	19.65	19.27	20.09	20.55	14.62	15.46	15.08	15.90	16.36
	8H	19.03	19.81	19.49	20.25	20.72	14.78	15.56	15.25	16.01	16.47
	12H	19.18	19.88	19.66	20.36	20.83	14.90	15.60	15.38	16.08	16.55
8H	4H	18.25	19.02	18.71	19.47	19.94	14.49	15.27	14.95	15.71	16.18
	6H	18.88	19.53	19.38	20.02	20.50	15.08	15.72	15.57	16.21	16.69
	8H	19.13	19.71	19.65	20.22	20.71	15.30	15.87	15.81	16.38	16.87
	12H	19.34	19.85	19.85	20.34	20.91	15.48	15.99	15.99	16.48	17.04
12H	4H	18.23	18.93	18.71	19.40	19.88	14.53	15.23	15.01	15.70	16.18
	6H	18.87	19.44	19.38	19.95	20.44	15.14	15.72	15.65	16.23	16.71
	8H	19.15	19.66	19.66	20.15	20.72	15.41	15.92	15.92	16.41	16.98

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7