

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930651

Luminaire Tested: DFN2DS-PN4F0-050DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-050DS830-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4662.9 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 48.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930651

CATALOG NUMBER: DFN2DS-PN4F0-050DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930651

CATALOG NUMBER: DFN2DS-PN4F0-050DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1338	1338	1338
5°	1343	1324	1331
10°	1335	1310	1317
15°	1318	1293	1292
20°	1295	1268	1266
25°	1272	1236	1236
30°	1242	1208	1197
35°	1214	1173	1156
40°	1179	1138	1117
45°	1144	1104	1077
50°	1107	1069	1031
55°	1068	1027	989
60°	1024	978	942
65°	977	928	886
70°	918	869	828
75°	835	800	781
80°	741	718	681
85°	605	576	517

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1144 cd/sqm

TEST NUMBER: P930651

CATALOG NUMBER: DFN2DS-PN4F0-050DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.5	3.7
10°-20°	485.3	10.4
20°-30°	713.2	15.3
30°-40°	828.4	17.8
40°-50°	827.4	17.7
50°-60°	721.4	15.5
60°-70°	533.3	11.4
70°-80°	301.7	6.5
80°-90°	79.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.1	29.4
0°-40°	2199.4	47.2
0°-60°	3748.2	80.4
0°-90°	4662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4662.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1826	1806	1820	1817	174
15°	1745	1734	1711	1718	1709	491
25°	1579	1565	1535	1538	1535	727
35°	1362	1345	1316	1306	1297	851
45°	1108	1096	1070	1050	1043	856
55°	839	828	807	786	777	750
65°	566	555	538	522	513	559
75°	296	293	284	273	277	316
85°	72	70	69	63	62	85
90°	0	0	0	0	0	

TEST NUMBER: P930651

CATALOG NUMBER: DFN2DS-PN4F0-050DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.7	1832.7	1832.7	1832.7	1832.7
2.5°	1843.3	1834.5	1815.1	1832.7	1829.4
5°	1832.7	1825.8	1806.3	1820.3	1817.0
7.5°	1820.3	1809.9	1790.5	1804.7	1801.1
10°	1801.1	1788.8	1767.7	1781.6	1776.4
12.5°	1774.5	1764.1	1743.0	1751.7	1748.2
15°	1744.6	1734.1	1711.1	1718.3	1709.4
17.5°	1707.6	1697.1	1674.1	1682.9	1674.1
20°	1667.1	1656.6	1631.9	1637.1	1630.2
22.5°	1626.6	1610.7	1587.7	1587.7	1584.2
25°	1579.0	1564.9	1535.0	1538.4	1535.0
27.5°	1526.0	1513.7	1490.9	1485.6	1476.9
30°	1473.3	1459.2	1432.8	1427.5	1420.4
32.5°	1416.9	1406.4	1378.1	1367.5	1360.4
35°	1362.2	1344.7	1316.4	1305.8	1297.0
37.5°	1300.5	1284.7	1256.4	1244.1	1235.3
40°	1237.2	1223.0	1194.7	1179.0	1171.9
42.5°	1175.5	1161.3	1133.2	1115.4	1105.0
45°	1108.5	1096.2	1069.6	1050.4	1043.3
47.5°	1043.3	1030.9	1002.8	983.3	972.8
50°	974.5	965.7	941.1	916.4	907.5
52.5°	907.5	895.2	872.4	853.0	840.6
55°	838.9	828.3	807.1	786.0	777.2
57.5°	770.1	761.3	738.3	717.2	710.1
60°	701.3	694.4	669.8	650.3	645.1
62.5°	634.4	622.1	604.5	586.9	579.8
65°	565.8	555.1	537.5	521.7	512.8
67.5°	495.3	486.4	470.6	458.3	451.1
70°	430.0	423.0	407.0	394.7	387.8
72.5°	363.1	356.0	347.2	334.9	329.6
75°	296.0	292.6	283.6	273.2	276.8
77.5°	236.2	229.0	225.5	220.2	215.1
80°	176.3	174.5	170.9	165.7	162.1
82.5°	119.8	119.8	118.1	111.1	111.1
85°	72.2	70.5	68.8	63.4	61.7
87.5°	31.7	28.3	24.7	19.4	17.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930651

CATALOG NUMBER: DFN2DS-PN4F0-050DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.29	13.90	12.66	14.22	14.53	11.85	13.46	12.21	13.77	14.09
	3H	14.04	15.50	14.42	15.82	16.19	13.55	15.01	13.93	15.33	15.69
	4H	14.69	16.06	15.09	16.41	16.78	14.20	15.56	14.59	15.91	16.29
	6H	15.16	16.43	15.57	16.79	17.18	14.66	15.93	15.07	16.29	16.68
	8H	15.30	16.51	15.73	16.90	17.30	14.80	16.01	15.22	16.40	16.80
	12H	15.39	16.55	15.82	16.93	17.36	14.88	16.04	15.31	16.42	16.85
4H	2H	12.85	14.22	13.25	14.57	14.95	12.50	13.87	12.90	14.22	14.59
	3H	14.83	15.98	15.24	16.37	16.77	14.42	15.57	14.83	15.97	16.37
	4H	15.61	16.64	16.04	17.06	17.49	15.18	16.22	15.61	16.63	17.07
	6H	16.20	17.11	16.66	17.55	18.00	15.77	16.67	16.22	17.12	17.57
	8H	16.39	17.24	16.85	17.68	18.15	15.95	16.80	16.41	17.24	17.71
	12H	16.52	17.28	17.00	17.76	18.23	16.07	16.83	16.55	17.31	17.78
8H	4H	15.88	16.73	16.34	17.17	17.63	15.50	16.35	15.97	16.79	17.26
	6H	16.59	17.30	17.09	17.78	18.26	16.21	16.92	16.71	17.40	17.88
	8H	16.85	17.48	17.36	17.99	18.48	16.46	17.09	16.97	17.60	18.08
	12H	17.05	17.61	17.56	18.10	18.66	16.64	17.20	17.15	17.69	18.25
12H	4H	15.91	16.66	16.39	17.14	17.61	15.54	16.30	16.02	16.78	17.25
	6H	16.64	17.27	17.15	17.78	18.26	16.27	16.90	16.78	17.41	17.90
	8H	16.95	17.51	17.46	18.00	18.56	16.57	17.13	17.08	17.62	18.18