

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930239

Luminaire Tested: DFN2DS-HX3F0-090DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-090DS835-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8910.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930239

CATALOG NUMBER: DFN2DS-HX3F0-090DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930239

CATALOG NUMBER: DFN2DS-HX3F0-090DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4056	4056	4056
5°	4072	4013	4037
10°	4048	3973	3993
15°	3998	3921	3917
20°	3927	3844	3840
25°	3856	3749	3749
30°	3766	3662	3630
35°	3681	3557	3505
40°	3575	3452	3386
45°	3470	3348	3266
50°	3356	3240	3125
55°	3237	3115	2999
60°	3105	2965	2856
65°	2963	2815	2686
70°	2783	2634	2510
75°	2531	2426	2367
80°	2247	2178	2067
85°	1833	1748	1567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3470 cd/sqm

TEST NUMBER: P930239

CATALOG NUMBER: DFN2DS-HX3F0-090DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	3.7
10°-20°	927.4	10.4
20°-30°	1362.9	15.3
30°-40°	1582.9	17.8
40°-50°	1580.9	17.7
50°-60°	1378.5	15.5
60°-70°	1019.0	11.4
70°-80°	576.6	6.5
80°-90°	152.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2619.9	29.4
0°-40°	4202.8	47.2
0°-60°	7162.3	80.4
0°-90°	8910.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8910.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	162
90°	0	0	0	0	0	

TEST NUMBER: P930239

CATALOG NUMBER: DFN2DS-HX3F0-090DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930239

CATALOG NUMBER: DFN2DS-HX3F0-090DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.15	17.76	16.51	18.07	18.39	15.70	17.31	16.07	17.63	17.94
	3H	17.90	19.35	18.27	19.68	20.04	17.41	18.86	17.78	19.19	19.55
	4H	18.54	19.91	18.94	20.26	20.64	18.05	19.42	18.45	19.77	20.14
	6H	19.01	20.28	19.42	20.65	21.04	18.51	19.78	18.92	20.15	20.54
	8H	19.16	20.37	19.58	20.76	21.16	18.65	19.86	19.08	20.25	20.65
	12H	19.25	20.41	19.68	20.79	21.22	18.73	19.89	19.16	20.28	20.71
4H	2H	16.71	18.08	17.11	18.43	18.80	16.36	17.72	16.75	18.07	18.45
	3H	18.68	19.83	19.09	20.23	20.63	18.28	19.42	18.69	19.82	20.22
	4H	19.46	20.50	19.89	20.91	21.35	19.04	20.07	19.47	20.49	20.92
	6H	20.06	20.96	20.51	21.40	21.86	19.62	20.53	20.08	20.97	21.43
	8H	20.25	21.09	20.71	21.53	22.00	19.81	20.65	20.27	21.10	21.56
	12H	20.38	21.14	20.86	21.61	22.08	19.93	20.69	20.41	21.16	21.63
8H	4H	19.73	20.58	20.19	21.02	21.49	19.36	20.21	19.82	20.65	21.11
	6H	20.45	21.15	20.94	21.64	22.11	20.07	20.77	20.56	21.26	21.73
	8H	20.71	21.34	21.22	21.84	22.33	20.32	20.95	20.82	21.45	21.94
	12H	20.91	21.46	21.41	21.95	22.52	20.49	21.05	21.00	21.54	22.10
12H	4H	19.76	20.52	20.24	20.99	21.46	19.39	20.15	19.87	20.63	21.10
	6H	20.49	21.12	21.00	21.63	22.12	20.12	20.76	20.63	21.26	21.75
	8H	20.81	21.36	21.31	21.86	22.42	20.43	20.99	20.94	21.48	22.04