

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930669

Luminaire Tested: DFN2DS-PN4F0-060DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS830-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5595.4 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930669

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930669

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1605	1605	1605
5°	1611	1588	1598
10°	1602	1572	1580
15°	1582	1552	1550
20°	1554	1521	1520
25°	1526	1484	1484
30°	1490	1449	1437
35°	1457	1408	1387
40°	1415	1366	1340
45°	1373	1325	1292
50°	1328	1282	1237
55°	1281	1233	1187
60°	1229	1173	1130
65°	1173	1114	1063
70°	1101	1042	993
75°	1002	960	937
80°	889	862	818
85°	725	691	620

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1373 cd/sqm

TEST NUMBER: P930669

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	3.7
10°-20°	582.4	10.4
20°-30°	855.9	15.3
30°-40°	994.1	17.8
40°-50°	992.8	17.7
50°-60°	865.7	15.5
60°-70°	639.9	11.4
70°-80°	362.1	6.5
80°-90°	95.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1645.3	29.4
0°-40°	2639.3	47.2
0°-60°	4497.9	80.4
0°-90°	5595.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2199	2199	2199	2199	2199	
5°	2199	2191	2168	2184	2180	209
15°	2094	2081	2053	2062	2051	590
25°	1895	1878	1842	1846	1842	872
35°	1635	1614	1580	1567	1556	1021
45°	1330	1315	1284	1260	1252	1027
55°	1007	994	969	943	933	900
65°	679	666	645	626	615	671
75°	355	351	340	328	332	379
85°	87	85	82	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930669

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2199.2	2199.2	2199.2	2199.2	2199.2
2.5°	2212.0	2201.5	2178.1	2199.2	2195.1
5°	2199.2	2190.9	2167.5	2184.4	2180.4
7.5°	2184.4	2171.9	2148.5	2165.6	2161.3
10°	2161.3	2146.5	2121.1	2138.0	2131.7
12.5°	2129.5	2116.9	2091.5	2102.1	2097.8
15°	2093.5	2081.0	2053.4	2061.9	2051.4
17.5°	2049.1	2036.6	2009.0	2019.5	2009.0
20°	2000.4	1987.9	1958.2	1964.5	1956.3
22.5°	1952.0	1932.9	1905.3	1905.3	1901.1
25°	1894.7	1878.0	1842.0	1846.0	1842.0
27.5°	1831.2	1816.5	1789.0	1782.8	1772.3
30°	1768.0	1750.9	1719.3	1713.0	1704.5
32.5°	1700.2	1687.7	1653.8	1641.0	1632.5
35°	1634.7	1613.6	1579.7	1566.9	1556.4
37.5°	1560.7	1541.6	1507.8	1492.9	1482.3
40°	1484.6	1467.5	1433.7	1414.9	1406.3
42.5°	1410.6	1393.5	1359.9	1338.6	1326.0
45°	1330.3	1315.4	1283.6	1260.5	1251.9
47.5°	1251.9	1237.1	1203.3	1179.9	1167.3
50°	1169.4	1158.8	1129.3	1099.6	1089.0
52.5°	1089.0	1074.3	1046.8	1023.6	1008.8
55°	1006.7	993.9	968.6	943.2	932.7
57.5°	924.2	913.6	886.0	860.7	852.1
60°	841.6	833.3	803.7	780.4	774.0
62.5°	761.2	746.4	725.3	704.2	695.8
65°	678.9	666.2	645.1	626.0	615.4
67.5°	594.3	583.6	564.7	549.9	541.4
70°	516.0	507.5	488.4	473.6	465.3
72.5°	435.7	427.2	416.6	401.9	395.5
75°	355.1	351.2	340.3	327.8	332.1
77.5°	283.4	274.9	270.5	264.3	258.0
80°	211.6	209.3	205.1	198.8	194.5
82.5°	143.8	143.8	141.8	133.3	133.3
85°	86.6	84.6	82.5	76.0	74.0
87.5°	38.2	33.9	29.6	23.4	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930669

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.93	14.54	13.29	14.85	15.17	12.48	14.09	12.85	14.41	14.72
	3H	14.68	16.13	15.05	16.46	16.82	14.19	15.64	14.56	15.97	16.33
	4H	15.32	16.69	15.72	17.04	17.42	14.83	16.20	15.23	16.55	16.92
	6H	15.79	17.06	16.20	17.43	17.82	15.29	16.56	15.70	16.92	17.32
	8H	15.94	17.15	16.36	17.54	17.93	15.43	16.64	15.86	17.03	17.43
	12H	16.03	17.19	16.46	17.57	18.00	15.51	16.67	15.94	17.06	17.48
4H	2H	13.49	14.86	13.89	15.20	15.58	13.13	14.50	13.53	14.85	15.23
	3H	15.46	16.61	15.87	17.01	17.41	15.06	16.20	15.47	16.60	17.00
	4H	16.24	17.28	16.67	17.69	18.12	15.82	16.85	16.25	17.26	17.70
	6H	16.84	17.74	17.29	18.18	18.64	16.40	17.31	16.86	17.75	18.20
	8H	17.03	17.87	17.49	18.31	18.78	16.59	17.43	17.05	17.88	18.34
	12H	17.16	17.92	17.64	18.39	18.86	16.70	17.46	17.19	17.94	18.41
8H	4H	16.51	17.36	16.97	17.80	18.27	16.14	16.98	16.60	17.43	17.89
	6H	17.23	17.93	17.72	18.42	18.89	16.85	17.55	17.34	18.04	18.51
	8H	17.49	18.12	18.00	18.62	19.11	17.09	17.73	17.60	18.23	18.72
	12H	17.69	18.24	18.19	18.73	19.30	17.27	17.83	17.78	18.32	18.88
12H	4H	16.54	17.30	17.02	17.77	18.24	16.17	16.93	16.65	17.41	17.88
	6H	17.27	17.90	17.78	18.41	18.90	16.90	17.54	17.41	18.04	18.53
	8H	17.59	18.14	18.09	18.63	19.20	17.21	17.77	17.72	18.26	18.82