

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930670

Luminaire Tested: DFN2DS-PN4F0-060DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS830-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4804.2 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930670

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930670

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1705	1705	1705
5°	1712	1684	1693
10°	1699	1656	1642
15°	1679	1607	1561
20°	1652	1537	1460
25°	1624	1457	1362
30°	1586	1376	1237
35°	1549	1287	1126
40°	1511	1194	999
45°	1467	1091	884
50°	1421	987	771
55°	1375	874	662
60°	1321	756	549
65°	1260	635	500
70°	1187	523	460
75°	1097	477	430
80°	968	426	391
85°	760	336	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1467 cd/sqm

TEST NUMBER: P930670

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.9	4.6
10°-20°	601.0	12.5
20°-30°	843.8	17.6
30°-40°	919.8	19.1
40°-50°	845.4	17.6
50°-60°	663.9	13.8
60°-70°	432.2	9.0
70°-80°	222.5	4.6
80°-90°	56.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1663.7	34.6
0°-40°	2583.5	53.8
0°-60°	4092.8	85.2
0°-90°	4804.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4804.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2336	2336	2336	2336	2336	
5°	2336	2325	2298	2317	2311	221
15°	2222	2198	2127	2086	2065	626
25°	2017	1949	1810	1723	1691	928
35°	1738	1630	1444	1311	1264	1088
45°	1421	1279	1057	907	856	1097
55°	1080	915	687	560	520	965
65°	729	558	368	296	290	723
75°	389	241	169	154	152	411
85°	91	46	40	40	40	109
90°	0	0	0	0	0	

TEST NUMBER: P930670

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.0	2336.0	2336.0	2336.0	2336.0
2.5°	2346.5	2336.0	2312.6	2333.9	2329.7
5°	2336.0	2325.4	2297.8	2316.9	2310.6
7.5°	2316.9	2304.3	2274.7	2283.0	2272.5
10°	2291.5	2276.7	2234.6	2228.1	2215.5
12.5°	2260.0	2240.8	2183.7	2171.1	2147.8
15°	2221.8	2198.4	2126.7	2086.5	2065.4
17.5°	2177.4	2143.5	2054.7	2008.2	1974.4
20°	2126.7	2084.3	1978.7	1925.9	1879.3
22.5°	2071.7	2023.0	1900.4	1828.6	1797.0
25°	2016.8	1949.1	1809.6	1723.0	1691.2
27.5°	1951.4	1879.3	1725.0	1625.6	1577.0
30°	1881.6	1801.0	1631.9	1524.3	1467.1
32.5°	1813.8	1716.5	1543.4	1416.4	1363.5
35°	1737.8	1629.9	1444.0	1310.7	1264.1
37.5°	1663.8	1547.3	1350.9	1204.9	1152.2
40°	1585.5	1458.8	1253.5	1103.5	1048.5
42.5°	1505.2	1370.0	1156.4	999.8	947.2
45°	1420.6	1278.9	1057.1	906.8	856.1
47.5°	1340.4	1190.3	962.0	811.7	765.3
50°	1251.5	1101.5	868.9	722.9	678.7
52.5°	1164.7	1006.2	780.1	640.6	600.4
55°	1080.2	915.3	687.0	560.3	520.1
57.5°	993.6	824.4	604.7	486.3	452.3
60°	904.8	735.7	517.9	410.2	376.3
62.5°	818.2	649.1	443.9	342.5	325.6
65°	729.4	558.0	367.9	296.1	289.6
67.5°	644.8	473.4	296.1	260.0	253.7
70°	556.0	391.1	245.1	224.1	215.5
72.5°	471.5	314.9	205.0	188.2	183.9
75°	389.0	240.9	169.1	154.3	152.3
77.5°	306.6	171.2	133.2	124.7	120.5
80°	230.3	122.6	101.4	93.1	93.1
82.5°	160.6	82.5	69.7	65.5	65.5
85°	90.8	46.4	40.1	40.1	40.1
87.5°	33.9	16.9	16.9	14.8	14.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930670

CATALOG NUMBER: DFN2DS-PN4F0-060DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.09	14.61	13.45	14.92	15.24	9.05	10.57	9.41	10.88	11.20
	3H	14.85	16.22	15.23	16.55	16.91	10.31	11.68	10.69	12.01	12.37
	4H	15.52	16.80	15.92	17.15	17.53	10.82	12.10	11.22	12.45	12.82
	6H	16.01	17.19	16.42	17.56	17.95	11.20	12.38	11.61	12.75	13.14
	8H	16.17	17.30	16.60	17.69	18.09	11.32	12.45	11.75	12.84	13.24
	12H	16.28	17.36	16.71	17.74	18.17	11.40	12.48	11.83	12.86	13.29
4H	2H	13.19	14.47	13.59	14.82	15.20	9.75	11.03	10.15	11.37	11.75
	3H	15.13	16.19	15.54	16.59	16.99	11.19	12.25	11.60	12.65	13.05
	4H	15.88	16.83	16.31	17.25	17.69	11.79	12.74	12.22	13.16	13.60
	6H	16.47	17.30	16.92	17.74	18.20	12.28	13.11	12.73	13.55	14.01
	8H	16.68	17.46	17.14	17.90	18.37	12.44	13.22	12.90	13.66	14.13
	12H	16.83	17.53	17.32	18.01	18.48	12.56	13.25	13.04	13.73	14.20
8H	4H	15.90	16.68	16.36	17.12	17.59	12.14	12.92	12.60	13.36	13.83
	6H	16.54	17.18	17.03	17.67	18.15	12.73	13.37	13.23	13.86	14.34
	8H	16.79	17.36	17.30	17.87	18.36	12.95	13.53	13.46	14.04	14.52
	12H	16.99	17.50	17.50	17.99	18.56	13.13	13.64	13.64	14.13	14.69
12H	4H	15.88	16.58	16.37	17.06	17.53	12.18	12.88	12.67	13.36	13.83
	6H	16.52	17.10	17.03	17.60	18.09	12.79	13.37	13.31	13.88	14.37
	8H	16.80	17.31	17.31	17.80	18.37	13.06	13.57	13.57	14.07	14.63