

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930205

Luminaire Tested: DFN2DS-HX3F0-070DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS840-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6936.9 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930205

CATALOG NUMBER: DFN2DS-HX3F0-070DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930205

CATALOG NUMBER: DFN2DS-HX3F0-070DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3158	3158	3158
5°	3170	3125	3143
10°	3152	3093	3108
15°	3113	3053	3050
20°	3057	2993	2990
25°	3002	2919	2919
30°	2932	2851	2826
35°	2866	2769	2728
40°	2783	2688	2636
45°	2701	2607	2543
50°	2612	2523	2433
55°	2520	2425	2335
60°	2417	2308	2223
65°	2307	2192	2091
70°	2167	2051	1954
75°	1971	1888	1843
80°	1750	1696	1608
85°	1427	1361	1220

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2701 cd/sqm

TEST NUMBER: P930205

CATALOG NUMBER: DFN2DS-HX3F0-070DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.6	3.7
10°-20°	722.0	10.4
20°-30°	1061.1	15.3
30°-40°	1232.4	17.8
40°-50°	1230.8	17.7
50°-60°	1073.3	15.5
60°-70°	793.4	11.4
70°-80°	448.9	6.5
80°-90°	118.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2039.7	29.4
0°-40°	3272.1	47.2
0°-60°	5576.2	80.4
0°-90°	6936.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6936.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2726	2726	2726	2726	2726	
5°	2726	2716	2687	2708	2703	259
15°	2596	2580	2546	2556	2543	731
25°	2349	2328	2284	2289	2284	1081
35°	2027	2000	1958	1943	1930	1266
45°	1649	1631	1591	1563	1552	1273
55°	1248	1232	1201	1169	1156	1116
65°	842	826	800	776	763	832
75°	440	435	422	406	412	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P930205

CATALOG NUMBER: DFN2DS-HX3F0-070DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.4	2726.4	2726.4	2726.4	2726.4
2.5°	2742.3	2729.2	2700.3	2726.4	2721.4
5°	2726.4	2716.2	2687.3	2708.1	2703.1
7.5°	2708.1	2692.5	2663.6	2684.8	2679.5
10°	2679.5	2661.1	2629.6	2650.5	2642.7
12.5°	2639.9	2624.4	2593.0	2606.0	2600.7
15°	2595.5	2579.9	2545.6	2556.3	2543.1
17.5°	2540.3	2524.8	2490.6	2503.7	2490.6
20°	2480.0	2464.5	2427.7	2435.5	2425.2
22.5°	2419.9	2396.3	2362.1	2362.1	2356.8
25°	2349.0	2328.1	2283.7	2288.7	2283.7
27.5°	2270.3	2251.9	2218.0	2210.2	2197.1
30°	2191.9	2170.7	2131.5	2123.7	2113.1
32.5°	2107.8	2092.3	2050.2	2034.4	2023.8
35°	2026.6	2000.5	1958.5	1942.6	1929.5
37.5°	1934.8	1911.2	1869.2	1850.8	1837.7
40°	1840.5	1819.4	1777.4	1754.1	1743.4
42.5°	1748.7	1727.6	1685.9	1659.5	1643.8
45°	1649.1	1630.8	1591.3	1562.7	1552.1
47.5°	1552.1	1533.7	1491.7	1462.8	1447.2
50°	1449.7	1436.6	1399.9	1363.3	1350.1
52.5°	1350.1	1331.8	1297.9	1269.0	1250.5
55°	1248.0	1232.2	1200.8	1169.4	1156.3
57.5°	1145.7	1132.6	1098.4	1067.0	1056.5
60°	1043.3	1033.0	996.4	967.5	959.7
62.5°	943.7	925.4	899.3	873.2	862.6
65°	841.7	825.8	799.7	776.1	763.0
67.5°	736.8	723.5	700.1	681.8	671.2
70°	639.7	629.2	605.5	587.2	576.9
72.5°	540.1	529.6	516.5	498.2	490.4
75°	440.3	435.3	421.9	406.4	411.7
77.5°	351.4	340.7	335.4	327.6	319.9
80°	262.3	259.6	254.3	246.4	241.1
82.5°	178.3	178.3	175.8	165.3	165.3
85°	107.4	104.9	102.4	94.3	91.8
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930205

CATALOG NUMBER: DFN2DS-HX3F0-070DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.28	16.89	15.64	17.20	17.52	14.83	16.44	15.20	16.76	17.07
	3H	17.03	18.48	17.40	18.81	19.17	16.54	17.99	16.91	18.32	18.68
	4H	17.67	19.04	18.07	19.39	19.77	17.18	18.55	17.58	18.90	19.27
	6H	18.14	19.41	18.55	19.78	20.17	17.64	18.91	18.05	19.28	19.67
	8H	18.29	19.50	18.71	19.89	20.29	17.78	18.99	18.21	19.38	19.78
	12H	18.38	19.54	18.81	19.92	20.35	17.87	19.03	18.29	19.41	19.84
4H	2H	15.84	17.21	16.24	17.56	17.93	15.49	16.85	15.88	17.20	17.58
	3H	17.81	18.96	18.22	19.36	19.76	17.41	18.55	17.82	18.95	19.35
	4H	18.59	19.63	19.02	20.04	20.48	18.17	19.20	18.60	19.62	20.05
	6H	19.19	20.09	19.64	20.53	20.99	18.75	19.66	19.21	20.10	20.56
	8H	19.38	20.22	19.84	20.67	21.13	18.94	19.78	19.40	20.23	20.69
	12H	19.51	20.27	19.99	20.74	21.21	19.06	19.82	19.54	20.29	20.76
8H	4H	18.86	19.71	19.32	20.15	20.62	18.49	19.34	18.95	19.78	20.24
	6H	19.58	20.28	20.07	20.77	21.24	19.20	19.90	19.69	20.39	20.86
	8H	19.84	20.47	20.35	20.97	21.46	19.45	20.08	19.96	20.58	21.07
	12H	20.04	20.59	20.54	21.09	21.65	19.62	20.18	20.13	20.67	21.23
12H	4H	18.89	19.65	19.37	20.12	20.59	18.52	19.28	19.01	19.76	20.23
	6H	19.62	20.26	20.13	20.76	21.25	19.25	19.89	19.76	20.39	20.88
	8H	19.94	20.49	20.44	20.99	21.55	19.56	20.12	20.07	20.61	21.17