

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930135

Luminaire Tested: DFN2DS-HX3F0-030DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-030DS850-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3293.8 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 28.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930135

CATALOG NUMBER: DFN2DS-HX3F0-030DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930135

CATALOG NUMBER: DFN2DS-HX3F0-030DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1499	1499	1499
5°	1505	1484	1492
10°	1496	1469	1476
15°	1478	1449	1448
20°	1451	1421	1419
25°	1425	1386	1386
30°	1392	1354	1342
35°	1361	1315	1295
40°	1321	1276	1252
45°	1283	1238	1207
50°	1241	1198	1155
55°	1197	1151	1109
60°	1148	1096	1056
65°	1096	1041	993
70°	1029	974	928
75°	935	897	875
80°	830	805	764
85°	678	646	579

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1283 cd/sqm

TEST NUMBER: P930135

CATALOG NUMBER: DFN2DS-HX3F0-030DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	3.7
10°-20°	342.8	10.4
20°-30°	503.8	15.3
30°-40°	585.2	17.8
40°-50°	584.4	17.7
50°-60°	509.6	15.5
60°-70°	376.7	11.4
70°-80°	213.1	6.5
80°-90°	56.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.5	29.4
0°-40°	1553.6	47.2
0°-60°	2647.7	80.4
0°-90°	3293.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3293.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	60
90°	0	0	0	0	0	

TEST NUMBER: P930135

CATALOG NUMBER: DFN2DS-HX3F0-030DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930135

CATALOG NUMBER: DFN2DS-HX3F0-030DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.69	14.30	13.06	14.62	14.93	12.25	13.86	12.61	14.17	14.48
	3H	14.44	15.90	14.82	16.22	16.58	13.95	15.40	14.33	15.73	16.09
	4H	15.09	16.46	15.49	16.80	17.18	14.59	15.96	14.99	16.31	16.68
	6H	15.56	16.82	15.97	17.19	17.58	15.05	16.32	15.47	16.69	17.08
	8H	15.70	16.91	16.12	17.30	17.70	15.20	16.41	15.62	16.80	17.20
	12H	15.79	16.95	16.22	17.33	17.76	15.28	16.44	15.71	16.82	17.25
4H	2H	13.25	14.62	13.65	14.97	15.34	12.90	14.27	13.30	14.61	14.99
	3H	15.23	16.37	15.64	16.77	17.17	14.82	15.97	15.23	16.36	16.76
	4H	16.00	17.04	16.43	17.45	17.89	15.58	16.61	16.01	17.03	17.46
	6H	16.60	17.50	17.05	17.94	18.40	16.17	17.07	16.62	17.51	17.97
	8H	16.79	17.63	17.25	18.08	18.54	16.35	17.20	16.81	17.64	18.10
	12H	16.92	17.68	17.40	18.16	18.63	16.47	17.23	16.95	17.70	18.17
8H	4H	16.28	17.12	16.74	17.56	18.03	15.90	16.75	16.36	17.19	17.66
	6H	16.99	17.69	17.48	18.18	18.66	16.61	17.31	17.10	17.80	18.28
	8H	17.25	17.88	17.76	18.39	18.87	16.86	17.49	17.37	18.00	18.48
	12H	17.45	18.01	17.96	18.50	19.06	17.04	17.59	17.54	18.08	18.65
12H	4H	16.30	17.06	16.78	17.54	18.01	15.94	16.70	16.42	17.17	17.64
	6H	17.04	17.67	17.54	18.17	18.66	16.67	17.30	17.18	17.81	18.29
	8H	17.35	17.91	17.86	18.40	18.96	16.97	17.53	17.48	18.02	18.58