

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930777

Luminaire Tested: DFN2DS-PN4F0-120DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-120DS830-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11191.0 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 131
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930777

CATALOG NUMBER: DFN2DS-PN4F0-120DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930777

CATALOG NUMBER: DFN2DS-PN4F0-120DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3211	3211	3211
5°	3223	3177	3195
10°	3204	3144	3160
15°	3164	3103	3100
20°	3108	3042	3039
25°	3052	2967	2967
30°	2980	2898	2873
35°	2913	2815	2774
40°	2829	2732	2680
45°	2746	2650	2585
50°	2656	2565	2473
55°	2562	2465	2374
60°	2457	2347	2260
65°	2345	2228	2126
70°	2203	2085	1986
75°	2004	1920	1873
80°	1779	1724	1635
85°	1451	1383	1240

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2746 cd/sqm

TEST NUMBER: P930777

CATALOG NUMBER: DFN2DS-PN4F0-120DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.0	3.7
10°-20°	1164.8	10.4
20°-30°	1711.8	15.3
30°-40°	1988.1	17.8
40°-50°	1985.7	17.7
50°-60°	1731.4	15.5
60°-70°	1279.9	11.4
70°-80°	724.1	6.5
80°-90°	191.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3290.5	29.4
0°-40°	5278.7	47.2
0°-60°	8995.8	80.4
0°-90°	11191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11191.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4398	4398	4398	4398	4398	
5°	4398	4382	4335	4369	4361	418
15°	4187	4162	4107	4124	4103	1179
25°	3790	3756	3684	3692	3684	1744
35°	3269	3227	3160	3134	3113	2042
45°	2660	2631	2567	2521	2504	2053
55°	2013	1988	1937	1886	1865	1800
65°	1358	1332	1290	1252	1231	1343
75°	710	702	681	656	664	758
85°	173	169	165	152	148	204
90°	0	0	0	0	0	

TEST NUMBER: P930777

CATALOG NUMBER: DFN2DS-PN4F0-120DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4398.5	4398.5	4398.5	4398.5	4398.5
2.5°	4424.0	4402.9	4356.3	4398.5	4390.4
5°	4398.5	4381.8	4335.2	4368.8	4360.7
7.5°	4368.8	4343.7	4297.0	4331.1	4322.6
10°	4322.6	4293.0	4242.3	4275.9	4263.4
12.5°	4258.9	4233.7	4183.0	4204.1	4195.6
15°	4187.1	4161.9	4106.7	4123.8	4102.7
17.5°	4098.3	4073.1	4017.9	4039.0	4017.9
20°	4000.9	3975.7	3916.6	3929.1	3912.5
22.5°	3903.9	3865.8	3810.6	3810.6	3802.1
25°	3789.5	3755.8	3684.1	3692.2	3684.1
27.5°	3662.5	3632.9	3578.2	3565.6	3544.6
30°	3536.0	3501.9	3438.6	3426.1	3409.0
32.5°	3400.4	3375.4	3307.6	3282.0	3265.0
35°	3269.4	3227.3	3159.5	3133.9	3112.8
37.5°	3121.3	3083.3	3015.4	2985.9	2964.8
40°	2969.3	2935.2	2867.4	2829.7	2812.6
42.5°	2821.2	2787.1	2719.7	2677.2	2652.0
45°	2660.5	2630.9	2567.1	2521.0	2503.9
47.5°	2503.9	2474.3	2406.5	2359.9	2334.7
50°	2338.8	2317.7	2258.4	2199.2	2178.1
52.5°	2178.1	2148.5	2093.8	2047.1	2017.5
55°	2013.4	1987.9	1937.1	1886.4	1865.3
57.5°	1848.3	1827.2	1772.0	1721.3	1704.3
60°	1683.2	1666.6	1607.3	1560.7	1548.1
62.5°	1522.6	1492.9	1450.8	1408.6	1391.5
65°	1357.9	1332.3	1290.1	1251.9	1230.9
67.5°	1188.7	1167.1	1129.5	1099.9	1082.8
70°	1032.1	1015.0	976.9	947.3	930.7
72.5°	871.4	854.4	833.3	803.7	791.1
75°	710.4	702.3	680.7	655.6	664.1
77.5°	566.7	549.7	541.2	528.6	516.0
80°	423.1	418.6	410.1	397.6	389.0
82.5°	287.6	287.6	283.6	266.6	266.6
85°	173.2	169.2	165.1	152.1	148.1
87.5°	76.3	67.7	59.3	46.6	42.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930777

CATALOG NUMBER: DFN2DS-PN4F0-120DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.34	16.95	15.70	17.26	17.57	14.89	16.50	15.26	16.82	17.13
	3H	17.09	18.54	17.46	18.87	19.23	16.59	18.05	16.97	18.38	18.74
	4H	17.73	19.10	18.13	19.45	19.82	17.24	18.61	17.64	18.95	19.33
	6H	18.20	19.47	18.61	19.83	20.22	17.70	18.97	18.11	19.33	19.72
	8H	18.34	19.55	18.77	19.94	20.34	17.84	19.05	18.27	19.44	19.84
	12H	18.43	19.59	18.86	19.98	20.40	17.92	19.08	18.35	19.46	19.89
4H	2H	15.90	17.26	16.29	17.61	17.99	15.54	16.91	15.94	17.26	17.64
	3H	17.87	19.02	18.28	19.41	19.81	17.46	18.61	17.87	19.01	19.41
	4H	18.65	19.68	19.08	20.10	20.53	18.22	19.26	18.65	19.67	20.11
	6H	19.24	20.15	19.70	20.59	21.05	18.81	19.72	19.27	20.16	20.61
	8H	19.43	20.28	19.89	20.72	21.19	19.00	19.84	19.46	20.28	20.75
	12H	19.57	20.33	20.05	20.80	21.27	19.11	19.87	19.59	20.35	20.82
8H	4H	18.92	19.77	19.38	20.21	20.68	18.55	19.39	19.01	19.84	20.30
	6H	19.63	20.34	20.13	20.83	21.30	19.25	19.96	19.75	20.44	20.92
	8H	19.89	20.52	20.40	21.03	21.52	19.50	20.13	20.01	20.64	21.13
	12H	20.09	20.65	20.60	21.14	21.70	19.68	20.24	20.19	20.73	21.29
12H	4H	18.95	19.71	19.43	20.18	20.65	18.58	19.34	19.06	19.82	20.29
	6H	19.68	20.31	20.19	20.82	21.31	19.31	19.94	19.82	20.45	20.94
	8H	19.99	20.55	20.50	21.04	21.60	19.62	20.17	20.12	20.66	21.23