

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930189

Luminaire Tested: DFN2DS-HX3F0-060DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-060DS850-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.4 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 61.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930189

CATALOG NUMBER: DFN2DS-HX3F0-060DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930189

CATALOG NUMBER: DFN2DS-HX3F0-060DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2999	2999	2999
5°	3011	2967	2985
10°	2993	2937	2952
15°	2956	2899	2896
20°	2903	2842	2839
25°	2851	2772	2772
30°	2784	2707	2684
35°	2722	2630	2591
40°	2643	2552	2503
45°	2566	2475	2414
50°	2481	2396	2310
55°	2394	2303	2217
60°	2295	2192	2111
65°	2191	2081	1986
70°	2057	1947	1855
75°	1871	1793	1749
80°	1662	1610	1528
85°	1354	1291	1159

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2566 cd/sqm

TEST NUMBER: P930189

CATALOG NUMBER: DFN2DS-HX3F0-060DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	3.7
10°-20°	685.6	10.4
20°-30°	1007.6	15.3
30°-40°	1170.3	17.8
40°-50°	1168.8	17.7
50°-60°	1019.2	15.5
60°-70°	753.4	11.4
70°-80°	426.3	6.5
80°-90°	112.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1937.0	29.4
0°-40°	3107.2	47.2
0°-60°	5295.3	80.4
0°-90°	6587.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6587.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	120
90°	0	0	0	0	0	

TEST NUMBER: P930189

CATALOG NUMBER: DFN2DS-HX3F0-060DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930189

CATALOG NUMBER: DFN2DS-HX3F0-060DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.10	16.71	15.46	17.02	17.34	14.65	16.27	15.02	16.58	16.89
	3H	16.85	18.30	17.23	18.63	18.99	16.36	17.81	16.73	18.14	18.50
	4H	17.49	18.86	17.89	19.21	19.59	17.00	18.37	17.40	18.72	19.09
	6H	17.96	19.23	18.38	19.60	19.99	17.46	18.73	17.87	19.10	19.49
	8H	18.11	19.32	18.53	19.71	20.11	17.60	18.82	18.03	19.20	19.60
	12H	18.20	19.36	18.63	19.74	20.17	17.69	18.85	18.11	19.23	19.66
4H	2H	15.66	17.03	16.06	17.38	17.75	15.31	16.68	15.70	17.02	17.40
	3H	17.63	18.78	18.04	19.18	19.58	17.23	18.37	17.64	18.77	19.17
	4H	18.41	19.45	18.84	19.86	20.30	17.99	19.02	18.42	19.44	19.87
	6H	19.01	19.91	19.46	20.35	20.81	18.57	19.48	19.03	19.92	20.38
	8H	19.20	20.04	19.66	20.49	20.95	18.76	19.61	19.22	20.05	20.51
	12H	19.33	20.09	19.81	20.56	21.03	18.88	19.64	19.36	20.11	20.58
8H	4H	18.68	19.53	19.14	19.97	20.44	18.31	19.16	18.77	19.60	20.06
	6H	19.40	20.10	19.89	20.59	21.06	19.02	19.72	19.51	20.21	20.68
	8H	19.66	20.29	20.17	20.79	21.28	19.27	19.90	19.78	20.40	20.89
	12H	19.86	20.41	20.36	20.91	21.47	19.44	20.00	19.95	20.49	21.05
12H	4H	18.71	19.47	19.19	19.95	20.42	18.35	19.11	18.83	19.58	20.05
	6H	19.44	20.08	19.95	20.58	21.07	19.07	19.71	19.58	20.21	20.70
	8H	19.76	20.32	20.26	20.81	21.37	19.38	19.94	19.89	20.43	20.99