

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930244

Luminaire Tested: DFN2DS-HX3F0-090DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-090DS850-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8483.9 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930244

CATALOG NUMBER: DFN2DS-HX3F0-090DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930244

CATALOG NUMBER: DFN2DS-HX3F0-090DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4778	4778	4778
5°	4797	4718	4744
10°	4760	4642	4602
15°	4705	4504	4374
20°	4629	4307	4091
25°	4552	4084	3817
30°	4444	3855	3465
35°	4340	3606	3157
40°	4234	3347	2800
45°	4110	3058	2477
50°	3983	2765	2160
55°	3852	2450	1855
60°	3701	2119	1540
65°	3530	1780	1402
70°	3325	1466	1289
75°	3074	1337	1203
80°	2714	1194	1097
85°	2132	942	942

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4110 cd/sqm

TEST NUMBER: P930244

CATALOG NUMBER: DFN2DS-HX3F0-090DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.6	4.6
10°-20°	1061.3	12.5
20°-30°	1490.1	17.6
30°-40°	1624.3	19.1
40°-50°	1492.9	17.6
50°-60°	1172.4	13.8
60°-70°	763.1	9.0
70°-80°	392.8	4.6
80°-90°	100.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2938.0	34.6
0°-40°	4562.3	53.8
0°-60°	7227.6	85.2
0°-90°	8483.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8483.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4125	4125	4125	4125	4125	
5°	4125	4106	4058	4091	4080	391
15°	3924	3882	3756	3685	3648	1106
25°	3562	3442	3196	3043	2986	1638
35°	3069	2878	2550	2315	2232	1921
45°	2509	2258	1867	1601	1512	1937
55°	1908	1616	1213	989	918	1705
65°	1288	986	650	523	511	1277
75°	687	425	299	272	269	726
85°	160	82	71	71	71	192
90°	0	0	0	0	0	

TEST NUMBER: P930244

CATALOG NUMBER: DFN2DS-HX3F0-090DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4125.1	4125.1	4125.1	4125.1	4125.1
2.5°	4143.8	4125.1	4083.9	4121.6	4114.1
5°	4125.1	4106.5	4057.8	4091.4	4080.3
7.5°	4091.4	4069.3	4017.0	4031.7	4013.0
10°	4046.7	4020.6	3946.2	3934.6	3912.4
12.5°	3990.8	3957.2	3856.2	3834.0	3792.8
15°	3923.5	3882.4	3755.6	3684.7	3647.5
17.5°	3845.1	3785.3	3628.4	3546.5	3486.7
20°	3755.6	3680.8	3494.1	3401.1	3318.7
22.5°	3658.6	3572.6	3355.9	3229.2	3173.4
25°	3561.6	3441.9	3195.6	3042.7	2986.4
27.5°	3445.9	3318.7	3046.2	2870.8	2784.8
30°	3322.7	3180.5	2881.8	2691.8	2590.7
32.5°	3203.0	3031.1	2725.4	2501.2	2407.7
35°	3068.8	2878.3	2549.9	2314.7	2232.3
37.5°	2938.1	2732.6	2385.6	2127.7	2034.7
40°	2799.9	2576.1	2213.7	1948.7	1851.7
42.5°	2658.1	2419.3	2042.1	1765.7	1672.6
45°	2508.8	2258.5	1866.7	1601.3	1511.8
47.5°	2366.9	2102.0	1698.8	1433.4	1351.4
50°	2210.1	1945.1	1534.4	1276.6	1198.5
52.5°	2056.9	1776.8	1377.6	1131.2	1060.3
55°	1907.5	1616.4	1213.1	989.4	918.5
57.5°	1754.7	1456.0	1067.9	858.7	798.9
60°	1597.7	1299.1	914.6	724.4	664.6
62.5°	1444.9	1146.3	783.8	604.8	575.1
65°	1288.0	985.5	649.5	522.8	511.4
67.5°	1138.7	836.1	522.8	459.0	447.9
70°	981.9	690.8	433.0	395.7	380.6
72.5°	832.5	556.1	362.0	332.3	324.8
75°	686.8	425.4	298.7	272.5	268.9
77.5°	541.4	302.2	235.2	220.2	212.7
80°	406.8	216.7	179.0	164.4	164.4
82.5°	283.6	145.7	123.2	115.7	115.7
85°	160.4	82.0	70.9	70.9	70.9
87.5°	59.8	29.7	29.7	26.2	26.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930244

CATALOG NUMBER: DFN2DS-HX3F0-090DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.67	18.19	17.03	18.50	18.82	12.63	14.15	12.99	14.46	14.78
	3H	18.43	19.80	18.81	20.13	20.49	13.89	15.26	14.27	15.59	15.95
	4H	19.10	20.38	19.50	20.73	21.11	14.40	15.68	14.80	16.03	16.40
	6H	19.59	20.77	20.00	21.14	21.53	14.78	15.96	15.19	16.33	16.72
	8H	19.75	20.88	20.18	21.27	21.67	14.90	16.03	15.33	16.42	16.82
	12H	19.86	20.94	20.29	21.32	21.75	14.98	16.06	15.41	16.44	16.87
4H	2H	16.77	18.05	17.17	18.40	18.78	13.32	14.61	13.72	14.95	15.33
	3H	18.71	19.77	19.12	20.17	20.57	14.77	15.83	15.18	16.23	16.63
	4H	19.46	20.41	19.89	20.83	21.27	15.37	16.32	15.80	16.74	17.18
	6H	20.05	20.88	20.50	21.32	21.78	15.86	16.69	16.31	17.13	17.59
	8H	20.26	21.04	20.73	21.48	21.95	16.02	16.80	16.48	17.24	17.71
	12H	20.42	21.11	20.90	21.59	22.06	16.13	16.83	16.62	17.31	17.78
8H	4H	19.48	20.26	19.94	20.70	21.17	15.72	16.50	16.18	16.94	17.41
	6H	20.12	20.76	20.61	21.25	21.73	16.31	16.95	16.80	17.44	17.92
	8H	20.37	20.94	20.88	21.45	21.94	16.53	17.11	17.04	17.62	18.10
	12H	20.57	21.08	21.08	21.57	22.14	16.71	17.22	17.22	17.71	18.27
12H	4H	19.46	20.16	19.95	20.64	21.11	15.76	16.46	16.25	16.94	17.41
	6H	20.10	20.68	20.61	21.19	21.67	16.37	16.95	16.88	17.46	17.95
	8H	20.38	20.89	20.89	21.38	21.95	16.64	17.15	17.15	17.65	18.21