

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930762

Luminaire Tested: DFN2DS-PN4F0-110DS835-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-110DS835-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9350.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 119
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930762

CATALOG NUMBER: DFN2DS-PN4F0-110DS835-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930762

CATALOG NUMBER: DFN2DS-PN4F0-110DS835-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3319	3319	3319
5°	3331	3277	3295
10°	3306	3224	3196
15°	3268	3128	3038
20°	3215	2991	2841
25°	3161	2837	2651
30°	3087	2677	2407
35°	3014	2504	2192
40°	2940	2325	1945
45°	2854	2124	1720
50°	2766	1920	1500
55°	2675	1702	1288
60°	2571	1471	1069
65°	2452	1237	973
70°	2309	1018	895
75°	2135	928	836
80°	1885	829	762
85°	1481	654	654

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2854 cd/sqm

TEST NUMBER: P930762

CATALOG NUMBER: DFN2DS-PN4F0-110DS835-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	4.6
10°-20°	1169.7	12.5
20°-30°	1642.2	17.6
30°-40°	1790.1	19.1
40°-50°	1645.3	17.6
50°-60°	1292.1	13.8
60°-70°	841.1	9.0
70°-80°	432.9	4.6
80°-90°	110.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3238.0	34.6
0°-40°	5028.1	53.8
0°-60°	7965.5	85.2
0°-90°	9350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9350.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	212
90°	0	0	0	0	0	

TEST NUMBER: P930762

CATALOG NUMBER: DFN2DS-PN4F0-110DS835-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930762

CATALOG NUMBER: DFN2DS-PN4F0-110DS835-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.40	16.92	15.77	17.24	17.55	11.36	12.88	11.73	13.20	13.51
	3H	17.17	18.53	17.55	18.86	19.22	12.63	13.99	13.01	14.32	14.68
	4H	17.83	19.11	18.23	19.46	19.84	13.13	14.41	13.53	14.76	15.14
	6H	18.32	19.51	18.74	19.87	20.26	13.51	14.69	13.92	15.06	15.45
	8H	18.49	19.61	18.91	20.00	20.41	13.64	14.76	14.06	15.15	15.55
	12H	18.59	19.67	19.02	20.05	20.48	13.72	14.79	14.15	15.18	15.61
4H	2H	15.51	16.79	15.91	17.14	17.51	12.06	13.34	12.46	13.69	14.07
	3H	17.44	18.50	17.85	18.90	19.30	13.50	14.56	13.91	14.96	15.37
	4H	18.19	19.15	18.62	19.56	20.00	14.10	15.06	14.53	15.47	15.91
	6H	18.78	19.61	19.24	20.06	20.52	14.59	15.42	15.05	15.86	16.32
	8H	19.00	19.77	19.46	20.22	20.68	14.75	15.53	15.21	15.97	16.44
	12H	19.15	19.84	19.63	20.32	20.79	14.87	15.56	15.35	16.04	16.51
8H	4H	18.21	18.99	18.68	19.43	19.90	14.45	15.23	14.92	15.68	16.14
	6H	18.85	19.49	19.35	19.98	20.46	15.04	15.68	15.54	16.18	16.65
	8H	19.10	19.68	19.61	20.19	20.68	15.26	15.84	15.78	16.35	16.84
	12H	19.31	19.81	19.81	20.31	20.87	15.44	15.95	15.95	16.44	17.01
12H	4H	18.20	18.89	18.68	19.37	19.84	14.50	15.19	14.98	15.67	16.14
	6H	18.83	19.41	19.35	19.92	20.41	15.10	15.68	15.62	16.19	16.68
	8H	19.12	19.63	19.63	20.12	20.68	15.38	15.89	15.89	16.38	16.94