

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930156

Luminaire Tested: DFN2DS-HX3F0-040DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-040DS927-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2692.8 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930156

CATALOG NUMBER: DFN2DS-HX3F0-040DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930156

CATALOG NUMBER: DFN2DS-HX3F0-040DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1517	1517	1517
5°	1522	1498	1506
10°	1511	1473	1461
15°	1493	1429	1388
20°	1469	1367	1299
25°	1445	1296	1212
30°	1411	1223	1100
35°	1377	1144	1002
40°	1344	1063	889
45°	1304	971	786
50°	1264	878	686
55°	1223	778	589
60°	1175	673	489
65°	1120	565	445
70°	1056	465	409
75°	976	424	382
80°	861	379	348
85°	676	299	299

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1304 cd/sqm

TEST NUMBER: P930156

CATALOG NUMBER: DFN2DS-HX3F0-040DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	4.6
10°-20°	336.9	12.5
20°-30°	473.0	17.6
30°-40°	515.5	19.1
40°-50°	473.8	17.6
50°-60°	372.1	13.8
60°-70°	242.2	9.0
70°-80°	124.7	4.6
80°-90°	31.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	932.5	34.6
0°-40°	1448.1	53.8
0°-60°	2294.1	85.2
0°-90°	2692.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2692.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	61
90°	0	0	0	0	0	

TEST NUMBER: P930156

CATALOG NUMBER: DFN2DS-HX3F0-040DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930156

CATALOG NUMBER: DFN2DS-HX3F0-040DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.68	14.20	13.05	14.52	14.83	8.64	10.16	9.01	10.48	10.79
	3H	14.45	15.81	14.82	16.14	16.50	9.91	11.27	10.28	11.60	11.96
	4H	15.11	16.39	15.51	16.74	17.12	10.41	11.69	10.81	12.04	12.42
	6H	15.60	16.79	16.01	17.15	17.54	10.79	11.97	11.20	12.34	12.73
	8H	15.77	16.89	16.19	17.28	17.69	10.91	12.04	11.34	12.43	12.83
	12H	15.87	16.95	16.30	17.33	17.76	11.00	12.07	11.43	12.46	12.89
4H	2H	12.79	14.07	13.19	14.41	14.79	9.34	10.62	9.74	10.97	11.35
	3H	14.72	15.78	15.13	16.18	16.58	10.78	11.84	11.19	12.24	12.64
	4H	15.47	16.43	15.90	16.84	17.28	11.38	12.34	11.81	12.75	13.19
	6H	16.06	16.89	16.52	17.33	17.79	11.87	12.70	12.33	13.14	13.60
	8H	16.27	17.05	16.74	17.50	17.96	12.03	12.81	12.49	13.25	13.72
	12H	16.43	17.12	16.91	17.60	18.07	12.15	12.84	12.63	13.32	13.79
8H	4H	15.49	16.27	15.96	16.71	17.18	11.73	12.51	12.20	12.96	13.42
	6H	16.13	16.77	16.63	17.26	17.74	12.32	12.96	12.82	13.45	13.93
	8H	16.38	16.96	16.89	17.47	17.96	12.54	13.12	13.06	13.63	14.12
	12H	16.59	17.09	17.09	17.59	18.15	12.72	13.23	13.23	13.72	14.29
12H	4H	15.48	16.17	15.96	16.65	17.12	11.78	12.47	12.26	12.95	13.42
	6H	16.11	16.69	16.62	17.20	17.69	12.38	12.96	12.90	13.47	13.96
	8H	16.40	16.91	16.91	17.40	17.96	12.66	13.17	13.17	13.66	14.22