

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930674

Luminaire Tested: DFN2DS-PN4F0-060DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS840-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5105.1 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930674

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930674

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1812	1812	1812
5°	1819	1789	1799
10°	1805	1760	1745
15°	1784	1708	1659
20°	1756	1633	1551
25°	1726	1549	1447
30°	1685	1462	1314
35°	1646	1367	1197
40°	1605	1269	1062
45°	1558	1160	939
50°	1510	1049	819
55°	1461	929	703
60°	1404	803	584
65°	1339	675	531
70°	1261	556	489
75°	1166	507	457
80°	1029	453	416
85°	808	357	357

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1558 cd/sqm

TEST NUMBER: P930674

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.6	4.6
10°-20°	638.6	12.5
20°-30°	896.6	17.6
30°-40°	977.4	19.1
40°-50°	898.3	17.6
50°-60°	705.5	13.8
60°-70°	459.2	9.0
70°-80°	236.4	4.6
80°-90°	60.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1767.9	34.6
0°-40°	2745.3	53.8
0°-60°	4349.1	85.2
0°-90°	5105.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5105.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2482	2482	2482	2482	2482	
5°	2482	2471	2442	2462	2455	235
15°	2361	2336	2260	2217	2195	665
25°	2143	2071	1923	1831	1797	986
35°	1847	1732	1534	1393	1343	1156
45°	1510	1359	1123	964	910	1166
55°	1148	973	730	595	553	1026
65°	775	593	391	315	308	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	116
90°	0	0	0	0	0	

TEST NUMBER: P930674

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2482.3	2482.3	2482.3	2482.3	2482.3
2.5°	2493.5	2482.3	2457.5	2480.1	2475.6
5°	2482.3	2471.1	2441.7	2462.1	2455.4
7.5°	2462.1	2448.6	2417.2	2426.0	2414.8
10°	2435.0	2419.3	2374.6	2367.7	2354.3
12.5°	2401.5	2381.2	2320.4	2307.1	2282.3
15°	2361.0	2336.1	2259.9	2217.2	2194.8
17.5°	2313.8	2277.8	2183.4	2134.0	2098.1
20°	2259.9	2214.8	2102.6	2046.5	1997.0
22.5°	2201.5	2149.7	2019.4	1943.1	1909.5
25°	2143.1	2071.2	1922.9	1830.9	1797.1
27.5°	2073.6	1997.0	1833.0	1727.4	1675.8
30°	1999.4	1913.8	1734.1	1619.7	1559.0
32.5°	1927.4	1824.0	1640.0	1505.1	1448.8
35°	1846.6	1732.0	1534.4	1392.8	1343.2
37.5°	1768.0	1644.2	1435.5	1280.4	1224.3
40°	1684.8	1550.1	1332.0	1172.6	1114.2
42.5°	1599.5	1455.8	1228.8	1062.5	1006.5
45°	1509.6	1359.0	1123.3	963.6	909.7
47.5°	1424.3	1264.9	1022.2	862.6	813.2
50°	1329.9	1170.5	923.3	768.2	721.2
52.5°	1237.6	1069.2	828.9	680.7	638.0
55°	1147.8	972.7	730.0	595.4	552.7
57.5°	1055.9	876.1	642.5	516.7	480.7
60°	961.5	781.8	550.3	435.9	399.9
62.5°	869.5	689.8	471.7	364.0	346.0
65°	775.1	593.0	390.9	314.6	307.7
67.5°	685.2	503.1	314.6	276.3	269.6
70°	590.8	415.6	260.5	238.1	229.0
72.5°	501.0	334.6	217.8	200.0	195.4
75°	413.3	256.0	179.7	164.0	161.9
77.5°	325.8	181.9	141.5	132.5	128.0
80°	244.7	130.3	107.7	98.9	98.9
82.5°	170.7	87.7	74.1	69.6	69.6
85°	96.5	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930674

CATALOG NUMBER: DFN2DS-PN4F0-060DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.30	14.82	13.66	15.14	15.45	9.26	10.78	9.63	11.10	11.41
	3H	15.07	16.43	15.44	16.76	17.12	10.53	11.89	10.90	12.22	12.58
	4H	15.73	17.01	16.13	17.36	17.74	11.03	12.31	11.43	12.66	13.04
	6H	16.22	17.40	16.63	17.77	18.16	11.41	12.59	11.82	12.96	13.35
	8H	16.39	17.51	16.81	17.90	18.30	11.53	12.66	11.96	13.05	13.45
	12H	16.49	17.57	16.92	17.95	18.38	11.61	12.69	12.04	13.07	13.50
4H	2H	13.40	14.68	13.80	15.03	15.41	9.96	11.24	10.36	11.59	11.96
	3H	15.34	16.40	15.75	16.80	17.20	11.40	12.46	11.81	12.86	13.26
	4H	16.09	17.04	16.52	17.46	17.90	12.00	12.96	12.43	13.37	13.81
	6H	16.68	17.51	17.14	17.95	18.41	12.49	13.32	12.94	13.76	14.22
	8H	16.89	17.67	17.36	18.11	18.58	12.65	13.43	13.11	13.87	14.34
	12H	17.05	17.74	17.53	18.22	18.69	12.77	13.46	13.25	13.94	14.41
8H	4H	16.11	16.89	16.57	17.33	17.80	12.35	13.13	12.82	13.57	14.04
	6H	16.75	17.39	17.24	17.88	18.36	12.94	13.58	13.44	14.07	14.55
	8H	17.00	17.58	17.51	18.08	18.57	13.16	13.74	13.67	14.25	14.73
	12H	17.20	17.71	17.71	18.20	18.77	13.34	13.85	13.85	14.34	14.91
12H	4H	16.10	16.79	16.58	17.27	17.74	12.40	13.09	12.88	13.57	14.04
	6H	16.73	17.31	17.24	17.82	18.30	13.00	13.58	13.52	14.09	14.58
	8H	17.01	17.52	17.52	18.02	18.58	13.28	13.79	13.79	14.28	14.84