

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930691

Luminaire Tested: DFN2DS-PN4F0-070DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-070DS840-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6936.9 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930691

CATALOG NUMBER: DFN2DS-PN4F0-070DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930691

CATALOG NUMBER: DFN2DS-PN4F0-070DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1990	1990	1990
5°	1998	1969	1981
10°	1986	1949	1959
15°	1961	1924	1922
20°	1926	1886	1884
25°	1892	1839	1839
30°	1848	1797	1781
35°	1806	1745	1719
40°	1754	1694	1661
45°	1702	1643	1602
50°	1646	1590	1533
55°	1588	1528	1472
60°	1523	1455	1401
65°	1454	1381	1318
70°	1365	1292	1231
75°	1242	1190	1161
80°	1103	1069	1014
85°	900	858	769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1702 cd/sqm

TEST NUMBER: P930691

CATALOG NUMBER: DFN2DS-PN4F0-070DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.6	3.7
10°-20°	722.0	10.4
20°-30°	1061.1	15.3
30°-40°	1232.4	17.8
40°-50°	1230.8	17.7
50°-60°	1073.3	15.5
60°-70°	793.4	11.4
70°-80°	448.9	6.5
80°-90°	118.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2039.7	29.4
0°-40°	3272.1	47.2
0°-60°	5576.2	80.4
0°-90°	6936.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6936.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2726	2726	2726	2726	2726	
5°	2726	2716	2687	2708	2703	259
15°	2596	2580	2546	2556	2543	731
25°	2349	2328	2284	2289	2284	1081
35°	2027	2000	1958	1943	1930	1266
45°	1649	1631	1591	1563	1552	1273
55°	1248	1232	1201	1169	1156	1116
65°	842	826	800	776	763	832
75°	440	435	422	406	412	470
85°	107	105	102	94	92	126
90°	0	0	0	0	0	

TEST NUMBER: P930691

CATALOG NUMBER: DFN2DS-PN4F0-070DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.4	2726.4	2726.4	2726.4	2726.4
2.5°	2742.3	2729.2	2700.3	2726.4	2721.4
5°	2726.4	2716.2	2687.3	2708.1	2703.1
7.5°	2708.1	2692.5	2663.6	2684.8	2679.5
10°	2679.5	2661.1	2629.6	2650.5	2642.7
12.5°	2639.9	2624.4	2593.0	2606.0	2600.7
15°	2595.5	2579.9	2545.6	2556.3	2543.1
17.5°	2540.3	2524.8	2490.6	2503.7	2490.6
20°	2480.0	2464.5	2427.7	2435.5	2425.2
22.5°	2419.9	2396.3	2362.1	2362.1	2356.8
25°	2349.0	2328.1	2283.7	2288.7	2283.7
27.5°	2270.3	2251.9	2218.0	2210.2	2197.1
30°	2191.9	2170.7	2131.5	2123.7	2113.1
32.5°	2107.8	2092.3	2050.2	2034.4	2023.8
35°	2026.6	2000.5	1958.5	1942.6	1929.5
37.5°	1934.8	1911.2	1869.2	1850.8	1837.7
40°	1840.5	1819.4	1777.4	1754.1	1743.4
42.5°	1748.7	1727.6	1685.9	1659.5	1643.8
45°	1649.1	1630.8	1591.3	1562.7	1552.1
47.5°	1552.1	1533.7	1491.7	1462.8	1447.2
50°	1449.7	1436.6	1399.9	1363.3	1350.1
52.5°	1350.1	1331.8	1297.9	1269.0	1250.5
55°	1248.0	1232.2	1200.8	1169.4	1156.3
57.5°	1145.7	1132.6	1098.4	1067.0	1056.5
60°	1043.3	1033.0	996.4	967.5	959.7
62.5°	943.7	925.4	899.3	873.2	862.6
65°	841.7	825.8	799.7	776.1	763.0
67.5°	736.8	723.5	700.1	681.8	671.2
70°	639.7	629.2	605.5	587.2	576.9
72.5°	540.1	529.6	516.5	498.2	490.4
75°	440.3	435.3	421.9	406.4	411.7
77.5°	351.4	340.7	335.4	327.6	319.9
80°	262.3	259.6	254.3	246.4	241.1
82.5°	178.3	178.3	175.8	165.3	165.3
85°	107.4	104.9	102.4	94.3	91.8
87.5°	47.2	42.0	36.7	28.9	26.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930691

CATALOG NUMBER: DFN2DS-PN4F0-070DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.67	15.28	14.04	15.60	15.91	13.23	14.84	13.59	15.15	15.47
	3H	15.42	16.88	15.80	17.20	17.57	14.93	16.39	15.31	16.71	17.07
	4H	16.07	17.44	16.47	17.79	18.16	15.58	16.94	15.97	17.29	17.67
	6H	16.54	17.81	16.95	18.17	18.56	16.04	17.31	16.45	17.67	18.06
	8H	16.68	17.89	17.11	18.28	18.68	16.18	17.39	16.60	17.78	18.18
	12H	16.77	17.93	17.20	18.31	18.74	16.26	17.42	16.69	17.80	18.23
4H	2H	14.23	15.60	14.63	15.95	16.33	13.88	15.25	14.28	15.60	15.97
	3H	16.21	17.36	16.62	17.75	18.15	15.80	16.95	16.21	17.35	17.75
	4H	16.99	18.02	17.42	18.44	18.87	16.56	17.60	16.99	18.01	18.45
	6H	17.58	18.49	18.04	18.93	19.38	17.15	18.05	17.60	18.50	18.95
	8H	17.77	18.62	18.23	19.06	19.53	17.33	18.18	17.79	18.62	19.09
	12H	17.90	18.66	18.38	19.14	19.61	17.45	18.21	17.93	18.69	19.16
8H	4H	17.26	18.11	17.72	18.55	19.01	16.89	17.73	17.35	18.17	18.64
	6H	17.97	18.68	18.47	19.16	19.64	17.59	18.29	18.09	18.78	19.26
	8H	18.23	18.86	18.74	19.37	19.86	17.84	18.47	18.35	18.98	19.46
	12H	18.43	18.99	18.94	19.48	20.04	18.02	18.58	18.53	19.07	19.63
12H	4H	17.28	18.04	17.77	18.52	18.99	16.92	17.68	17.40	18.16	18.63
	6H	18.02	18.65	18.53	19.16	19.64	17.65	18.28	18.16	18.79	19.27
	8H	18.33	18.89	18.84	19.38	19.94	17.95	18.51	18.46	19.00	19.56