

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930728

Luminaire Tested: DFN2DS-PN4F0-090DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-090DS840-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7657.7 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 93.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930728

CATALOG NUMBER: DFN2DS-PN4F0-090DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930728

CATALOG NUMBER: DFN2DS-PN4F0-090DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2718	2718	2718
5°	2728	2684	2699
10°	2707	2640	2618
15°	2676	2562	2488
20°	2633	2450	2327
25°	2589	2323	2171
30°	2528	2193	1971
35°	2468	2051	1796
40°	2408	1904	1593
45°	2338	1739	1409
50°	2265	1573	1229
55°	2191	1394	1055
60°	2105	1205	876
65°	2008	1013	797
70°	1892	834	733
75°	1748	760	684
80°	1544	679	623
85°	1212	536	536

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2338 cd/sqm

TEST NUMBER: P930728

CATALOG NUMBER: DFN2DS-PN4F0-090DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.0	4.6
10°-20°	958.0	12.5
20°-30°	1345.0	17.6
30°-40°	1466.1	19.1
40°-50°	1347.5	17.6
50°-60°	1058.3	13.8
60°-70°	688.8	9.0
70°-80°	354.6	4.6
80°-90°	90.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2651.9	34.6
0°-40°	4118.0	53.8
0°-60°	6523.8	85.2
0°-90°	7657.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7657.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3723	3723	3723	3723	3723	
5°	3723	3707	3663	3693	3683	353
15°	3541	3504	3390	3326	3292	998
25°	3215	3107	2884	2746	2696	1478
35°	2770	2598	2302	2089	2015	1734
45°	2264	2038	1685	1445	1365	1749
55°	1722	1459	1095	893	829	1539
65°	1163	890	586	472	462	1153
75°	620	384	270	246	243	656
85°	145	74	64	64	64	174
90°	0	0	0	0	0	

TEST NUMBER: P930728

CATALOG NUMBER: DFN2DS-PN4F0-090DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3723.4	3723.4	3723.4	3723.4	3723.4
2.5°	3740.2	3723.4	3686.2	3720.2	3713.4
5°	3723.4	3706.6	3662.7	3693.0	3683.0
7.5°	3693.0	3673.0	3625.8	3639.0	3622.2
10°	3652.6	3629.0	3561.9	3551.4	3531.4
12.5°	3602.2	3571.9	3480.7	3460.7	3423.4
15°	3541.4	3504.3	3389.9	3325.8	3292.3
17.5°	3470.7	3416.7	3275.1	3201.1	3147.1
20°	3389.9	3322.3	3153.9	3069.9	2995.5
22.5°	3302.3	3224.7	3029.1	2914.7	2864.4
25°	3214.7	3106.7	2884.4	2746.3	2695.6
27.5°	3110.3	2995.5	2749.5	2591.2	2513.6
30°	2999.1	2870.8	2601.2	2429.6	2338.4
32.5°	2891.1	2735.9	2460.0	2257.7	2173.3
35°	2770.0	2598.0	2301.6	2089.3	2014.9
37.5°	2651.9	2466.5	2153.3	1920.5	1836.5
40°	2527.2	2325.2	1998.1	1759.0	1671.4
42.5°	2399.2	2183.7	1843.2	1593.8	1509.7
45°	2264.5	2038.5	1684.9	1445.3	1364.6
47.5°	2136.4	1897.3	1533.3	1293.8	1219.8
50°	1994.9	1755.7	1385.0	1152.3	1081.8
52.5°	1856.6	1603.8	1243.4	1021.0	957.1
55°	1721.7	1459.0	1095.0	893.1	829.0
57.5°	1583.8	1314.2	963.9	775.1	721.1
60°	1442.1	1172.6	825.5	653.9	599.9
62.5°	1304.2	1034.6	707.5	545.9	519.1
65°	1162.6	889.5	586.3	471.9	461.6
67.5°	1027.8	754.7	471.9	414.3	404.3
70°	886.3	623.5	390.8	357.2	343.5
72.5°	751.5	501.9	326.7	299.9	293.2
75°	619.9	384.0	269.6	245.9	242.7
77.5°	488.7	272.8	212.3	198.8	192.0
80°	367.2	195.6	161.6	148.3	148.3
82.5°	256.0	131.5	111.2	104.4	104.4
85°	144.7	74.0	64.0	64.0	64.0
87.5°	54.0	26.8	26.8	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930728

CATALOG NUMBER: DFN2DS-PN4F0-090DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.71	16.23	15.07	16.54	16.86	10.67	12.19	11.03	12.50	12.82
	3H	16.47	17.84	16.85	18.17	18.53	11.93	13.30	12.31	13.63	13.99
	4H	17.14	18.42	17.54	18.77	19.15	12.44	13.72	12.84	14.07	14.44
	6H	17.63	18.81	18.04	19.18	19.57	12.82	14.00	13.23	14.37	14.76
	8H	17.79	18.92	18.22	19.31	19.71	12.94	14.07	13.37	14.46	14.86
	12H	17.90	18.98	18.33	19.36	19.79	13.02	14.10	13.45	14.48	14.91
4H	2H	14.81	16.09	15.21	16.44	16.82	11.36	12.65	11.76	12.99	13.37
	3H	16.75	17.81	17.16	18.21	18.61	12.81	13.87	13.22	14.27	14.67
	4H	17.50	18.45	17.93	18.87	19.31	13.41	14.36	13.84	14.78	15.22
	6H	18.09	18.92	18.54	19.36	19.82	13.90	14.73	14.35	15.17	15.63
	8H	18.30	19.08	18.77	19.52	19.99	14.06	14.83	14.52	15.28	15.75
	12H	18.46	19.15	18.94	19.63	20.10	14.17	14.87	14.66	15.35	15.82
8H	4H	17.52	18.30	17.98	18.74	19.21	13.76	14.54	14.22	14.98	15.45
	6H	18.16	18.80	18.65	19.29	19.77	14.35	14.99	14.84	15.48	15.96
	8H	18.41	18.98	18.92	19.49	19.98	14.57	15.14	15.08	15.65	16.14
	12H	18.61	19.12	19.12	19.61	20.18	14.75	15.26	15.26	15.75	16.31
12H	4H	17.50	18.20	17.99	18.68	19.15	13.80	14.50	14.29	14.98	15.45
	6H	18.14	18.72	18.65	19.23	19.71	14.41	14.99	14.92	15.50	15.99
	8H	18.42	18.93	18.93	19.42	19.99	14.68	15.19	15.19	15.69	16.25

END OF REPORT