

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930212

Luminaire Tested: DFN2DS-HX3F0-070DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-070DS930-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4849.2 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 73.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930212

CATALOG NUMBER: DFN2DS-HX3F0-070DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930212

CATALOG NUMBER: DFN2DS-HX3F0-070DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2731	2731	2731
5°	2742	2697	2712
10°	2721	2653	2630
15°	2689	2574	2500
20°	2646	2462	2338
25°	2602	2334	2182
30°	2540	2203	1981
35°	2480	2061	1804
40°	2420	1913	1600
45°	2349	1748	1416
50°	2276	1580	1235
55°	2202	1400	1060
60°	2116	1211	880
65°	2018	1018	801
70°	1901	838	737
75°	1757	764	688
80°	1551	683	627
85°	1219	538	538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2349 cd/sqm

TEST NUMBER: P930212

CATALOG NUMBER: DFN2DS-HX3F0-070DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	4.6
10°-20°	606.6	12.5
20°-30°	851.7	17.6
30°-40°	928.4	19.1
40°-50°	853.3	17.6
50°-60°	670.1	13.8
60°-70°	436.2	9.0
70°-80°	224.5	4.6
80°-90°	57.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1679.3	34.6
0°-40°	2607.7	53.8
0°-60°	4131.2	85.2
0°-90°	4849.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4849.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2358	2358	2358	2358	2358	
5°	2358	2347	2319	2339	2332	224
15°	2243	2219	2147	2106	2085	632
25°	2036	1967	1826	1739	1707	936
35°	1754	1645	1458	1323	1276	1098
45°	1434	1291	1067	915	864	1107
55°	1090	924	693	566	525	974
65°	736	563	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	110
90°	0	0	0	0	0	

TEST NUMBER: P930212

CATALOG NUMBER: DFN2DS-HX3F0-070DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2357.9	2357.9	2357.9	2357.9	2357.9
2.5°	2368.5	2357.9	2334.3	2355.8	2351.5
5°	2357.9	2347.2	2319.4	2338.6	2332.3
7.5°	2338.6	2325.9	2296.1	2304.4	2293.8
10°	2313.1	2298.1	2255.5	2249.0	2236.3
12.5°	2281.1	2261.9	2204.2	2191.5	2167.9
15°	2242.6	2219.1	2146.6	2106.1	2084.9
17.5°	2197.8	2163.7	2074.0	2027.1	1992.9
20°	2146.6	2103.8	1997.2	1944.0	1896.9
22.5°	2091.2	2042.1	1918.2	1845.7	1813.9
25°	2035.7	1967.3	1826.5	1739.1	1707.0
27.5°	1969.6	1896.9	1741.2	1640.9	1591.8
30°	1899.2	1817.9	1647.2	1538.6	1480.9
32.5°	1830.8	1732.6	1557.8	1429.7	1376.2
35°	1754.0	1645.2	1457.5	1323.1	1276.0
37.5°	1679.4	1561.9	1363.6	1216.1	1163.0
40°	1600.3	1472.5	1265.3	1113.9	1058.4
42.5°	1519.3	1382.8	1167.2	1009.2	956.1
45°	1434.0	1290.9	1067.0	915.3	864.1
47.5°	1352.9	1201.5	971.0	819.3	772.5
50°	1263.2	1111.8	877.0	729.7	685.1
52.5°	1175.6	1015.6	787.4	646.5	606.0
55°	1090.3	923.9	693.4	565.5	525.0
57.5°	1002.9	832.2	610.4	490.8	456.6
60°	913.3	742.5	522.7	414.1	379.9
62.5°	825.8	655.2	448.0	345.7	328.7
65°	736.2	563.2	371.3	298.9	292.3
67.5°	650.9	477.9	298.9	262.3	256.1
70°	561.2	394.8	247.4	226.2	217.5
72.5°	475.9	317.8	206.9	190.0	185.7
75°	392.6	243.1	170.7	155.7	153.7
77.5°	309.5	172.7	134.5	125.8	121.6
80°	232.5	123.8	102.4	94.0	94.0
82.5°	162.1	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.1	17.0	17.0	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930212

CATALOG NUMBER: DFN2DS-HX3F0-070DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.73	16.25	15.09	16.56	16.88	10.69	12.21	11.05	12.52	12.84
	3H	16.49	17.86	16.87	18.18	18.55	11.95	13.32	12.33	13.64	14.01
	4H	17.16	18.44	17.56	18.79	19.16	12.45	13.73	12.85	14.08	14.46
	6H	17.65	18.83	18.06	19.20	19.59	12.83	14.02	13.25	14.38	14.78
	8H	17.81	18.94	18.24	19.33	19.73	12.96	14.09	13.38	14.47	14.88
	12H	17.91	18.99	18.35	19.37	19.80	13.04	14.12	13.47	14.50	14.93
4H	2H	14.83	16.11	15.23	16.46	16.84	11.38	12.66	11.78	13.01	13.39
	3H	16.76	17.83	17.17	18.23	18.63	12.82	13.89	13.24	14.29	14.69
	4H	17.51	18.47	17.94	18.88	19.32	13.42	14.38	13.86	14.80	15.23
	6H	18.10	18.94	18.56	19.38	19.84	13.91	14.74	14.37	15.19	15.65
	8H	18.32	19.10	18.78	19.54	20.01	14.07	14.85	14.54	15.30	15.76
	12H	18.47	19.17	18.95	19.64	20.12	14.19	14.89	14.67	15.36	15.84
8H	4H	17.54	18.31	18.00	18.76	19.23	13.78	14.56	14.24	15.00	15.47
	6H	18.17	18.82	18.67	19.31	19.78	14.36	15.01	14.86	15.50	15.98
	8H	18.42	19.00	18.94	19.51	20.00	14.59	15.16	15.10	15.67	16.16
	12H	18.63	19.14	19.14	19.63	20.19	14.76	15.27	15.27	15.77	16.33
12H	4H	17.52	18.22	18.00	18.69	19.16	13.82	14.52	14.30	14.99	15.46
	6H	18.15	18.73	18.67	19.24	19.73	14.43	15.01	14.94	15.52	16.00
	8H	18.44	18.95	18.95	19.44	20.01	14.70	15.21	15.21	15.70	16.27