

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930657

Luminaire Tested: DFN2DS-PN4F0-050DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-050DS850-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.6 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 48.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930657

CATALOG NUMBER: DFN2DS-PN4F0-050DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930657

CATALOG NUMBER: DFN2DS-PN4F0-050DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1575	1575	1575
5°	1581	1558	1567
10°	1572	1542	1550
15°	1552	1522	1521
20°	1525	1492	1491
25°	1497	1455	1455
30°	1462	1422	1410
35°	1429	1381	1361
40°	1388	1340	1315
45°	1347	1300	1268
50°	1303	1258	1213
55°	1257	1209	1164
60°	1205	1151	1109
65°	1151	1093	1043
70°	1081	1023	975
75°	983	942	919
80°	873	846	802
85°	711	678	608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1347 cd/sqm

TEST NUMBER: P930657

CATALOG NUMBER: DFN2DS-PN4F0-050DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	3.7
10°-20°	571.4	10.4
20°-30°	839.7	15.3
30°-40°	975.2	17.8
40°-50°	974.0	17.7
50°-60°	849.3	15.5
60°-70°	627.9	11.4
70°-80°	355.2	6.5
80°-90°	93.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1614.1	29.4
0°-40°	2589.4	47.2
0°-60°	4412.7	80.4
0°-90°	5489.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5489.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2126	2143	2139	205
15°	2054	2042	2014	2023	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	100
90°	0	0	0	0	0	

TEST NUMBER: P930657

CATALOG NUMBER: DFN2DS-PN4F0-050DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.6	2157.6	2157.6	2157.6	2157.6
2.5°	2170.1	2159.8	2136.9	2157.6	2153.7
5°	2157.6	2149.5	2126.5	2143.0	2139.2
7.5°	2143.0	2130.7	2107.9	2124.6	2120.4
10°	2120.4	2105.9	2081.0	2097.5	2091.4
12.5°	2089.1	2076.8	2052.0	2062.3	2058.1
15°	2053.9	2041.6	2014.5	2022.9	2012.5
17.5°	2010.3	1998.0	1970.9	1981.2	1970.9
20°	1962.6	1950.3	1921.2	1927.3	1919.2
22.5°	1915.0	1896.3	1869.2	1869.2	1865.0
25°	1858.9	1842.4	1807.1	1811.1	1807.1
27.5°	1796.6	1782.1	1755.2	1749.0	1738.7
30°	1734.5	1717.8	1686.8	1680.6	1672.3
32.5°	1668.0	1655.7	1622.5	1609.9	1601.6
35°	1603.7	1583.1	1549.8	1537.3	1527.0
37.5°	1531.1	1512.5	1479.2	1464.7	1454.3
40°	1456.6	1439.8	1406.5	1388.0	1379.7
42.5°	1383.9	1367.2	1334.1	1313.2	1300.9
45°	1305.1	1290.5	1259.3	1236.6	1228.2
47.5°	1228.2	1213.7	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.8	1068.4
52.5°	1068.4	1053.9	1027.0	1004.2	989.7
55°	987.7	975.1	950.2	925.3	915.0
57.5°	906.6	896.3	869.2	844.4	836.0
60°	825.7	817.6	788.5	765.5	759.4
62.5°	746.9	732.4	711.6	690.9	682.6
65°	666.1	653.5	632.8	614.2	603.7
67.5°	583.1	572.6	554.1	539.5	531.1
70°	506.3	497.9	479.2	464.7	456.6
72.5°	427.5	419.1	408.8	394.2	388.0
75°	348.4	344.5	333.9	321.6	325.8
77.5°	278.0	269.6	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.1	190.9
82.5°	141.1	141.1	139.1	130.8	130.8
85°	84.9	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.8	20.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930657

CATALOG NUMBER: DFN2DS-PN4F0-050DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.86	14.47	13.23	14.79	15.10	12.42	14.03	12.78	14.34	14.66
	3H	14.61	16.07	14.99	16.39	16.75	14.12	15.57	14.50	15.90	16.26
	4H	15.26	16.63	15.66	16.97	17.35	14.76	16.13	15.16	16.48	16.86
	6H	15.73	16.99	16.14	17.36	17.75	15.23	16.49	15.64	16.86	17.25
	8H	15.87	17.08	16.29	17.47	17.87	15.37	16.58	15.79	16.97	17.37
	12H	15.96	17.12	16.39	17.50	17.93	15.45	16.61	15.88	16.99	17.42
4H	2H	13.42	14.79	13.82	15.14	15.51	13.07	14.44	13.47	14.79	15.16
	3H	15.40	16.54	15.81	16.94	17.34	14.99	16.14	15.40	16.53	16.93
	4H	16.17	17.21	16.60	17.62	18.06	15.75	16.78	16.18	17.20	17.63
	6H	16.77	17.67	17.22	18.11	18.57	16.34	17.24	16.79	17.68	18.14
	8H	16.96	17.81	17.42	18.25	18.71	16.52	17.37	16.98	17.81	18.28
	12H	17.09	17.85	17.57	18.33	18.80	16.64	17.40	17.12	17.87	18.34
8H	4H	16.45	17.29	16.91	17.74	18.20	16.07	16.92	16.53	17.36	17.83
	6H	17.16	17.86	17.65	18.35	18.83	16.78	17.48	17.27	17.97	18.45
	8H	17.42	18.05	17.93	18.56	19.04	17.03	17.66	17.54	18.17	18.65
	12H	17.62	18.18	18.13	18.67	19.23	17.21	17.76	17.71	18.26	18.82
12H	4H	16.47	17.23	16.95	17.71	18.18	16.11	16.87	16.59	17.34	17.81
	6H	17.21	17.84	17.72	18.34	18.83	16.84	17.47	17.35	17.98	18.46
	8H	17.52	18.08	18.03	18.57	19.13	17.14	17.70	17.65	18.19	18.75