

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930676

Luminaire Tested: DFN2DS-PN4F0-060DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS850-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5655.9 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930676

CATALOG NUMBER: DFN2DS-PN4F0-060DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930676

CATALOG NUMBER: DFN2DS-PN4F0-060DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2007	2007	2007
5°	2015	1982	1993
10°	2000	1950	1933
15°	1977	1892	1838
20°	1945	1810	1719
25°	1912	1716	1604
30°	1867	1619	1456
35°	1823	1515	1326
40°	1779	1406	1176
45°	1727	1285	1040
50°	1673	1162	907
55°	1618	1029	779
60°	1555	890	647
65°	1483	748	589
70°	1397	616	541
75°	1291	562	506
80°	1140	501	461
85°	895	395	395

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1727 cd/sqm

TEST NUMBER: P930676

CATALOG NUMBER: DFN2DS-PN4F0-060DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	4.6
10°-20°	707.6	12.5
20°-30°	993.4	17.6
30°-40°	1082.8	19.1
40°-50°	995.2	17.6
50°-60°	781.6	13.8
60°-70°	508.8	9.0
70°-80°	261.9	4.6
80°-90°	66.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1958.7	34.6
0°-40°	3041.5	53.8
0°-60°	4818.4	85.2
0°-90°	5655.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5655.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	128
90°	0	0	0	0	0	

TEST NUMBER: P930676

CATALOG NUMBER: DFN2DS-PN4F0-060DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930676

CATALOG NUMBER: DFN2DS-PN4F0-060DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.66	15.18	14.02	15.49	15.81	9.62	11.14	9.98	11.45	11.77
	3H	15.42	16.79	15.80	17.11	17.48	10.88	12.25	11.26	12.57	12.94
	4H	16.09	17.37	16.49	17.72	18.10	11.38	12.66	11.78	13.01	13.39
	6H	16.58	17.76	16.99	18.13	18.52	11.76	12.95	12.18	13.31	13.71
	8H	16.74	17.87	17.17	18.26	18.66	11.89	13.02	12.32	13.41	13.81
	12H	16.84	17.92	17.28	18.31	18.73	11.97	13.05	12.40	13.43	13.86
4H	2H	13.76	15.04	14.16	15.39	15.77	10.31	11.59	10.71	11.94	12.32
	3H	15.69	16.76	16.10	17.16	17.56	11.76	12.82	12.17	13.22	13.62
	4H	16.44	17.40	16.88	17.81	18.25	12.35	13.31	12.79	13.73	14.17
	6H	17.03	17.87	17.49	18.31	18.77	12.84	13.68	13.30	14.12	14.58
	8H	17.25	18.03	17.71	18.47	18.94	13.00	13.78	13.47	14.23	14.69
	12H	17.40	18.10	17.88	18.58	19.05	13.12	13.82	13.60	14.29	14.77
8H	4H	16.47	17.24	16.93	17.69	18.16	12.71	13.49	13.17	13.93	14.40
	6H	17.10	17.75	17.60	18.24	18.72	13.30	13.94	13.79	14.43	14.91
	8H	17.35	17.93	17.87	18.44	18.93	13.52	14.09	14.03	14.60	15.09
	12H	17.56	18.07	18.07	18.56	19.13	13.70	14.20	14.20	14.70	15.26
12H	4H	16.45	17.15	16.93	17.62	18.10	12.75	13.45	13.23	13.92	14.40
	6H	17.08	17.66	17.60	18.17	18.66	13.36	13.94	13.87	14.45	14.93
	8H	17.37	17.88	17.88	18.37	18.94	13.63	14.14	14.14	14.63	15.20