

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930712

Luminaire Tested: DFN2DS-PN4F0-080DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-080DS850-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7541.2 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 81.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930712

CATALOG NUMBER: DFN2DS-PN4F0-080DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930712

CATALOG NUMBER: DFN2DS-PN4F0-080DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2677	2677	2677
5°	2687	2643	2658
10°	2666	2600	2578
15°	2636	2523	2450
20°	2593	2413	2291
25°	2550	2288	2138
30°	2489	2159	1941
35°	2431	2020	1768
40°	2372	1875	1568
45°	2302	1713	1387
50°	2231	1549	1210
55°	2158	1372	1039
60°	2073	1187	863
65°	1978	997	785
70°	1863	821	722
75°	1722	749	674
80°	1520	669	614
85°	1194	528	528

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2302 cd/sqm

TEST NUMBER: P930712

CATALOG NUMBER: DFN2DS-PN4F0-080DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	4.6
10°-20°	943.4	12.5
20°-30°	1324.5	17.6
30°-40°	1443.8	19.1
40°-50°	1327.0	17.6
50°-60°	1042.1	13.8
60°-70°	678.3	9.0
70°-80°	349.2	4.6
80°-90°	89.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2611.6	34.6
0°-40°	4055.4	53.8
0°-60°	6424.5	85.2
0°-90°	7541.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7541.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	171
90°	0	0	0	0	0	

TEST NUMBER: P930712

CATALOG NUMBER: DFN2DS-PN4F0-080DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930712

CATALOG NUMBER: DFN2DS-PN4F0-080DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.66	16.18	15.02	16.49	16.81	10.62	12.14	10.98	12.45	12.77
	3H	16.42	17.79	16.80	18.11	18.48	11.88	13.25	12.26	13.57	13.94
	4H	17.09	18.37	17.49	18.72	19.09	12.38	13.66	12.78	14.01	14.39
	6H	17.58	18.76	17.99	19.13	19.52	12.76	13.95	13.18	14.31	14.71
	8H	17.74	18.87	18.17	19.26	19.66	12.89	14.02	13.31	14.40	14.81
	12H	17.84	18.92	18.27	19.30	19.73	12.97	14.05	13.40	14.43	14.86
4H	2H	14.76	16.04	15.16	16.39	16.77	11.31	12.59	11.71	12.94	13.32
	3H	16.69	17.76	17.10	18.16	18.56	12.75	13.82	13.17	14.22	14.62
	4H	17.44	18.40	17.87	18.81	19.25	13.35	14.31	13.79	14.73	15.16
	6H	18.03	18.87	18.49	19.31	19.77	13.84	14.67	14.30	15.12	15.58
	8H	18.25	19.03	18.71	19.47	19.94	14.00	14.78	14.47	15.23	15.69
	12H	18.40	19.10	18.88	19.57	20.05	14.12	14.82	14.60	15.29	15.77
8H	4H	17.47	18.24	17.93	18.69	19.16	13.71	14.49	14.17	14.93	15.40
	6H	18.10	18.75	18.60	19.24	19.71	14.29	14.94	14.79	15.43	15.91
	8H	18.35	18.93	18.87	19.44	19.93	14.52	15.09	15.03	15.60	16.09
	12H	18.56	19.07	19.07	19.56	20.12	14.69	15.20	15.20	15.70	16.26
12H	4H	17.45	18.15	17.93	18.62	19.09	13.75	14.45	14.23	14.92	15.40
	6H	18.08	18.66	18.60	19.17	19.66	14.36	14.94	14.87	15.44	15.93
	8H	18.37	18.88	18.88	19.37	19.94	14.63	15.14	15.14	15.63	16.20