

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930178

Luminaire Tested: DFN2DS-HX3F0-050DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-050DS935-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3655.0 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930178

CATALOG NUMBER: DFN2DS-HX3F0-050DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930178

CATALOG NUMBER: DFN2DS-HX3F0-050DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2059	2059	2059
5°	2066	2033	2044
10°	2051	2000	1983
15°	2027	1940	1884
20°	1994	1856	1763
25°	1961	1760	1644
30°	1915	1661	1493
35°	1870	1554	1360
40°	1824	1442	1206
45°	1771	1317	1067
50°	1716	1191	930
55°	1660	1055	799
60°	1595	913	663
65°	1521	767	604
70°	1433	632	555
75°	1324	576	518
80°	1169	514	472
85°	918	405	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1771 cd/sqm

TEST NUMBER: P930178

CATALOG NUMBER: DFN2DS-HX3F0-050DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	4.6
10°-20°	457.2	12.5
20°-30°	641.9	17.6
30°-40°	699.8	19.1
40°-50°	643.2	17.6
50°-60°	505.1	13.8
60°-70°	328.8	9.0
70°-80°	169.3	4.6
80°-90°	43.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1265.8	34.6
0°-40°	1965.5	53.8
0°-60°	3113.8	85.2
0°-90°	3655.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3655.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1777	1769	1748	1763	1758	169
15°	1690	1673	1618	1588	1571	476
25°	1534	1483	1377	1311	1287	706
35°	1322	1240	1099	997	962	827
45°	1081	973	804	690	651	835
55°	822	696	523	426	396	734
65°	555	425	280	225	220	550
75°	296	183	129	117	116	313
85°	69	35	30	30	30	83
90°	0	0	0	0	0	

TEST NUMBER: P930178

CATALOG NUMBER: DFN2DS-HX3F0-050DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1777.2	1777.2	1777.2	1777.2	1777.2
2.5°	1785.2	1777.2	1759.5	1775.6	1772.4
5°	1777.2	1769.2	1748.2	1762.7	1757.9
7.5°	1762.7	1753.1	1730.6	1736.9	1728.9
10°	1743.4	1732.1	1700.0	1695.1	1685.5
12.5°	1719.3	1704.9	1661.3	1651.8	1634.0
15°	1690.3	1672.6	1618.0	1587.5	1571.4
17.5°	1656.5	1630.8	1563.2	1527.9	1502.1
20°	1618.0	1585.8	1505.3	1465.3	1429.8
22.5°	1576.2	1539.1	1445.8	1391.2	1367.1
25°	1534.3	1482.8	1376.7	1310.8	1286.6
27.5°	1484.5	1429.8	1312.4	1236.8	1199.8
30°	1431.5	1370.2	1241.6	1159.6	1116.1
32.5°	1380.0	1305.9	1174.2	1077.6	1037.3
35°	1322.1	1240.0	1098.6	997.2	961.7
37.5°	1265.7	1177.3	1027.8	916.7	876.6
40°	1206.2	1109.8	953.7	839.5	797.7
42.5°	1145.2	1042.2	879.8	760.7	720.6
45°	1080.8	973.0	804.2	689.9	651.3
47.5°	1019.7	905.6	731.9	617.6	582.2
50°	952.2	838.0	661.1	550.0	516.3
52.5°	886.1	765.5	593.5	487.4	456.8
55°	821.8	696.3	522.6	426.2	395.7
57.5°	755.9	627.3	460.0	370.0	344.2
60°	688.3	559.7	394.0	312.1	286.3
62.5°	622.5	493.8	337.7	260.6	247.8
65°	554.9	424.6	279.8	225.2	220.3
67.5°	490.5	360.3	225.2	197.8	193.0
70°	423.0	297.6	186.5	170.5	164.0
72.5°	358.7	239.6	156.0	143.2	139.9
75°	295.9	183.3	128.7	117.4	115.8
77.5°	233.2	130.2	101.4	94.9	91.6
80°	175.3	93.3	77.1	70.8	70.8
82.5°	122.2	62.8	53.1	49.8	49.8
85°	69.1	35.3	30.5	30.5	30.5
87.5°	25.8	12.8	12.8	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930178

CATALOG NUMBER: DFN2DS-HX3F0-050DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.74	15.27	14.11	15.58	15.89	9.70	11.23	10.07	11.54	11.85
	3H	15.51	16.87	15.89	17.20	17.56	10.97	12.34	11.35	12.66	13.02
	4H	16.18	17.46	16.57	17.80	18.18	11.47	12.75	11.87	13.10	13.48
	6H	16.66	17.85	17.08	18.21	18.61	11.85	13.03	12.26	13.40	13.79
	8H	16.83	17.96	17.26	18.35	18.75	11.98	13.10	12.40	13.49	13.89
	12H	16.93	18.01	17.36	18.39	18.82	12.06	13.14	12.49	13.52	13.95
4H	2H	13.85	15.13	14.25	15.48	15.86	10.40	11.68	10.80	12.03	12.41
	3H	15.78	16.84	16.19	17.24	17.64	11.84	12.91	12.25	13.31	13.71
	4H	16.53	17.49	16.96	17.90	18.34	12.44	13.40	12.87	13.81	14.25
	6H	17.12	17.95	17.58	18.40	18.86	12.93	13.76	13.39	14.20	14.66
	8H	17.34	18.11	17.80	18.56	19.03	13.09	13.87	13.56	14.31	14.78
	12H	17.49	18.18	17.97	18.66	19.13	13.21	13.90	13.69	14.38	14.85
8H	4H	16.55	17.33	17.02	17.78	18.24	12.80	13.57	13.26	14.02	14.49
	6H	17.19	17.83	17.69	18.33	18.80	13.38	14.03	13.88	14.52	14.99
	8H	17.44	18.02	17.96	18.53	19.02	13.60	14.18	14.12	14.69	15.18
	12H	17.65	18.16	18.16	18.65	19.21	13.78	14.29	14.29	14.78	15.35
12H	4H	16.54	17.23	17.02	17.71	18.18	12.84	13.53	13.32	14.01	14.48
	6H	17.17	17.75	17.69	18.26	18.75	13.45	14.02	13.96	14.53	15.02
	8H	17.46	17.97	17.97	18.46	19.02	13.72	14.23	14.23	14.72	15.29

END OF REPORT