

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930660

Luminaire Tested: DFN2DS-PN4F0-050DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-050DS927-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3366.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 48.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930660

CATALOG NUMBER: DFN2DS-PN4F0-050DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930660

CATALOG NUMBER: DFN2DS-PN4F0-050DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1195	1195	1195
5°	1199	1180	1186
10°	1190	1160	1151
15°	1176	1126	1094
20°	1158	1077	1023
25°	1138	1021	954
30°	1111	964	866
35°	1085	902	789
40°	1059	837	700
45°	1028	765	619
50°	996	691	540
55°	963	613	464
60°	925	530	385
65°	883	445	350
70°	832	367	322
75°	769	334	301
80°	678	298	274
85°	534	235	235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1028 cd/sqm

TEST NUMBER: P930660

CATALOG NUMBER: DFN2DS-PN4F0-050DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	4.6
10°-20°	421.1	12.5
20°-30°	591.2	17.6
30°-40°	644.4	19.1
40°-50°	592.3	17.6
50°-60°	465.2	13.8
60°-70°	302.8	9.0
70°-80°	155.9	4.6
80°-90°	39.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.7	34.6
0°-40°	1810.1	53.8
0°-60°	2867.6	85.2
0°-90°	3366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3366.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1629	1610	1623	1619	155
15°	1557	1540	1490	1462	1447	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	995	896	741	635	600	769
55°	757	641	481	392	364	676
65°	511	391	258	207	203	507
75°	272	169	118	108	107	288
85°	64	33	28	28	28	76
90°	0	0	0	0	0	

TEST NUMBER: P930660

CATALOG NUMBER: DFN2DS-PN4F0-050DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	1644.0	1636.7	1620.4	1635.2	1632.2
5°	1636.7	1629.3	1610.0	1623.3	1618.9
7.5°	1623.3	1614.5	1593.7	1599.6	1592.2
10°	1605.5	1595.2	1565.6	1561.1	1552.2
12.5°	1583.4	1570.1	1530.0	1521.2	1504.8
15°	1556.7	1540.4	1490.1	1462.0	1447.1
17.5°	1525.6	1501.9	1439.6	1407.1	1383.3
20°	1490.1	1460.4	1386.3	1349.4	1316.7
22.5°	1451.6	1417.4	1331.5	1281.2	1259.0
25°	1413.0	1365.6	1267.8	1207.2	1184.8
27.5°	1367.2	1316.7	1208.6	1139.0	1104.9
30°	1318.3	1261.9	1143.4	1067.9	1027.9
32.5°	1270.8	1202.7	1081.3	992.4	955.3
35°	1217.5	1142.0	1011.7	918.3	885.7
37.5°	1165.7	1084.2	946.5	844.2	807.3
40°	1110.9	1022.1	878.2	773.2	734.7
42.5°	1054.6	959.8	810.2	700.5	663.6
45°	995.4	896.1	740.6	635.3	599.8
47.5°	939.1	834.0	674.0	568.7	536.2
50°	876.9	771.7	608.8	506.5	475.5
52.5°	816.1	705.0	546.6	448.8	420.7
55°	756.8	641.3	481.3	392.5	364.4
57.5°	696.2	577.7	423.6	340.7	317.0
60°	633.9	515.4	362.8	287.4	263.7
62.5°	573.2	454.8	311.0	240.0	228.2
65°	511.0	391.0	257.7	207.4	202.9
67.5°	451.8	331.8	207.4	182.2	177.7
70°	389.6	274.0	171.8	157.0	151.0
72.5°	330.3	220.7	143.7	131.9	128.9
75°	272.5	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.3
80°	161.4	85.9	71.0	65.2	65.2
82.5°	112.5	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930660

CATALOG NUMBER: DFN2DS-PN4F0-050DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.85	13.37	12.22	13.69	14.00	7.81	9.34	8.18	9.65	9.96
	3H	13.62	14.98	14.00	15.31	15.67	9.08	10.44	9.46	10.77	11.13
	4H	14.28	15.57	14.68	15.91	16.29	9.58	10.86	9.98	11.21	11.59
	6H	14.77	15.96	15.19	16.32	16.71	9.96	11.14	10.37	11.51	11.90
	8H	14.94	16.07	15.37	16.45	16.86	10.09	11.21	10.51	11.60	12.00
	12H	15.04	16.12	15.47	16.50	16.93	10.17	11.24	10.60	11.63	12.06
4H	2H	11.96	13.24	12.36	13.59	13.96	8.51	9.79	8.91	10.14	10.52
	3H	13.89	14.95	14.30	15.35	15.75	9.95	11.02	10.36	11.41	11.82
	4H	14.64	15.60	15.07	16.01	16.45	10.55	11.51	10.98	11.92	12.36
	6H	15.23	16.06	15.69	16.51	16.97	11.04	11.87	11.50	12.31	12.77
	8H	15.45	16.22	15.91	16.67	17.13	11.20	11.98	11.66	12.42	12.89
	12H	15.60	16.29	16.08	16.77	17.24	11.32	12.01	11.80	12.49	12.96
8H	4H	14.66	15.44	15.13	15.89	16.35	10.91	11.68	11.37	12.13	12.59
	6H	15.30	15.94	15.80	16.43	16.91	11.49	12.13	11.99	12.63	13.10
	8H	15.55	16.13	16.07	16.64	17.13	11.71	12.29	12.23	12.80	13.29
	12H	15.76	16.27	16.27	16.76	17.32	11.89	12.40	12.40	12.89	13.46
12H	4H	14.65	15.34	15.13	15.82	16.29	10.95	11.64	11.43	12.12	12.59
	6H	15.28	15.86	15.80	16.37	16.86	11.56	12.13	12.07	12.64	13.13
	8H	15.57	16.08	16.08	16.57	17.13	11.83	12.34	12.34	12.83	13.40