

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930179

Luminaire Tested: DFN2DS-HX3F0-050DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-050DS940-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4415.4 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930179

CATALOG NUMBER: DFN2DS-HX3F0-050DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930179

CATALOG NUMBER: DFN2DS-HX3F0-050DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2010	2010	2010
5°	2018	1989	2001
10°	2006	1969	1979
15°	1981	1943	1941
20°	1946	1905	1903
25°	1911	1858	1858
30°	1866	1815	1799
35°	1824	1763	1737
40°	1772	1711	1678
45°	1720	1659	1618
50°	1663	1606	1549
55°	1604	1544	1486
60°	1539	1469	1415
65°	1468	1395	1331
70°	1379	1305	1244
75°	1254	1202	1173
80°	1114	1079	1024
85°	908	865	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1720 cd/sqm

TEST NUMBER: P930179

CATALOG NUMBER: DFN2DS-HX3F0-050DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	3.7
10°-20°	459.6	10.4
20°-30°	675.4	15.3
30°-40°	784.4	17.8
40°-50°	783.4	17.7
50°-60°	683.1	15.5
60°-70°	505.0	11.4
70°-80°	285.7	6.5
80°-90°	75.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.3	29.4
0°-40°	2082.7	47.2
0°-60°	3549.3	80.4
0°-90°	4415.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4415.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1729	1710	1724	1721	165
15°	1652	1642	1620	1627	1619	465
25°	1495	1482	1454	1457	1454	688
35°	1290	1273	1247	1236	1228	806
45°	1050	1038	1013	995	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	486	530
75°	280	277	269	259	262	299
85°	68	67	65	60	58	80
90°	0	0	0	0	0	

TEST NUMBER: P930179

CATALOG NUMBER: DFN2DS-HX3F0-050DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1735.4	1735.4	1735.4	1735.4	1735.4
2.5°	1745.5	1737.2	1718.8	1735.4	1732.3
5°	1735.4	1728.9	1710.4	1723.7	1720.6
7.5°	1723.7	1713.8	1695.4	1708.9	1705.5
10°	1705.5	1693.8	1673.8	1687.0	1682.1
12.5°	1680.3	1670.4	1650.5	1658.8	1655.4
15°	1652.0	1642.1	1620.3	1627.1	1618.7
17.5°	1616.9	1607.0	1585.3	1593.6	1585.3
20°	1578.6	1568.7	1545.3	1550.2	1543.7
22.5°	1540.3	1525.2	1503.5	1503.5	1500.1
25°	1495.2	1481.9	1453.5	1456.7	1453.5
27.5°	1445.0	1433.4	1411.8	1406.8	1398.5
30°	1395.1	1381.7	1356.7	1351.7	1345.0
32.5°	1341.7	1331.8	1305.0	1294.9	1288.2
35°	1289.9	1273.3	1246.6	1236.5	1228.2
37.5°	1231.5	1216.5	1189.7	1178.1	1169.8
40°	1171.6	1158.1	1131.3	1116.4	1109.7
42.5°	1113.1	1099.7	1073.1	1056.2	1046.3
45°	1049.7	1038.0	1012.9	994.7	987.9
47.5°	987.9	976.2	949.5	931.1	921.2
50°	922.8	914.5	891.1	867.7	859.4
52.5°	859.4	847.7	826.1	807.7	796.0
55°	794.4	784.3	764.3	744.3	736.0
57.5°	729.2	720.9	699.1	679.2	672.4
60°	664.1	657.6	634.2	615.7	610.8
62.5°	600.8	589.1	572.4	555.7	549.0
65°	535.7	525.7	509.0	494.0	485.6
67.5°	469.0	460.5	445.6	434.0	427.2
70°	407.2	400.5	385.4	373.7	367.2
72.5°	343.9	337.1	328.8	317.1	312.1
75°	280.3	277.1	268.6	258.7	262.1
77.5°	223.6	216.8	213.5	208.5	203.6
80°	167.0	165.2	161.8	156.9	153.5
82.5°	113.5	113.5	111.9	105.2	105.2
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930179

CATALOG NUMBER: DFN2DS-HX3F0-050DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.71	15.32	14.07	15.63	15.95	13.26	14.88	13.63	15.19	15.50
	3H	15.46	16.91	15.84	17.24	17.60	14.97	16.42	15.34	16.75	17.11
	4H	16.10	17.47	16.50	17.82	18.20	15.61	16.98	16.01	17.33	17.70
	6H	16.57	17.84	16.99	18.21	18.60	16.07	17.34	16.48	17.71	18.10
	8H	16.72	17.93	17.14	18.32	18.72	16.21	17.43	16.64	17.81	18.21
	12H	16.81	17.97	17.24	18.35	18.78	16.30	17.46	16.72	17.84	18.27
4H	2H	14.27	15.64	14.67	15.99	16.36	13.92	15.29	14.31	15.63	16.01
	3H	16.24	17.39	16.65	17.79	18.19	15.84	16.98	16.25	17.38	17.78
	4H	17.02	18.06	17.45	18.47	18.91	16.60	17.63	17.03	18.05	18.48
	6H	17.62	18.52	18.07	18.96	19.42	17.18	18.09	17.64	18.53	18.99
	8H	17.81	18.65	18.27	19.10	19.56	17.37	18.22	17.83	18.66	19.12
	12H	17.94	18.70	18.42	19.17	19.64	17.49	18.25	17.97	18.72	19.19
8H	4H	17.29	18.14	17.75	18.58	19.05	16.92	17.77	17.38	18.21	18.67
	6H	18.01	18.71	18.50	19.20	19.67	17.63	18.33	18.12	18.82	19.29
	8H	18.27	18.90	18.78	19.40	19.89	17.88	18.51	18.39	19.01	19.50
	12H	18.47	19.02	18.97	19.52	20.08	18.05	18.61	18.56	19.10	19.66
12H	4H	17.32	18.08	17.80	18.56	19.03	16.96	17.72	17.44	18.19	18.66
	6H	18.05	18.69	18.56	19.19	19.68	17.68	18.32	18.19	18.82	19.31
	8H	18.37	18.93	18.87	19.42	19.98	17.99	18.55	18.50	19.04	19.60