

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930696

Luminaire Tested: DFN2DS-PN4F0-070DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-070DS927-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.4 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930696

CATALOG NUMBER: DFN2DS-PN4F0-070DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930696

CATALOG NUMBER: DFN2DS-PN4F0-070DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1673	1673	1673
5°	1679	1652	1661
10°	1666	1625	1611
15°	1647	1576	1531
20°	1620	1508	1432
25°	1593	1430	1336
30°	1556	1349	1213
35°	1519	1262	1105
40°	1482	1172	980
45°	1439	1070	867
50°	1394	968	756
55°	1348	858	649
60°	1296	742	539
65°	1236	623	491
70°	1164	513	451
75°	1076	468	421
80°	950	418	384
85°	746	330	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1439 cd/sqm

TEST NUMBER: P930696

CATALOG NUMBER: DFN2DS-PN4F0-070DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	4.6
10°-20°	589.5	12.5
20°-30°	827.7	17.6
30°-40°	902.2	19.1
40°-50°	829.2	17.6
50°-60°	651.2	13.8
60°-70°	423.9	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.9	34.6
0°-40°	2534.1	53.8
0°-60°	4014.6	85.2
0°-90°	4712.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4712.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2291	2291	2291	2291	2291	
5°	2291	2281	2254	2273	2266	217
15°	2179	2156	2086	2047	2026	614
25°	1978	1912	1775	1690	1659	910
35°	1704	1599	1416	1286	1240	1067
45°	1394	1254	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	715	547	361	290	284	709
75°	382	236	166	151	149	403
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P930696

CATALOG NUMBER: DFN2DS-PN4F0-070DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.3	2291.3	2291.3	2291.3	2291.3
2.5°	2301.6	2291.3	2268.4	2289.4	2285.2
5°	2291.3	2281.0	2254.0	2272.6	2266.5
7.5°	2272.6	2260.3	2231.3	2239.4	2229.1
10°	2247.8	2233.3	2191.9	2185.5	2173.2
12.5°	2216.7	2198.0	2142.0	2129.6	2106.7
15°	2179.3	2156.5	2086.0	2046.7	2026.0
17.5°	2135.8	2102.6	2015.5	1969.9	1936.7
20°	2086.0	2044.5	1940.9	1889.2	1843.4
22.5°	2032.2	1984.4	1864.1	1793.6	1762.7
25°	1978.3	1911.8	1775.0	1690.0	1658.8
27.5°	1914.0	1843.4	1692.0	1594.6	1546.9
30°	1845.6	1766.6	1600.7	1495.1	1439.1
32.5°	1779.1	1683.7	1513.8	1389.3	1337.4
35°	1704.5	1598.7	1416.4	1285.7	1240.0
37.5°	1632.0	1517.8	1325.1	1181.8	1130.2
40°	1555.2	1430.9	1229.6	1082.4	1028.5
42.5°	1476.4	1343.8	1134.3	980.7	929.1
45°	1393.5	1254.4	1036.9	889.5	839.8
47.5°	1314.7	1167.6	943.6	796.2	750.7
50°	1227.6	1080.4	852.3	709.1	665.8
52.5°	1142.5	986.9	765.2	628.3	588.9
55°	1059.5	897.8	673.8	549.6	510.2
57.5°	974.6	808.7	593.1	476.9	443.8
60°	887.5	721.6	508.0	402.4	369.2
62.5°	802.5	636.7	435.4	336.0	319.4
65°	715.4	547.4	360.8	290.4	284.0
67.5°	632.5	464.4	290.4	254.9	248.8
70°	545.4	383.6	240.5	219.8	211.4
72.5°	462.4	308.9	201.1	184.6	180.4
75°	381.5	236.3	165.8	151.4	149.4
77.5°	300.7	167.8	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.5	80.9	68.4	64.2	64.2
85°	89.1	45.5	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930696

CATALOG NUMBER: DFN2DS-PN4F0-070DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.02	14.54	13.39	14.86	15.17	8.98	10.50	9.35	10.82	11.13
	3H	14.79	16.15	15.16	16.48	16.84	10.25	11.61	10.62	11.94	12.30
	4H	15.45	16.73	15.85	17.08	17.46	10.75	12.03	11.15	12.38	12.76
	6H	15.94	17.13	16.35	17.49	17.88	11.13	12.31	11.54	12.68	13.07
	8H	16.11	17.23	16.53	17.62	18.02	11.25	12.38	11.68	12.77	13.17
	12H	16.21	17.29	16.64	17.67	18.10	11.34	12.41	11.77	12.80	13.23
4H	2H	13.13	14.41	13.53	14.75	15.13	9.68	10.96	10.08	11.31	11.69
	3H	15.06	16.12	15.47	16.52	16.92	11.12	12.18	11.53	12.58	12.98
	4H	15.81	16.76	16.24	17.18	17.62	11.72	12.68	12.15	13.09	13.53
	6H	16.40	17.23	16.86	17.67	18.13	12.21	13.04	12.67	13.48	13.94
	8H	16.61	17.39	17.08	17.84	18.30	12.37	13.15	12.83	13.59	14.06
	12H	16.77	17.46	17.25	17.94	18.41	12.49	13.18	12.97	13.66	14.13
8H	4H	15.83	16.61	16.30	17.05	17.52	12.07	12.85	12.54	13.30	13.76
	6H	16.47	17.11	16.97	17.60	18.08	12.66	13.30	13.16	13.79	14.27
	8H	16.72	17.30	17.23	17.81	18.29	12.88	13.46	13.40	13.97	14.46
	12H	16.92	17.43	17.43	17.93	18.49	13.06	13.57	13.57	14.06	14.63
12H	4H	15.82	16.51	16.30	16.99	17.46	12.12	12.81	12.60	13.29	13.76
	6H	16.45	17.03	16.96	17.54	18.03	12.72	13.30	13.24	13.81	14.30
	8H	16.74	17.24	17.24	17.74	18.30	13.00	13.51	13.51	14.00	14.56

END OF REPORT