

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930234

Luminaire Tested: DFN2DS-HX3F0-080DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-080DS940-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6065.6 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 84.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930234

CATALOG NUMBER: DFN2DS-HX3F0-080DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930234

CATALOG NUMBER: DFN2DS-HX3F0-080DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3416	3416	3416
5°	3429	3373	3392
10°	3403	3318	3290
15°	3364	3220	3127
20°	3310	3080	2925
25°	3254	2920	2729
30°	3177	2756	2477
35°	3103	2578	2257
40°	3027	2393	2002
45°	2938	2186	1771
50°	2847	1977	1544
55°	2754	1752	1326
60°	2646	1515	1101
65°	2524	1273	1002
70°	2378	1048	922
75°	2197	956	861
80°	1940	854	784
85°	1524	674	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2938 cd/sqm

TEST NUMBER: P930234

CATALOG NUMBER: DFN2DS-HX3F0-080DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.4	4.6
10°-20°	758.8	12.5
20°-30°	1065.3	17.6
30°-40°	1161.3	19.1
40°-50°	1067.3	17.6
50°-60°	838.3	13.8
60°-70°	545.6	9.0
70°-80°	280.9	4.6
80°-90°	71.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2100.6	34.6
0°-40°	3261.8	53.8
0°-60°	5167.4	85.2
0°-90°	6065.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6065.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2949	2949	2949	2949	2949	
5°	2949	2936	2901	2925	2917	280
15°	2805	2776	2685	2634	2608	790
25°	2546	2461	2285	2175	2135	1171
35°	2194	2058	1823	1655	1596	1373
45°	1794	1615	1335	1145	1081	1385
55°	1364	1156	867	707	657	1219
65°	921	704	464	374	366	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	138
90°	0	0	0	0	0	

TEST NUMBER: P930234

CATALOG NUMBER: DFN2DS-HX3F0-080DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2949.3	2949.3	2949.3	2949.3	2949.3
2.5°	2962.6	2949.3	2919.9	2946.7	2941.4
5°	2949.3	2936.0	2901.1	2925.2	2917.3
7.5°	2925.2	2909.3	2872.0	2882.5	2869.1
10°	2893.2	2874.6	2821.3	2813.1	2797.2
12.5°	2853.3	2829.2	2757.0	2741.1	2711.7
15°	2805.2	2775.7	2685.1	2634.4	2607.8
17.5°	2749.1	2706.3	2594.2	2535.6	2492.8
20°	2685.1	2631.6	2498.2	2431.7	2372.7
22.5°	2615.7	2554.2	2399.4	2308.8	2268.8
25°	2546.3	2460.8	2284.7	2175.4	2135.2
27.5°	2463.6	2372.7	2177.9	2052.5	1991.0
30°	2375.6	2273.9	2060.4	1924.5	1852.2
32.5°	2290.0	2167.2	1948.6	1788.3	1721.5
35°	2194.1	2057.8	1823.1	1654.9	1596.0
37.5°	2100.6	1953.7	1705.6	1521.2	1454.7
40°	2001.8	1841.8	1582.7	1393.2	1323.8
42.5°	1900.4	1729.7	1460.0	1262.4	1195.8
45°	1793.6	1614.7	1334.6	1144.9	1080.9
47.5°	1692.3	1502.8	1214.5	1024.8	966.2
50°	1580.1	1390.7	1097.1	912.7	856.9
52.5°	1470.6	1270.3	984.9	808.8	758.1
55°	1363.8	1155.7	867.4	707.4	656.7
57.5°	1254.5	1041.0	763.5	614.0	571.1
60°	1142.3	928.8	653.8	517.9	475.2
62.5°	1033.0	819.5	560.4	432.4	411.2
65°	920.9	704.5	464.4	373.8	365.5
67.5°	814.1	597.8	373.8	328.2	320.3
70°	702.0	493.9	309.5	282.9	272.1
72.5°	595.2	397.6	258.9	237.6	232.2
75°	491.0	304.2	213.5	194.8	192.3
77.5°	387.1	216.0	168.2	157.4	152.1
80°	290.8	154.9	128.0	117.5	117.5
82.5°	202.8	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.7	50.7	50.7
87.5°	42.7	21.2	21.2	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930234

CATALOG NUMBER: DFN2DS-HX3F0-080DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.50	17.03	15.87	17.34	17.65	11.46	12.99	11.83	13.30	13.61
	3H	17.27	18.63	17.65	18.96	19.32	12.73	14.09	13.11	14.42	14.78
	4H	17.93	19.22	18.33	19.56	19.94	13.23	14.51	13.63	14.86	15.24
	6H	18.42	19.61	18.84	19.97	20.37	13.61	14.79	14.02	15.16	15.55
	8H	18.59	19.72	19.02	20.11	20.51	13.74	14.86	14.16	15.25	15.65
	12H	18.69	19.77	19.12	20.15	20.58	13.82	14.90	14.25	15.28	15.71
4H	2H	15.61	16.89	16.01	17.24	17.62	12.16	13.44	12.56	13.79	14.17
	3H	17.54	18.60	17.95	19.00	19.40	13.60	14.67	14.01	15.07	15.47
	4H	18.29	19.25	18.72	19.66	20.10	14.20	15.16	14.63	15.57	16.01
	6H	18.88	19.71	19.34	20.16	20.62	14.69	15.52	15.15	15.96	16.42
	8H	19.10	19.87	19.56	20.32	20.78	14.85	15.63	15.32	16.07	16.54
	12H	19.25	19.94	19.73	20.42	20.89	14.97	15.66	15.45	16.14	16.61
8H	4H	18.31	19.09	18.78	19.54	20.00	14.56	15.33	15.02	15.78	16.24
	6H	18.95	19.59	19.45	20.09	20.56	15.14	15.78	15.64	16.28	16.75
	8H	19.20	19.78	19.72	20.29	20.78	15.36	15.94	15.88	16.45	16.94
	12H	19.41	19.92	19.92	20.41	20.97	15.54	16.05	16.05	16.54	17.11
12H	4H	18.30	18.99	18.78	19.47	19.94	14.60	15.29	15.08	15.77	16.24
	6H	18.93	19.51	19.45	20.02	20.51	15.21	15.78	15.72	16.29	16.78
	8H	19.22	19.73	19.73	20.22	20.78	15.48	15.99	15.99	16.48	17.05