

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930251

Luminaire Tested: DFN2DS-HX3F0-090DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-090DS940-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7947.7 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930251

CATALOG NUMBER: DFN2DS-HX3F0-090DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930251

CATALOG NUMBER: DFN2DS-HX3F0-090DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3618	3618	3618
5°	3632	3580	3601
10°	3611	3544	3561
15°	3566	3498	3494
20°	3503	3429	3425
25°	3440	3344	3344
30°	3359	3266	3238
35°	3284	3173	3126
40°	3189	3079	3020
45°	3095	2987	2913
50°	2993	2890	2788
55°	2888	2778	2675
60°	2769	2645	2547
65°	2643	2511	2396
70°	2483	2350	2239
75°	2258	2164	2111
80°	2005	1943	1843
85°	1635	1559	1398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3095 cd/sqm

TEST NUMBER: P930251

CATALOG NUMBER: DFN2DS-HX3F0-090DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.0	3.7
10°-20°	827.2	10.4
20°-30°	1215.7	15.3
30°-40°	1412.0	17.8
40°-50°	1410.2	17.7
50°-60°	1229.7	15.5
60°-70°	909.0	11.4
70°-80°	514.3	6.5
80°-90°	135.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2336.9	29.4
0°-40°	3748.9	47.2
0°-60°	6388.7	80.4
0°-90°	7947.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7947.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3124	3124	3124	3124	3124	
5°	3124	3112	3079	3103	3097	297
15°	2974	2956	2917	2929	2914	837
25°	2691	2667	2616	2622	2616	1238
35°	2322	2292	2244	2226	2211	1450
45°	1889	1868	1823	1790	1778	1458
55°	1430	1412	1376	1340	1325	1278
65°	964	946	916	889	874	953
75°	504	499	484	466	472	539
85°	123	120	117	108	105	145
90°	0	0	0	0	0	

TEST NUMBER: P930251

CATALOG NUMBER: DFN2DS-HX3F0-090DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3123.7	3123.7	3123.7	3123.7	3123.7
2.5°	3141.9	3126.9	3093.8	3123.7	3118.0
5°	3123.7	3111.9	3078.8	3102.7	3096.9
7.5°	3102.7	3084.9	3051.7	3076.0	3069.9
10°	3069.9	3048.9	3012.8	3036.7	3027.8
12.5°	3024.6	3006.8	2970.8	2985.7	2979.7
15°	2973.7	2955.8	2916.6	2928.7	2913.7
17.5°	2910.5	2892.7	2853.5	2868.5	2853.5
20°	2841.4	2823.5	2781.4	2790.4	2778.6
22.5°	2772.5	2745.5	2706.2	2706.2	2700.2
25°	2691.3	2667.3	2616.4	2622.1	2616.4
27.5°	2601.1	2580.0	2541.2	2532.3	2517.3
30°	2511.2	2487.0	2442.0	2433.1	2421.1
32.5°	2415.0	2397.2	2349.0	2330.9	2318.8
35°	2322.0	2292.0	2243.8	2225.7	2210.7
37.5°	2216.8	2189.7	2141.5	2120.6	2105.6
40°	2108.7	2084.5	2036.3	2009.6	1997.5
42.5°	2003.5	1979.3	1931.5	1901.3	1883.5
45°	1889.4	1868.5	1823.2	1790.3	1778.3
47.5°	1778.3	1757.2	1709.1	1676.0	1658.1
50°	1661.0	1646.0	1603.9	1561.9	1546.9
52.5°	1546.9	1525.9	1487.0	1453.9	1432.8
55°	1430.0	1411.8	1375.7	1339.8	1324.8
57.5°	1312.7	1297.7	1258.5	1222.5	1210.4
60°	1195.4	1183.6	1141.5	1108.4	1099.5
62.5°	1081.3	1060.2	1030.3	1000.4	988.2
65°	964.3	946.1	916.2	889.1	874.2
67.5°	844.2	828.9	802.1	781.1	769.0
70°	733.0	720.8	693.8	672.7	661.0
72.5°	618.9	606.7	591.8	570.8	561.9
75°	504.5	498.7	483.5	465.6	471.7
77.5°	402.5	390.4	384.4	375.4	366.5
80°	300.5	297.3	291.2	282.3	276.3
82.5°	204.3	204.3	201.4	189.3	189.3
85°	123.0	120.2	117.3	108.0	105.2
87.5°	54.1	48.1	42.1	33.2	30.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930251

CATALOG NUMBER: DFN2DS-HX3F0-090DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.75	17.36	16.12	17.68	17.99	15.31	16.92	15.67	17.23	17.55
	3H	17.50	18.96	17.88	19.28	19.64	17.01	18.46	17.39	18.79	19.15
	4H	18.15	19.52	18.55	19.86	20.24	17.65	19.02	18.05	19.37	19.75
	6H	18.62	19.88	19.03	20.25	20.64	18.12	19.38	18.53	19.75	20.14
	8H	18.76	19.97	19.18	20.36	20.76	18.26	19.47	18.68	19.86	20.26
	12H	18.85	20.01	19.28	20.39	20.82	18.34	19.50	18.77	19.88	20.31
4H	2H	16.31	17.68	16.71	18.03	18.40	15.96	17.33	16.36	17.68	18.05
	3H	18.29	19.43	18.70	19.83	20.23	17.88	19.03	18.29	19.42	19.82
	4H	19.06	20.10	19.49	20.51	20.95	18.64	19.67	19.07	20.09	20.52
	6H	19.66	20.56	20.11	21.00	21.46	19.23	20.13	19.68	20.57	21.03
	8H	19.85	20.70	20.31	21.14	21.60	19.41	20.26	19.87	20.70	21.17
	12H	19.98	20.74	20.46	21.22	21.69	19.53	20.29	20.01	20.76	21.23
8H	4H	19.34	20.18	19.80	20.63	21.09	18.96	19.81	19.42	20.25	20.72
	6H	20.05	20.75	20.54	21.24	21.72	19.67	20.37	20.16	20.86	21.34
	8H	20.31	20.94	20.82	21.45	21.93	19.92	20.55	20.43	21.06	21.54
	12H	20.51	21.07	21.02	21.56	22.12	20.10	20.65	20.60	21.14	21.71
12H	4H	19.36	20.12	19.84	20.60	21.07	19.00	19.76	19.48	20.23	20.70
	6H	20.10	20.73	20.61	21.23	21.72	19.73	20.36	20.24	20.87	21.35
	8H	20.41	20.97	20.92	21.46	22.02	20.03	20.59	20.54	21.08	21.64