

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930734

Luminaire Tested: DFN2DS-PN4F0-090DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-090DS930-RLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6234.7 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 93.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930734

CATALOG NUMBER: DFN2DS-PN4F0-090DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930734

CATALOG NUMBER: DFN2DS-PN4F0-090DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2213	2213	2213
5°	2221	2185	2197
10°	2204	2150	2131
15°	2179	2086	2026
20°	2144	1995	1895
25°	2108	1891	1768
30°	2058	1785	1605
35°	2010	1670	1462
40°	1961	1550	1297
45°	1903	1416	1147
50°	1844	1281	1000
55°	1784	1135	859
60°	1714	981	713
65°	1635	824	649
70°	1540	679	597
75°	1423	619	557
80°	1256	553	508
85°	987	436	436

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1903 cd/sqm

TEST NUMBER: P930734

CATALOG NUMBER: DFN2DS-PN4F0-090DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.1	4.6
10°-20°	780.0	12.5
20°-30°	1095.0	17.6
30°-40°	1193.7	19.1
40°-50°	1097.1	17.6
50°-60°	861.6	13.8
60°-70°	560.8	9.0
70°-80°	288.7	4.6
80°-90°	73.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2159.1	34.6
0°-40°	3352.8	53.8
0°-60°	5311.5	85.2
0°-90°	6234.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6234.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3032	3032	3032	3032	3032	
5°	3032	3018	2982	3007	2999	287
15°	2883	2853	2760	2708	2680	813
25°	2617	2529	2348	2236	2195	1204
35°	2255	2115	1874	1701	1640	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	946	724	477	384	376	938
75°	505	313	220	200	198	534
85°	118	60	52	52	52	141
90°	0	0	0	0	0	

TEST NUMBER: P930734

CATALOG NUMBER: DFN2DS-PN4F0-090DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3031.6	3031.6	3031.6	3031.6	3031.6
2.5°	3045.2	3031.6	3001.2	3028.9	3023.4
5°	3031.6	3017.9	2982.1	3006.8	2998.6
7.5°	3006.8	2990.5	2952.1	2962.9	2949.2
10°	2973.9	2954.7	2900.0	2891.5	2875.2
12.5°	2932.9	2908.2	2833.9	2817.6	2787.3
15°	2883.4	2853.2	2760.0	2707.8	2680.5
17.5°	2825.8	2781.8	2666.5	2606.3	2562.4
20°	2760.0	2705.0	2567.8	2499.4	2438.9
22.5°	2688.7	2625.5	2466.3	2373.1	2332.1
25°	2617.4	2529.4	2348.4	2236.0	2194.7
27.5°	2532.4	2438.9	2238.6	2109.7	2046.5
30°	2441.8	2337.3	2117.9	1978.2	1903.9
32.5°	2353.9	2227.6	2002.9	1838.2	1769.4
35°	2255.3	2115.3	1873.9	1701.1	1640.5
37.5°	2159.2	2008.2	1753.1	1563.7	1495.3
40°	2057.6	1893.2	1626.8	1432.1	1360.8
42.5°	1953.4	1777.9	1500.7	1297.6	1229.2
45°	1843.7	1659.7	1371.8	1176.8	1111.0
47.5°	1739.5	1544.8	1248.4	1053.4	993.2
50°	1624.2	1429.4	1127.6	938.1	880.8
52.5°	1511.6	1305.8	1012.4	831.3	779.2
55°	1401.8	1187.9	891.5	727.1	675.0
57.5°	1289.5	1070.0	784.8	631.1	587.1
60°	1174.2	954.7	672.1	532.4	488.4
62.5°	1061.9	842.4	576.0	444.5	422.7
65°	946.5	724.2	477.3	384.2	375.8
67.5°	836.8	614.4	384.2	337.3	329.2
70°	721.6	507.7	318.2	290.8	279.7
72.5°	611.8	408.6	266.0	244.2	238.7
75°	504.7	312.6	219.5	200.2	197.6
77.5°	397.9	222.1	172.9	161.9	156.3
80°	298.9	159.3	131.5	120.8	120.8
82.5°	208.4	107.1	90.5	85.0	85.0
85°	117.8	60.2	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930734

CATALOG NUMBER: DFN2DS-PN4F0-090DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.99	15.52	14.36	15.83	16.14	9.96	11.48	10.32	11.79	12.11
	3H	15.76	17.12	16.14	17.45	17.81	11.22	12.59	11.60	12.91	13.28
	4H	16.43	17.71	16.83	18.06	18.43	11.72	13.00	12.12	13.35	13.73
	6H	16.91	18.10	17.33	18.46	18.86	12.10	13.29	12.51	13.65	14.04
	8H	17.08	18.21	17.51	18.60	19.00	12.23	13.35	12.65	13.74	14.14
	12H	17.18	18.26	17.61	18.64	19.07	12.31	13.39	12.74	13.77	14.20
4H	2H	14.10	15.38	14.50	15.73	16.11	10.65	11.93	11.05	12.28	12.66
	3H	16.03	17.09	16.44	17.49	17.90	12.09	13.16	12.50	13.56	13.96
	4H	16.78	17.74	17.21	18.15	18.59	12.69	13.65	13.13	14.06	14.50
	6H	17.37	18.20	17.83	18.65	19.11	13.18	14.01	13.64	14.46	14.92
	8H	17.59	18.36	18.05	18.81	19.28	13.34	14.12	13.81	14.56	15.03
	12H	17.74	18.44	18.22	18.91	19.38	13.46	14.15	13.94	14.63	15.10
8H	4H	16.81	17.58	17.27	18.03	18.49	13.05	13.82	13.51	14.27	14.74
	6H	17.44	18.09	17.94	18.58	19.05	13.63	14.28	14.13	14.77	15.24
	8H	17.69	18.27	18.21	18.78	19.27	13.85	14.43	14.37	14.94	15.43
	12H	17.90	18.41	18.41	18.90	19.46	14.03	14.54	14.54	15.04	15.60
12H	4H	16.79	17.48	17.27	17.96	18.43	13.09	13.78	13.57	14.26	14.73
	6H	17.42	18.00	17.94	18.51	19.00	13.70	14.27	14.21	14.78	15.27
	8H	17.71	18.22	18.22	18.71	19.27	13.97	14.48	14.48	14.97	15.54