

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930145

Luminaire Tested: DFN2DS-HX3F0-030DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-030DS950-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2806.7 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 28.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930145

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930145

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1278	1278	1278
5°	1283	1264	1272
10°	1275	1251	1258
15°	1259	1235	1234
20°	1237	1211	1210
25°	1215	1181	1181
30°	1186	1154	1143
35°	1160	1121	1104
40°	1126	1087	1067
45°	1093	1055	1029
50°	1057	1021	984
55°	1020	981	945
60°	978	934	900
65°	934	887	846
70°	877	830	790
75°	797	764	746
80°	708	686	651
85°	578	550	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1093 cd/sqm

TEST NUMBER: P930145

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.8	3.7
10°-20°	292.1	10.4
20°-30°	429.3	15.3
30°-40°	498.6	17.8
40°-50°	498.0	17.7
50°-60°	434.2	15.5
60°-70°	321.0	11.4
70°-80°	181.6	6.5
80°-90°	47.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.3	29.4
0°-40°	1323.9	47.2
0°-60°	2256.1	80.4
0°-90°	2806.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2806.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1103	1103	1103	1103	1103	
5°	1103	1099	1087	1096	1094	105
15°	1050	1044	1030	1034	1029	296
25°	950	942	924	926	924	437
35°	820	809	792	786	781	512
45°	667	660	644	632	628	515
55°	505	499	486	473	468	451
65°	341	334	324	314	309	337
75°	178	176	171	164	167	190
85°	44	42	41	38	37	51
90°	0	0	0	0	0	

TEST NUMBER: P930145

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1103.1	1103.1	1103.1	1103.1	1103.1
2.5°	1109.5	1104.2	1092.5	1103.1	1101.1
5°	1103.1	1098.9	1087.2	1095.7	1093.6
7.5°	1095.7	1089.4	1077.7	1086.3	1084.1
10°	1084.1	1076.6	1064.0	1072.4	1069.3
12.5°	1068.1	1061.8	1049.1	1054.3	1052.3
15°	1050.1	1043.8	1030.0	1034.2	1028.9
17.5°	1027.8	1021.5	1007.7	1012.9	1007.7
20°	1003.4	997.1	982.2	985.4	981.2
22.5°	979.1	969.6	955.7	955.7	953.5
25°	950.4	942.0	923.9	926.0	923.9
27.5°	918.5	911.1	897.4	894.3	889.0
30°	886.8	878.3	862.4	859.2	854.9
32.5°	852.9	846.5	829.5	823.1	818.8
35°	820.0	809.4	792.4	786.0	780.7
37.5°	782.8	773.3	756.3	748.8	743.5
40°	744.7	736.2	719.1	709.7	705.4
42.5°	707.5	699.0	682.1	671.4	665.1
45°	667.3	659.8	643.8	632.2	628.0
47.5°	628.0	620.6	603.6	591.9	585.5
50°	586.6	581.3	566.4	551.6	546.3
52.5°	546.3	538.8	525.1	513.4	506.0
55°	505.0	498.6	485.8	473.2	467.9
57.5°	463.5	458.2	444.4	431.7	427.4
60°	422.1	418.0	403.1	391.4	388.3
62.5°	381.9	374.4	363.8	353.2	349.0
65°	340.6	334.2	323.6	314.0	308.7
67.5°	298.1	292.8	283.2	275.8	271.6
70°	258.8	254.6	245.0	237.6	233.4
72.5°	218.6	214.2	208.9	201.6	198.4
75°	178.1	176.1	170.8	164.4	166.6
77.5°	142.1	137.9	135.7	132.6	129.5
80°	106.1	105.0	102.8	99.7	97.6
82.5°	72.1	72.1	71.2	66.8	66.8
85°	43.5	42.4	41.4	38.2	37.1
87.5°	19.1	17.0	14.8	11.7	10.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930145

CATALOG NUMBER: DFN2DS-HX3F0-030DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.13	13.74	12.50	14.06	14.37	11.69	13.30	12.05	13.61	13.93
	3H	13.88	15.34	14.26	15.67	16.03	13.39	14.85	13.77	15.17	15.53
	4H	14.53	15.90	14.93	16.25	16.62	14.04	15.40	14.43	15.75	16.13
	6H	15.00	16.27	15.41	16.63	17.02	14.50	15.77	14.91	16.13	16.52
	8H	15.14	16.35	15.57	16.74	17.14	14.64	15.85	15.06	16.24	16.64
	12H	15.23	16.39	15.66	16.77	17.20	14.72	15.88	15.15	16.26	16.69
4H	2H	12.69	14.06	13.09	14.41	14.79	12.34	13.71	12.74	14.06	14.43
	3H	14.67	15.82	15.08	16.21	16.61	14.26	15.41	14.67	15.81	16.21
	4H	15.45	16.48	15.88	16.90	17.33	15.02	16.06	15.45	16.47	16.91
	6H	16.04	16.95	16.50	17.39	17.84	15.61	16.52	16.07	16.96	17.41
	8H	16.23	17.08	16.69	17.52	17.99	15.79	16.64	16.26	17.08	17.55
	12H	16.36	17.12	16.84	17.60	18.07	15.91	16.67	16.39	17.15	17.62
8H	4H	15.72	16.57	16.18	17.01	17.47	15.35	16.19	15.81	16.63	17.10
	6H	16.43	17.14	16.93	17.62	18.10	16.05	16.76	16.55	17.24	17.72
	8H	16.69	17.32	17.20	17.83	18.32	16.30	16.93	16.81	17.44	17.93
	12H	16.89	17.45	17.40	17.94	18.50	16.48	17.04	16.99	17.53	18.09
12H	4H	15.75	16.51	16.23	16.98	17.45	15.38	16.14	15.86	16.62	17.09
	6H	16.48	17.11	16.99	17.62	18.10	16.11	16.74	16.62	17.25	17.74
	8H	16.79	17.35	17.30	17.84	18.40	16.42	16.97	16.92	17.46	18.02