

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930163

Luminaire Tested: DFN2DS-HX3F0-040DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930163
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-040DS950-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3742.2 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 38.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930163

CATALOG NUMBER: DFN2DS-HX3F0-040DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930163

CATALOG NUMBER: DFN2DS-HX3F0-040DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1704	1704	1704
5°	1710	1686	1696
10°	1700	1669	1677
15°	1679	1647	1645
20°	1649	1614	1613
25°	1620	1574	1574
30°	1582	1538	1525
35°	1546	1494	1472
40°	1501	1450	1422
45°	1457	1406	1372
50°	1409	1361	1312
55°	1360	1308	1260
60°	1304	1245	1199
65°	1245	1182	1128
70°	1169	1106	1054
75°	1063	1019	994
80°	944	915	868
85°	770	734	658

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1457 cd/sqm

TEST NUMBER: P930163

CATALOG NUMBER: DFN2DS-HX3F0-040DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	3.7
10°-20°	389.5	10.4
20°-30°	572.4	15.3
30°-40°	664.8	17.8
40°-50°	664.0	17.7
50°-60°	579.0	15.5
60°-70°	428.0	11.4
70°-80°	242.2	6.5
80°-90°	63.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.3	29.4
0°-40°	1765.2	47.2
0°-60°	3008.1	80.4
0°-90°	3742.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3742.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1471	1471	1471	1471	1471	
5°	1471	1465	1450	1461	1458	140
15°	1400	1392	1373	1379	1372	394
25°	1267	1256	1232	1235	1232	583
35°	1093	1079	1056	1048	1041	683
45°	890	880	858	843	837	687
55°	673	665	648	631	624	602
65°	454	446	431	419	412	449
75°	238	235	228	219	222	254
85°	58	57	55	51	50	68
90°	0	0	0	0	0	

TEST NUMBER: P930163

CATALOG NUMBER: DFN2DS-HX3F0-040DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1470.8	1470.8	1470.8	1470.8	1470.8
2.5°	1479.4	1472.3	1456.7	1470.8	1468.2
5°	1470.8	1465.2	1449.6	1460.9	1458.2
7.5°	1460.9	1452.5	1436.9	1448.3	1445.5
10°	1445.5	1435.5	1418.6	1429.9	1425.6
12.5°	1424.1	1415.7	1398.8	1405.9	1402.9
15°	1400.1	1391.7	1373.3	1378.9	1372.0
17.5°	1370.4	1362.0	1343.6	1350.6	1343.6
20°	1337.8	1329.4	1309.7	1313.8	1308.4
22.5°	1305.4	1292.7	1274.2	1274.2	1271.4
25°	1267.2	1255.9	1231.9	1234.6	1231.9
27.5°	1224.7	1214.8	1196.6	1192.3	1185.3
30°	1182.4	1171.0	1149.9	1145.6	1140.0
32.5°	1137.1	1128.7	1106.0	1097.5	1091.8
35°	1093.3	1079.2	1056.5	1048.0	1040.9
37.5°	1043.8	1031.0	1008.3	998.5	991.4
40°	992.9	981.5	958.8	946.2	940.6
42.5°	943.4	932.0	909.5	895.2	886.8
45°	889.6	879.8	858.4	843.0	837.3
47.5°	837.3	827.3	804.8	789.2	780.8
50°	782.1	775.0	755.2	735.4	728.3
52.5°	728.3	718.5	700.2	684.6	674.6
55°	673.3	664.7	647.8	630.8	623.8
57.5°	618.0	611.0	592.5	575.6	569.9
60°	562.8	557.3	537.5	521.9	517.7
62.5°	509.2	499.2	485.2	471.0	465.3
65°	454.1	445.5	431.4	418.6	411.6
67.5°	397.5	390.3	377.7	367.8	362.1
70°	345.1	339.4	326.7	316.8	311.2
72.5°	291.4	285.7	278.7	268.8	264.5
75°	237.6	234.8	227.7	219.2	222.1
77.5°	189.5	183.8	181.0	176.7	172.6
80°	141.5	140.0	137.1	133.0	130.1
82.5°	96.2	96.2	94.9	89.1	89.1
85°	57.9	56.6	55.2	50.8	49.5
87.5°	25.5	22.7	19.8	15.6	14.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930163

CATALOG NUMBER: DFN2DS-HX3F0-040DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.13	14.74	13.50	15.06	15.37	12.69	14.30	13.05	14.61	14.93
	3H	14.88	16.34	15.26	16.66	17.03	14.39	15.85	14.77	16.17	16.53
	4H	15.53	16.90	15.93	17.25	17.62	15.04	16.40	15.43	16.75	17.13
	6H	16.00	17.27	16.41	17.63	18.02	15.50	16.77	15.91	17.13	17.52
	8H	16.14	17.35	16.57	17.74	18.14	15.64	16.85	16.06	17.24	17.64
	12H	16.23	17.39	16.66	17.77	18.20	15.72	16.88	16.15	17.26	17.69
4H	2H	13.69	15.06	14.09	15.41	15.79	13.34	14.71	13.74	15.06	15.43
	3H	15.67	16.82	16.08	17.21	17.61	15.26	16.41	15.67	16.81	17.21
	4H	16.45	17.48	16.88	17.90	18.33	16.02	17.06	16.45	17.47	17.91
	6H	17.04	17.95	17.50	18.39	18.84	16.61	17.51	17.06	17.96	18.41
	8H	17.23	18.08	17.69	18.52	18.99	16.79	17.64	17.25	18.08	18.55
	12H	17.36	18.12	17.84	18.60	19.07	16.91	17.67	17.39	18.15	18.62
8H	4H	16.72	17.57	17.18	18.01	18.47	16.35	17.19	16.81	17.63	18.10
	6H	17.43	18.14	17.93	18.62	19.10	17.05	17.76	17.55	18.24	18.72
	8H	17.69	18.32	18.20	18.83	19.32	17.30	17.93	17.81	18.44	18.92
	12H	17.89	18.45	18.40	18.94	19.50	17.48	18.04	17.99	18.53	19.09
12H	4H	16.75	17.51	17.23	17.98	18.45	16.38	17.14	16.86	17.62	18.09
	6H	17.48	18.11	17.99	18.62	19.10	17.11	17.74	17.62	18.25	18.74
	8H	17.79	18.35	18.30	18.84	19.40	17.41	17.97	17.92	18.46	19.02