

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930681

Luminaire Tested: DFN2DS-PN4F0-060DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-060DS935-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5108.4 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 59.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930681

CATALOG NUMBER: DFN2DS-PN4F0-060DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930681

CATALOG NUMBER: DFN2DS-PN4F0-060DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1466	1466	1466
5°	1471	1450	1459
10°	1463	1435	1442
15°	1444	1417	1415
20°	1419	1389	1387
25°	1393	1354	1354
30°	1360	1323	1312
35°	1330	1285	1266
40°	1292	1247	1223
45°	1254	1210	1180
50°	1212	1171	1129
55°	1170	1125	1084
60°	1122	1071	1032
65°	1071	1017	970
70°	1005	952	907
75°	914	876	855
80°	812	787	747
85°	662	631	566

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1254 cd/sqm

TEST NUMBER: P930681

CATALOG NUMBER: DFN2DS-PN4F0-060DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.7
10°-20°	531.7	10.4
20°-30°	781.4	15.3
30°-40°	907.5	17.8
40°-50°	906.4	17.7
50°-60°	790.4	15.5
60°-70°	584.3	11.4
70°-80°	330.6	6.5
80°-90°	87.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.1	29.4
0°-40°	2409.6	47.2
0°-60°	4106.3	80.4
0°-90°	5108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5108.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2008	2008	2008	2008	2008	
5°	2008	2000	1979	1994	1991	191
15°	1911	1900	1875	1882	1873	538
25°	1730	1714	1682	1685	1682	796
35°	1492	1473	1442	1430	1421	932
45°	1214	1201	1172	1151	1143	937
55°	919	907	884	861	852	822
65°	620	608	589	572	562	613
75°	324	321	311	299	303	346
85°	79	77	75	69	68	93
90°	0	0	0	0	0	

TEST NUMBER: P930681

CATALOG NUMBER: DFN2DS-PN4F0-060DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.8	2007.8	2007.8	2007.8	2007.8
2.5°	2019.5	2009.8	1988.5	2007.8	2004.1
5°	2007.8	2000.2	1978.9	1994.3	1990.6
7.5°	1994.3	1982.8	1961.5	1977.1	1973.2
10°	1973.2	1959.7	1936.5	1951.9	1946.1
12.5°	1944.1	1932.6	1909.5	1919.1	1915.2
15°	1911.3	1899.8	1874.6	1882.5	1872.8
17.5°	1870.8	1859.3	1834.1	1843.7	1834.1
20°	1826.3	1814.9	1787.8	1793.5	1786.0
22.5°	1782.1	1764.6	1739.4	1739.4	1735.6
25°	1729.8	1714.5	1681.6	1685.3	1681.6
27.5°	1671.8	1658.3	1633.3	1627.6	1618.0
30°	1614.1	1598.5	1569.7	1563.9	1556.1
32.5°	1552.2	1540.8	1509.8	1498.1	1490.4
35°	1492.4	1473.2	1442.2	1430.5	1420.9
37.5°	1424.8	1407.4	1376.5	1362.9	1353.3
40°	1355.4	1339.8	1308.9	1291.7	1283.9
42.5°	1287.8	1272.2	1241.5	1222.1	1210.5
45°	1214.5	1200.9	1171.8	1150.8	1142.9
47.5°	1142.9	1129.4	1098.6	1077.2	1065.7
50°	1067.6	1058.0	1031.0	1003.9	994.2
52.5°	994.2	980.7	955.7	934.5	921.0
55°	919.1	907.4	884.3	861.1	851.5
57.5°	843.7	834.1	808.9	785.8	778.0
60°	768.3	760.8	733.8	712.4	706.7
62.5°	695.0	681.5	662.2	642.9	635.2
65°	619.8	608.2	588.9	571.5	561.8
67.5°	542.6	532.8	515.6	502.1	494.2
70°	471.1	463.4	445.9	432.4	424.8
72.5°	397.8	390.0	380.4	366.9	361.1
75°	324.2	320.6	310.7	299.3	303.2
77.5°	258.7	250.9	247.0	241.3	235.6
80°	193.2	191.1	187.2	181.5	177.6
82.5°	131.3	131.3	129.4	121.7	121.7
85°	79.0	77.2	75.3	69.4	67.6
87.5°	34.8	31.0	27.0	21.3	19.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930681

CATALOG NUMBER: DFN2DS-PN4F0-060DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.61	14.22	12.98	14.54	14.85	12.17	13.78	12.53	14.09	14.41
	3H	14.36	15.82	14.74	16.14	16.50	13.87	15.32	14.25	15.65	16.01
	4H	15.01	16.38	15.41	16.72	17.10	14.51	15.88	14.91	16.23	16.61
	6H	15.48	16.74	15.89	17.11	17.50	14.98	16.24	15.39	16.61	17.00
	8H	15.62	16.83	16.04	17.22	17.62	15.12	16.33	15.54	16.72	17.12
	12H	15.71	16.87	16.14	17.25	17.68	15.20	16.36	15.63	16.74	17.17
4H	2H	13.17	14.54	13.57	14.89	15.26	12.82	14.19	13.22	14.54	14.91
	3H	15.15	16.29	15.56	16.69	17.09	14.74	15.89	15.15	16.28	16.68
	4H	15.92	16.96	16.35	17.37	17.81	15.50	16.54	15.93	16.95	17.38
	6H	16.52	17.42	16.97	17.86	18.32	16.09	16.99	16.54	17.43	17.89
	8H	16.71	17.56	17.17	18.00	18.46	16.27	17.12	16.73	17.56	18.03
	12H	16.84	17.60	17.32	18.08	18.55	16.39	17.15	16.87	17.62	18.09
8H	4H	16.20	17.04	16.66	17.49	17.95	15.82	16.67	16.28	17.11	17.58
	6H	16.91	17.61	17.40	18.10	18.58	16.53	17.23	17.02	17.72	18.20
	8H	17.17	17.80	17.68	18.31	18.79	16.78	17.41	17.29	17.92	18.40
	12H	17.37	17.93	17.88	18.42	18.98	16.96	17.51	17.46	18.01	18.57
12H	4H	16.22	16.98	16.70	17.46	17.93	15.86	16.62	16.34	17.09	17.56
	6H	16.96	17.59	17.47	18.09	18.58	16.59	17.22	17.10	17.73	18.21
	8H	17.27	17.83	17.78	18.32	18.88	16.89	17.45	17.40	17.94	18.50